

24" Full HD LED Monitor

Art. no. TVAC10060

Page 1 of 2



- Resolution: 1920 x 1080 pixels
- Fast reaction time (5 ms)
- LED background lighting: brilliant colour display and contrast
- Graphical on-screen display (OSD)
- Connections: HDMI, DVI, VGA, audio input and output
- Integrated loudspeakers
- Low power consumption (LED technology)
- For wall and ceiling installation (with VESA mount)

The 24" LED monitor displays full HD 1080p pictures in 16:9 format, making it ideally suited for displaying megapixel surveillance pictures.

Detailed surveillance pictures in full HD

Thanks to a rapid reaction time of just 5 ms, surveillance pictures in full HD are transmitted in a matter of seconds. Quick movements on the screen are shown clearly and continuously, without any distortions, flickering or ghost images. You see detailed, vivid pictures in full HD quality.

Versatile connections

The connections ensure a high level of flexibility when connecting the monitor to a recorder or PC. Thanks to the HDMI connection, the monitor is optimally suited to displaying images in full HD. The VGA and DVI connections provide additional options, making the monitor a suitable component for versatile surveillance systems, and it is further equipped with an integrated loudspeaker and an audio input and output.

Energy efficiency

The efficient LED display ensures very low power consumption.

Easy installation

VESA standard mounts allow mounting to a wall or ceiling. This makes installation fast and easy.

24" Full HD LED Monitor

Art. no. TVAC10060

Page 2 of 2

Technical Data:

Dimensions	580 x 407 x 75 mm
Connections	1 x HDMI, 1x DVI, 1 x VGA, 1 x PC Audio
Horizontal/vertical viewing angle	160° x 160° °
Picture format	16:9
Screen diagonal	23.6 "
Width	580 mm
Gross weight	5.2 kg
Display surface	matte
EAN	4043158063646
Input	1 x HDMI, 1x DVI, 1 x VGA, 1 x PC Audio
Color levels	16.7 MIO
Frequency range	30 – 80KHz (H) / 50 – 75Hz (V) GHz
Housing material	Plastic
Brightness	300 cd/m ²
Height	425 mm
Comb filter	3D

Contrast ratio	1000:1
Loudspeaker	2 x 1,5 W
Power consumption	max. 25 W
Max. operating temperature	50 °C
Max. humidity	max. 85 %
Min. operating temperature	0 °C
Monitor type	LED
Net weight	4 kg
Pixel pitch	0.2715 x 0.2715 (H) x (V) mm
Reaction time	5 ms
Signal detection	Automatic
DC voltage supply	12 V
Power consumption	3.000 mA