

# DMCV 0,5/ 2-G1SHL-2,54P20THR24 - PCB header



1150824

<https://www.phoenixcontact.com/gb/products/1150824>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



PCB headers, nominal cross section: 0.34 mm<sup>2</sup>, color: black, nominal current: 5 A, rated voltage (III/2): 160 V, contact surface: Au, contact connection type: Pin, number of positions: 2, product range: DMCV 0,5/...-G1SHL-THR, pitch: 2.54 mm, mounting: THR soldering / wave soldering, solder pin [P]: 2 mm, plug-in system: COMBICON DFMC 0,5 lock & shielded, Electrical properties: shielded, Pin connector pattern alignment: Standard, locking: shielded connection, mounting method: Lock & Shield, type of packaging: 24 mm wide tape, Suitable for CAT5

## Your advantages

- Satisfies CAT5 requirements in accordance with EN 50173 and ISO/IEC 11801

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 1150824       |
| Packing unit                         | 200 pc        |
| Minimum order quantity               | 200 pc        |
| Sales key                            | AAAJLB        |
| Product key                          | AAAJLB        |
| GTIN                                 | 4063151147341 |
| Weight per piece (including packing) | 3.347 g       |
| Weight per piece (excluding packing) | 3.347 g       |
| Customs tariff number                | 85366930      |
| Country of origin                    | PL            |

## Technical data

### Product properties

|                           |                        |
|---------------------------|------------------------|
| Product type              | PCB headers            |
| Product family            | DMCV 0,5/..-G1SHL-THR  |
| Product line              | COMBICON Connectors XS |
| Number of positions       | 2                      |
| Pitch                     | 2.54 mm                |
| Electrical characteristic | shielded               |

### Electrical properties

#### Properties

|                             |          |
|-----------------------------|----------|
| Nominal current $I_N$       | 5 A      |
| Nominal voltage $U_N$       | 160 V    |
| Contact resistance          | 5 mΩ     |
| Rated voltage (III/3)       | 50 V     |
| Rated surge voltage (III/3) | 0.8 kV   |
| Rated voltage (III/2)       | 160 V    |
| Rated surge voltage (III/2) | 2.5 kV   |
| Rated voltage (II/2)        | 160 V    |
| Rated surge voltage (II/2)  | 1.5 kV   |
| Electrical characteristic   | shielded |

#### Data transmission

|                                         |                  |
|-----------------------------------------|------------------|
| Signal type                             | EtherCAT®        |
| Frequency range                         | to 100 MHz       |
| Transmission medium                     | Copper           |
| Transmission characteristics (category) | CAT5 (IEC 11801) |
| Data transmission rate                  | 100 Mbps         |
| Power transmission                      | PoE+             |

### Mounting

|               |                                |
|---------------|--------------------------------|
| Mounting type | THR soldering / wave soldering |
|---------------|--------------------------------|

#### Processing notes

|                                  |                       |
|----------------------------------|-----------------------|
| Process                          | Reflow/wave soldering |
| Moisture Sensitive Level         | MSL 1                 |
| Classification temperature $T_c$ | 260 °C                |
| Solder cycles in the reflow      | 3                     |

### Material specifications

#### Material data - contact

|      |                                                                                  |
|------|----------------------------------------------------------------------------------|
| Note | WEEE/RoHS-compliant, free of whiskers according to IEC 60068-2-82/JEDEC JESD 201 |
|------|----------------------------------------------------------------------------------|

# DMCV 0,5/ 2-G1SHL-2,54P20THR24 - PCB header



1150824

<https://www.phoenixcontact.com/gb/products/1150824>

|                                             |                        |
|---------------------------------------------|------------------------|
| Contact material                            | Cu alloy               |
| Surface characteristics                     | Completely gold-plated |
| Metal surface contact area (top layer)      | Gold (0.25 Au)         |
| Metal surface contact area (middle layer)   | Nickel (2 - 4 µm Ni)   |
| Metal surface soldering area (top layer)    | Gold (0.25 Au)         |
| Metal surface soldering area (middle layer) | Nickel (2 - 4 µm Ni)   |


## Material data - housing

|                                        |              |
|----------------------------------------|--------------|
| Color (Housing)                        | black (9005) |
| Insulating material                    | LCP          |
| Insulating material group              | IIIa         |
| CTI according to IEC 60112             | 175          |
| Flammability rating according to UL 94 | V0           |

## Notes

|                     |                                                                                                             |
|---------------------|-------------------------------------------------------------------------------------------------------------|
| Note on application | The item is qualified for CAT5 Ethernet applications. For this reason, it is suited for use in IoT devices. |
|---------------------|-------------------------------------------------------------------------------------------------------------|

## Dimensions

|                       |                                                                                      |
|-----------------------|--------------------------------------------------------------------------------------|
| Dimensional drawing   |  |
| Pitch                 | 2.54 mm                                                                              |
| Width [w]             | 9.66 mm                                                                              |
| Height [h]            | 11.91 mm                                                                             |
| Length [l]            | 8.19 mm                                                                              |
| Installed height      | 9.91 mm                                                                              |
| Solder pin length [P] | 2 mm                                                                                 |

## PCB design

|               |        |
|---------------|--------|
| Hole diameter | 1.2 mm |
|---------------|--------|

## Mechanical tests

### Visual inspection

|               |                       |
|---------------|-----------------------|
| Specification | IEC 60512-1-1:2002-02 |
| Result        | Test passed           |

### Dimension check

|               |                       |
|---------------|-----------------------|
| Specification | IEC 60512-1-2:2002-02 |
| Result        | Test passed           |

### Resistance of inscriptions

|               |                        |
|---------------|------------------------|
| Specification | IEC 60068-2-70:1995-12 |
|---------------|------------------------|

# DMCV 0,5/ 2-G1SHL-2,54P20THR24 - PCB header



1150824

<https://www.phoenixcontact.com/gb/products/1150824>

|        |             |
|--------|-------------|
| Result | Test passed |
|--------|-------------|

## Polarization and coding

|               |                        |
|---------------|------------------------|
| Specification | IEC 60512-13-5:2006-02 |
| Result        | Test passed            |

## Contact holder in insert

|                                                |                        |
|------------------------------------------------|------------------------|
| Specification                                  | IEC 60512-15-1:2008-05 |
| Contact holder in insert<br>Requirements >20 N | Test passed            |

## Insertion and withdrawal forces

|                                     |             |
|-------------------------------------|-------------|
| Result                              | Test passed |
| No. of cycles                       | 100         |
| Insertion strength per pos. approx. | 3 N         |
| Withdraw strength per pos. approx.  | 3 N         |

## Electrical tests

### Thermal test | Test group C

|                            |                       |
|----------------------------|-----------------------|
| Specification              | IEC 60512-5-1:2002-02 |
| Tested number of positions | 4                     |

### Insulation resistance

|                                              |                       |
|----------------------------------------------|-----------------------|
| Specification                                | IEC 60512-3-1:2002-02 |
| Insulation resistance, neighboring positions | > 5 MΩ                |

### Air clearances and creepage distances |

|                                                        |                     |
|--------------------------------------------------------|---------------------|
| Specification                                          | IEC 60664-1:2007-04 |
| Insulating material group                              | IIIa                |
| Comparative tracking index (IEC 60112)                 | CTI 175             |
| Rated insulation voltage (III/3)                       | 50 V                |
| Rated surge voltage (III/3)                            | 0.8 kV              |
| minimum clearance value - non-homogenous field (III/3) | 0.8 mm              |
| minimum creepage distance (III/3)                      | 1.25 mm             |
| Rated insulation voltage (III/2)                       | 160 V               |
| Rated surge voltage (III/2)                            | 2.5 kV              |
| minimum clearance value - non-homogenous field (III/2) | 1.5 mm              |
| minimum creepage distance (III/2)                      | 1.6 mm              |
| Rated insulation voltage (II/2)                        | 160 V               |
| Rated surge voltage (II/2)                             | 1.5 kV              |
| minimum clearance value - non-homogenous field (II/2)  | 0.5 mm              |
| minimum creepage distance (II/2)                       | 1.6 mm              |

## Environmental and real-life conditions

### Vibration test

|               |                       |
|---------------|-----------------------|
| Specification | IEC 60068-2-6:2007-12 |
|---------------|-----------------------|

# DMCV 0,5/ 2-G1SHL-2,54P20THR24 - PCB header



1150824

<https://www.phoenixcontact.com/gb/products/1150824>

|                        |                                          |
|------------------------|------------------------------------------|
| Frequency              | 10 - 150 - 10 Hz                         |
| Sweep speed            | 1 octave/min                             |
| Amplitude              | 0.35 mm (10 Hz ... 60.1 Hz)              |
| Acceleration           | 50 m/s <sup>2</sup> (60.1 Hz ... 150 Hz) |
| Test duration per axis | 2.5 h                                    |
| Test directions        | X-, Y- and Z-axis                        |

## Durability test

|                                              |                       |
|----------------------------------------------|-----------------------|
| Specification                                | IEC 60512-9-1:2010-03 |
| Impulse withstand voltage at sea level       | 2.95 kV               |
| Contact resistance R <sub>1</sub>            | 5 mΩ                  |
| Contact resistance R <sub>2</sub>            | 4.6 mΩ                |
| Insertion/withdrawal cycles                  | 100                   |
| Insulation resistance, neighboring positions | > 5 MΩ                |

## Climatic test

|                                   |                                                                           |
|-----------------------------------|---------------------------------------------------------------------------|
| Specification                     | ISO 6988:1985-02                                                          |
| Corrosive stress                  | 0.2 dm <sup>3</sup> SO <sub>2</sub> on 300 dm <sup>3</sup> /40 °C/1 cycle |
| Thermal stress                    | 80 °C/168 h                                                               |
| Power-frequency withstand voltage | 1.39 kV                                                                   |


## Ambient conditions

|                                         |                                                     |
|-----------------------------------------|-----------------------------------------------------|
| Ambient temperature (operation)         | -55 °C ... 100 °C (dependent on the derating curve) |
| Ambient temperature (storage/transport) | -40 °C ... 70 °C                                    |
| Relative humidity (storage/transport)   | 30 % ... 70 %                                       |
| Ambient temperature (assembly)          | -5 °C ... 100 °C                                    |

## Packaging specifications

|                             |                                                                                      |
|-----------------------------|--------------------------------------------------------------------------------------|
| Dimensional drawing         |  |
| Type of packaging           | 24 mm wide tape                                                                      |
| [W] tape width              | 24 mm                                                                                |
| [W2] coil overall dimension | ≤ 30.4 mm                                                                            |
| [A] coil diameter           | ≤ 330 mm                                                                             |
| Outer packaging type        | Transparent-Bag                                                                      |
| ESD level                   | (D) electrostatically conductive                                                     |
| Specification               | DIN EN 61340-5-1 (VDE 0300-5-1): 2008-07                                             |

## Drawings



Type: DMCC 0,5/...-ST-SHL 7,0-2,54 with DMCV 0,5/...-G1SHL-2,54P20THR...

# DMCV 0,5/ 2-G1SHL-2,54P20THR24 - PCB header



1150824

<https://www.phoenixcontact.com/gb/products/1150824>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/gb/products/1150824>

|  <b>cULus Recognized</b><br>Approval ID: E60425-19920306 |                       |                       |                   |                             |
|-------------------------------------------------------------------------------------------------------------------------------------------|-----------------------|-----------------------|-------------------|-----------------------------|
|                                                                                                                                           | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $\text{mm}^2$ |
| Use group B                                                                                                                               | 150 V                 | 6 A                   | -                 | -                           |
| Use group C                                                                                                                               | 50 V                  | 6 A                   | -                 | -                           |

|  <b>VDE report with production monitoring</b><br>Approval ID: 40042389 |                       |                       |                   |                             |
|---------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------------|-----------------------|-------------------|-----------------------------|
|                                                                                                                                                         | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $\text{mm}^2$ |
|                                                                                                                                                         | 160 V                 | 6 A                   | -                 | -                           |

# DMCV 0,5/ 2-G1SHL-2,54P20THR24 - PCB header



1150824

<https://www.phoenixcontact.com/gb/products/1150824>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27460201 |
|-------------|----------|

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC002637 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

# DMCV 0,5/ 2-G1SHL-2,54P20THR24 - PCB header



1150824

<https://www.phoenixcontact.com/gb/products/1150824>

## Environmental product compliance

### EU RoHS

|                                         |                    |
|-----------------------------------------|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|-----------------------------------------|--------------------|

### China RoHS

|                                        |                                          |
|----------------------------------------|------------------------------------------|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|                                        | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd  
Halesfield 13, Telford  
Shropshire, TF7 4PG  
01952 681700  
[info@phoenixcontact.co.uk](mailto:info@phoenixcontact.co.uk)