



EN ISO 20345:2011



ENDURANCE

ARKO BOA®
81184-03L
S3 *CI SRC
Size: 36-48

Weight: 680 gr.

Fit: 11

Working Environment:

 Building, Wood-metal carpentry,
 Farming and Gardening,
 Multipurpose


FEATURES

UPPER

 Grain leather Hydro 1,8-2,0 mm
 No ladder H.T. Fabric
 Reflex insert

LINING

3D Air circulation 320 gr.

ANTISLIP LINING

DUALMICRO

INSOLE

Climaction-Fit 337

TOE CAP

Fiber cap SXT

RESISTANCE TO PERFORATION

KX Antiperforation PS

TYPE

Low Shoe

SOLE

PU DUAL-DENSITY SRC

Two-component PU sole with anti-wear scaff cap and high-comfort in-between insole. Outsole with self-cleaning tread pattern, with a formula designed to ensure greater grip. SRC Antislip standard.

TECHNOLOGIES

Removable Insole

climaction³³⁷ fit

Removable anatomic and ergonomic insole. Absorbent and transpiring open-cell foam support. Keeps feet fresh. Specifically-designed thermoforming for exceptional comfort.



Protection elements


 RESISTANT
 TO 3.0 mm.
 NAILS

fibercap sxt

Composite toecap with fiberglass. Resistant to over 200J. Non metal perforation resistant insert to over 1100 N with a 3.0 mm truncated cone nail. Protection over the entire sole of the foot. Flexible and comfortable



Lateral stability

dynamicHC control^{technology}

Ergonomic rigid internal structure. It houses the heel into the right seat, adjusting the foot support and control of the ankle sideways movements. It keeps the foot tight to the shoe, allowing the perfect fit.



Torsional stability

STABIL•ACTIVE

Support made of rigid plastic material. It stabilizes the heel bone, the instep and tarsal joints, without altering energy absorption. A support for the natural movement of the foot; it provides comfort and greater stability.




Electrical features

WED

Wire Electricity Discharge

Strip with 4 filaments of carbon fiber, ensuring proven anti-static properties of the footwear over time.



Other


FIT TO GO FURTHER.™

A patented closing system with a multi coated stainless steel cable. The BOA® Fit System delivers micro-adjustable precision fit, engineered to perform in the toughest conditions.



SRC (SRA+SRB)


 SOLE 81
 PU - PU

SRA CERAMIC + DETERGENT SOLUTION	FLAT ≥0.32 HEEL (CONTACT ANGLE °°) ≥0.28	0.52
SRB STEEL + GLYCEROL	FLAT ≥0.18 HEEL (CONTACT ANGLE °°) ≥0.13	0.23

EN ISO 20344:2011