


ENGLISH

Product Datasheet Anti-Vandal Switch Switch Pushbutton Stainless Latching









Package Contain:

1 x Anti-Vandal Switch

1 x Hex Nuts

1 x O-Ring

ENGLISH

Specification:

- r				
SWITCH TYPE:		8118411		
POLES/THROWS:		SPDT		
SWITCH FUNCTIONS:		Illuminated, ON-ON		
ELECTRICAL CHARACTERISTICS	CONTACT RATING:	MAX. 3Amps @ 250VAC		
	ELECTRICAL LIFE:	50,000 make-and-break cycles at full load		
	CONTACT RESISTANCE:	50m-ohms max. initial @ 2-4VDC, 100mA		
	INSULATION RESISTANCE:	Apply 500VDC for 1min±5sec. After which measurement to be made b/w terminals shall result 1000M-ohms min.		
	DIELECTRICAL STRENGTH:	2,000VAC (50Hz-60Hz) RMS @ sea level shall result no damage to parts arcing or flashover		
	OPERATING TEMPERATURE:	-20Celsius degree to +55Celsius degree		
	MECHANICAL LIFE:	Without load, 50,000cycles min.		
	OPERATING FORCE:	4N max.		
	TORQUE:	5~14Nm max. applied to nut		
핑	IP PROTECTION CLASS:	Front panel protection to IP67		
RELAIBILITY PERFORMANCE	SOLDERING HEAT RESISTANCE:	Max soldering temperature @ 260Celsius degree, immersion time 5+/-1sec, frequency of soldering process @ 2 times max.		
	COLD TEST:	Stored at temperature –20(+/-3)Celsius degree for 48 hours, shall result no changes to switch's electrical performance		
	HOT TEST:	Stored at temperature +55(+/-3)Celsius degree for 48 hours, shall result no changes to switch's electrical performance		
	HUMIDITY TEST:	Stored at temperature 40(+/-3)Celsius degree with relative humidity 90%~95% for 48 hours, shall result no changes to switch's electrical performance		
	TORQUE:	5~14Nm max. applied to nut		
	OPERATING FORCE:	4N max.		

RS, Professionally Approved Products, gives you professional quality parts across all products categories. Our range has been testified by engineers as giving comparable quality to that of the leading brands without paying a premium price.



ENGLISH

MATERIAL CHARACTERISTICS	BUTTON:	
	BUSHING:	B32 : Stain less steel with varnished polished
	BASE:	PBT
	PLUNGER:	РОМ
	SPRING:	Steel wire
	CONTACT:	Copper alloy, silver plated
	TERMINALS:	Brass, silver plated
	HARDWARE:	Nut (Brass, nickel plated)
2	LED:	Red,(AC/DC Compatible)
		Voltage & Rating: 24V@ 15mA
SOLDERING & CLEANING RECOMMENDATION	HAND SOLDERING:	Max. temperature @ 320Celsius degree (662F)with continuous soldering time @ 2sec. max.
	CLEANING PROCESS:	Noted, the switch is "not totally sealed" so it is important not to immerse/spray or clean unsealed areas of the switch during flux removal. Improper cleaning could cause switch deficiencies such as intermittence or open contact failures
PACKAGE	INTERNAL PACKAGING:	1pcs per PE bag
	RoHS IDENTIFI-CATIONS:	A label marking "RoHS compliant" will be attached to the carton box.