

# Eaton 265244

Catalog Number: 265244

Eaton Distribution parts. Restarting device, 24-48VDC, 4HP

General specifications



Product Name  
Eaton Distribution parts

Catalog Number  
265244

EAN  
4015082652449

Product Length/Depth  
80 mm

Product Height  
77.3 mm

Product Width  
88.4 mm

Product Weight  
0.247 kg

Compliances  
RoHS conform

## Product specifications

### Used with

Restarting device  
Accessory for residual current circuit breaker  
Accessory  
Accessory for miniature circuit breaker

### Type

Accessory  
Accessory for miniature  
circuit breaker  
Accessory for residual  
current circuit breaker

### Special features

Z-FW... (Test module (0.5 space unit) for remote testing of residual current devices)

### Application

Switchgear for industrial and advanced commercial applications

### Accessory/spare part type

Restarting device

### Degree of protection

IP40

### Frame

Standard front dimension: 45 mm

### Equipment heat dissipation, current-dependent

0 W

### Mounting method

For fitting on right to: CLS6, PFIM, PFHM-4p, dRCM, Z-A40, PFR, Z-MS  
Quick attachment with 2 latch positions on top-hat rail IEC/EN 60715

### Additional equipment required

Monitoring unit with automatic reclosing

### Terminal protection

Protection against electric shock to BGV A3, ÖVE-EN 6

### Terminal type

Lift terminals

### Ambient operating temperature - max

40 °C

## Resources

### Declarations of conformity

DA-DC-03\_Z-FW-LP

### Drawings

[eaton-dimensions-mas-fw-lp.jpg](#)

### Installation instructions

IL019014ZU

### mCAD model

[z\\_fw\\_lp.dwg](#)

[z\\_fw\\_lp.stp](#)

### Wiring diagrams

FW\_LPD

Ambient operating temperature - min

-25 °C

Assembly width

4 TE

Enclosure width

80 mm

Heat dissipation capacity

0 W

Heat dissipation per pole, current-dependent

0 W

Number of contacts (change-over contacts)

0

Number of contacts (normally closed contacts)

0

Number of contacts (normally open contacts)

0

Number of poles at main contact unit - max

0

Number of switches (fault signal)

0

Rated operational current for specified heat dissipation (In)

0 A

Voltage type

DC

Functions

Automatic restart

With auto test for earth leakage function

Remote drive

Device fitting

Universal

Mounting width

70 mm

Function selector

Automatic 5 x, OFF/RESET

Rated operational voltage (Ue) - max

48 V

Rated switch current

0 A

Relay output for alarm

5 A

Static heat dissipation, non-current-dependent

0.8 W

Suitable for current of main contact unit - max

0 A

Voltage rating at DC

24 V DC - 48 V DC

Terminal capacity (cable)

2.5 mm<sup>2</sup> (1x)

1.5 mm<sup>2</sup> (2x)

Terminal capacity (solid wire)

1 mm<sup>2</sup> - 2.5 mm<sup>2</sup>

1.5 mm<sup>2</sup> (2x)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://Eaton.com/socialmedia)