

DSE201 M C40 AC30 - N Blue



Products Low Voltage Products and Systems Modular DIN Rail Products Residual Current Devices RCDs
Residual Current Circuit Breakers with Overcurrent Protection RCBO

General Information

Extended Product Type:	DSE201 M C40 AC30 - N Blue
Product ID:	2CSR275051R1404
EAN:	8012542353232
Catalog Description:	DSE201 M C40 AC30 - N Blue
Long Description:	DSE201 M is a 1P+N residual current circuit breaker with overcurrent protection (RCBO) in one module for the protection against short-circuit currents, overload, earth fault currents, indirect contacts, additional protection against direct contacts (30 mA versions). DSE201 M is equipped with supply neutral wire and functional earth wire.

Additional Information

Country of Origin:	Italy (IT)
Customs Tariff Number:	85363030
Data Sheet, Technical Information:	9AKK106930A0939
Declaration of Conformity - CE:	9AKK106930A0955
EAN:	8012542353232
ETIM 4:	EC000905 - Earth leakage circuit breaker
ETIM 5:	EC000905 - Earth leakage circuit breaker
ETIM 6:	EC000905 - Earth leakage circuit breaker
Instructions and Manuals:	9AKK106930A0912
Invoice Description:	DSE201 M C40 AC30 - N Blue
Minimum Order Quantity:	1 piece
Number of Poles:	2
Number of Protected Poles:	1
Object Classification Code:	Q
Operating Characteristic:	Instantaneous
Options Provided:	-
Package Level 1 EAN:	8012542353232
Package Level 1 Gross Weight:	0.220 kg
Package Level 1 Height:	0.088 m
Package Level 1 Length:	0.143 m
Package Level 1 Units:	1 piece
Package Level 1 Width:	0.036 m
Position of Neutral Terminals:	Right
Power Loss:	5.5 W
Product Main Type:	DSE201 M
Product Name:	Residual Current Circuit Breaker with Overcurrent Protection
Product Net Depth:	0.069 m
Product Net Height:	0.115 m
Product Net Weight:	0.200 kg
Product Net Width:	0.018 m
Rated Current (I_n):	40 A
Rated Operational Voltage:	230-240 V AC
Rated Residual Current:	30 mA
Rated Short-Circuit Capacity (I_{cn}):	10 kA
RoHS Date:	20160829
RoHS Information:	9AKK106930A1510
RoHS Status:	Following EU Directive 2011/65/EC
Selling Unit of Measure:	piece
Standards:	IEC 61009-1 IEC 61009-2-2 BS EN 61009-1 AS/NZS 61009
Tripping Characteristic:	C
Type of Residual Current:	AC type
Accessories Available:	Yes

