



Datasheet

RS PRO Piezo Audio Transducer

EN



A. SCOPE


This specification applies piezo audio indicator, 1812661

B. SPECIFICATION

No.	Item	Unit	Specification	Condition
1	Resonant frequency	KHz	3.0 ± 0.5	
2	Operating Volt. Range	VDC	3~ 20	
3	Current consumption	mA	MAX 13	at 12VDC
4	Sound pressure level	dB	MIN 83	at 30cm/12VDC
5	Rated Voltage	VDC	12	
6	Tone		Continuous	
7	Operating temp.	°C	-30 ~ +85	
8	Storage temp.	°C	-40 ~ +95	
9	Dimension	mm	φ 24.0 x H16.0	See appearance drawing
10	Weight (MAX)	gram	4.5	
11	Material		ABS UL-94 1/16" HB HIGH HEAT (BLACK)	
12	Terminal		Pin type(Plating Au)	See appearance drawing
13	Environmental Protection Regulation		RoHS	



C. APPEARANCE DRAWING




Tol : ± 0.5

Unit : mm


D. MEASURING METHOD

S.P.L. Measuring Circuit



Mic : RION S.P.L meter UC30 or equivalent


**E.VOLTAGE: SOUND PRESSURE LEVEL /
VOLTAGE: CURRENT CONSUMPTION
CHARACTERISTICS**



F. MECHANICAL CHARACTERISTICS

No.	Item	Test Condition	Evaluation standard
1	Solderability	Lead terminals are immersed in rosin for 5 seconds and then immersed in solder bath of +270±5°C for 3±1 seconds.	90% min. lead terminals shall be wet with solder. (Except the edge of terminal)
2	Soldering Heat Resistance	Lead terminal are immersed up to 1.5mm from sounder's body in solder bath of +260±5°C for 3±1 seconds.	No interference in operation
3	Terminal Mechanical Strength	The force 10 seconds of 9.8N (1.0kg) is applied to each terminal in axial direction.	No damage and cutting off
4	Vibration	Buzzer shall be measured after being applied vibration of amplitude of 1.5mm with 10 to 55hz band of vibration frequency to each of 3 per-pendicular directions for 2 hours. .	The value of oscillation frequency/ current consumption should be in 10% compared with initial ones .The SPL should be in ± 10dB compared with initial one.
5	Drop test	The part only shall be dropped from a height of 75cm onto a 40mm thick wooden board 3 times in 3 axes (X.Y.Z). (a total of 9 times).	

G. ENVIRONMENT TEST

No.	Item	Test Condition	Evaluation standard
1	High temp. test	After being placed in a chamber at +95°C for 240 hours	Being placed for 4 hours at +25°C, buzzer shall be measured. The value of oscillation frequency/ current consumption should be in±10% compared with initial ones .The SPL should be in±10dB compared with initial one.
2	Low temp. test	After being placed in a chamber at -40°C for 240 hours	
3	Humidity test	After being placed in a chamber at +40°C and 90±5% relative humidity for 240 hours	
4	Temp. cycle test	<p>The part shall be subjected to 5 cycles. One cycle shall be consist of :</p>  <p>The diagram shows a temperature cycle test profile. It starts at -40°C for 0.5hr, then ramps up to +25°C in 0.5hr, stays at +25°C for 0.25hr, ramps up to +95°C in 0.5hr, stays at +95°C for 0.5hr, ramps down to +25°C in 0.5hr, and stays at +25°C for 0.25hr. The total duration of one cycle is 3 hours.</p>	

H. RELIABILITY TEST

No.	Item	Test condition	Evaluation
1	Operating life test	<p>1.Continuous life test 48 hours continuous operation at +70°C with rated voltage applied.</p> <p>2.Intermittent life test A duty cycle of 1 minute on, 1minutes off, a minimum of 5000 times at room temp.(+25±2°C)and rated voltage applied.</p>	Being placed for 4 hours at +25°C, buzzer shall be measured. The value of oscillation frequency/ current consumption should be in ±10% compared with initial ones .The SPL should be in ±10dB compared with initial one.

TEST CONDITION.

Standard Test Condition : a) Temperature : +5 ~ +35°C b) Humidity : 45-85%

Judgement Test Condition : a) Temperature : +25 ± 2°C b) Humidity : 60-70%

c) Pressure : 860-1060mbar

c) Pressure : 860-1060mbar