

NU306954S

2 Socket-outlet, New Unica, mechanism, 2P + E, 16A, French, shutter, screwless terminals, IP3x, painted, anthracite

Main

Range	New Unica
Product or component type	Socket-outlet
Device presentation	Mechanism
Device mounting	Flush
Socket number	2
Outlet poles configuration	2P + E
Outlet standard	CEE 7/5
Outlet standard deviation	French
Outlet standard description	Pin earth
Ground lug position	45° ground lug
Rated current	16 A

Complementary

Device application	Power supply
Cover type	With shutter
[Ue] rated operational voltage	250 V
Network type	AC
Network frequency	50/60 Hz
Number of modules	4 modules
Fixing mode	Clip-in
Colour tint	Anthracite (RAL 7021)
Pilot light	Red indicator lamp, colour: red, current consumption: 1.5 mA
Connections - terminals	Screwless terminals
Cable cross section	0...2.5 Mm² cable(s), 2 - cable stiffness: flexible 0...2.5 mm² cable(s), 2 - cable stiffness: rigid
Minimum load breaking capacity	100 operations 1.25 In and 1.1 Un, cos phi = 0.6
Electrical durability	10000 cycles, cos phi = 0.8
Insulation resistance	> 5 MOhm at 500 V
Dielectric strength	2000 V
Material	PC: mechanism cover
Surface finish	Painted
Quantity per set	Set of 1 without packaging
Standards	IEC 60884-1 NF C 61-314
Product certifications	NF
Embedding depth	30 mm
Depth	39.4 mm
Width	45 mm
Height	90 mm
Net weight	0.077 kg

The information provided in this documentation contains general descriptions and/or technical characteristics of the products of the company. It is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Surface treatment	Painted
Resistance to chemical agents	Resistant to alcohol (70 %) Resistant to alcohol (96 %) Resistant to A-Lactic Acid Resistant to diluted quaternary ammonium Resistant to diluted bleach Resistant to diluted ammonia Resistant to soapy water Resistant to crystal cleaner Resistant to hydrogen peroxide 10 volumes Resistant to hexane

Environment

Ambient air temperature for operation	-5...35 °C
Ambient air temperature for storage	-5...50 °C
IK degree of protection	IK04
IP degree of protection	IP3x
Environmental characteristic	Acetone Bleach UV resistant Petrol Oil Alcohol Window-cleaning fluid Liquid soap

Offer Sustainability

EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
Sustainable packaging	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Minimum percentage of recycled plastic content	60