

318.3247**CONNECTOR****32A 3P+N+E 6h 346-415V 60Hz 50Hz****Screw terminals**

* Product image may be indicative



EN IEC 60309-1 (2022)

EN IEC 60309-2 (2022)

Low voltage direct. 2014/35/EU

GENERAL CHARACTERISTICS

Commercial Series OPTIMA Series

Synthetical description CONNECTOR

Description

The OPTIMA Series connector is engineered for demanding electrical industrial environments, offering a rated voltage of 346-415V and a rated current of 32A. This connector features a 3P+N+E configuration and a 6h hour position, ensuring reliable performance across various applications. With an IP66/IP67/IP69 protection degree, it provides exceptional resistance to dust and water ingress. The connector is equipped with screw terminals for secure and efficient connections. Available in a straight outlet type, it is designed to meet the rigorous demands of industrial settings, ensuring durability and reliability.

Mounting version PORTABLE

TECHNICAL CHARACTERISTICS

Rated current 32A

Poles 3P+N+E

Hour position 6h

Rated voltage 346-415V

Working frequency 60Hz

50Hz

Terminals Screw terminals

PHYSICAL CHARACTERISTICS

Mounting version PORTABLE

Colour RED

Material THERMOPLASTIC

Protection degree Watertight

Protection degree IP IP66/IP67/IP69

Protection degree IK IK08

Types of available outlets STRAIGHT

Contact material CuZn (brass)

Cable entry CABLE GLAND

DOWNLOAD

Technical drawing [PDF]

Technical drawing [STP]

Technical drawing [DWG]