










CAPPED VIEW




REAR VIEW




RECOMMEND MINIMUM MOUNTING PITCH



ASSEMBLY VIEW



PCB LAYOUT
CONNECTOR SIDE



RECOMMEND PANEL CUT OUT

NOTE:
1. MATING CONNECTOR SHELL TO HAVE MIN 1.6 SURFACE FINISH TO ACHIEVE IP RATING OF THIS CONNECTOR.
2. BLACK MOUNTING SCREW 52500011-430 x 4 PCS TO BE SUPPLIED WITH THE CONNECTOR, MAX TORQUE 0.5Nm.
3. DUE TO 0.4mm THICK RUBBER SEAL, THE DIM WILL VARY DEPENDING ON THE SCREWS TIGHTENING IN ASSEMBLY.

3	52730035-000	AXS FRONT FLANGE D TYPE RUBBER SEAL IP54 WITH CAP	1
2	55011500-003/903	AXS3MPV WITHOUT RUBBER FLANGE - TIN/GOLD PLATED CONTACT	1
1	52500011-430	SELF TAPPING SCREW 2.9 x 1.06mm BLACK	4
ITEM	PART NUMBER	DESCRIPTION	QTY

UNLESS OTHERWISE SPECIFIED TOLERANCE TO BE	
LINEAR	ANGULAR
X ± 0.5	X' ± 1
X.X ± 0.2	X.X' ± 30'
X.XX ± 0.1	X.XX' ± 15'

BREAK ALL SHARP EDGES
AND REMOVE ALL BURRS

DO NOT SCALE

DIMENSIONS IN MILLIMETRES

THIS DOCUMENT IS THE PROPERTY OF AMPHENOL AUSTRALIA PTY. LTD.
NO PART THEREOF MAY BE REPRODUCED AND USED
WITHOUT THE PRIOR WRITTEN CONSENT OF THE OWNER

MATERIAL:
SEE COMPONENT

FINISH:
SEE COMPONENT



THIRD ANGLE
PROJECTION

DRN: M.H

CKD: M.H

APP'D: P.M

SCALE: **1:1**

DATE: 11-11-23

DATE: 11-11-23

DATE: 11-11-23

SIZE: **A4**

Amphenol Amphenol Australia Pty.Ltd,
22 Industry Blvd, Carrum Downs, VIC 3201

TITLE:
**AXS3MPV
AXS PANEL MOUNT SERIES
CUSTOMER DRAWING**

CAD FILE: 55011500803110

PART No.
SEE TABLE

DRAWING No.

55011500-803-2

SHEET
2/2

PART NUMBER	CONTACT FINISH
AXS3MPV	TIN PLATED
AXS3MPV-AU	GOLD PLATED