

Features

- Piezo buzzer
- Operating voltage 3-28VDC
- Rated voltage 12VDC
- Fitted with leads
- SPL 90dB
- Slow pulse tone
- With internal drive circuit
- Diameter: 42mm
Height: 16mm

RS PRO Piezo Buzzer Slow Pulse, 90dB

RS Stock No.: 1797426



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

Generating a minimum sound output of 90dB this buzzer operates with a slow pulse tone. It is ideal for an application which needs a warning. Operating between 3-28VDC it has a rated voltage of 12VDC. It is connected using 140mm leads. It doesn't need external circuitry to produce a sound as it has its own internal circuit and just requires a DC voltage.

APPLICATIONS:

- Access & security
- Medical
- Home appliances
- Toys & games
- Consumer electronics
- Timers
- Load monitors & pressure gauges
- Agricultural system monitoring
- Alarms within automotive applications such as seat belt, tyre pressure, temperature warnings
- Sensing & instrumentation
- Communications equipment
- Remote monitoring systems
- Safety products

Electrical Specifications



1. ELECTRICAL AND ACOUSTICAL SPECIFICATION

	Item	Unit	Specifications
1-1	Rated Voltage	VDC	12
1-2	Operating Voltage	VDC	3-28
1-3	* Rated Current (Max)	mA	9
1-4	* Min Sound Output at 30cm	dB	90
1-5	* Resonant Frequency	Hz	2800±500
1-6	Tone Nature		Slow Pulse 1.2±30%HZ
1-7	Operating Temperature	°C	-20~+60
1-8	Storage Temperature	°C	-30~+70
1-9	Weight	g	15
1-10	Housing Material		ABS
1-11	Lead Wire		UL1007 AWG24 (Red & Black)

* Value Applying at Rated Voltage(DC)

Note: With internal drive circuit

2.ENVIRONMENTAL TEST

	Item	Specifications
2-1	Storage in High temp.	Storage in $+70^{\circ}\text{C} \pm 2^{\circ}\text{C}$ test box for 96 hours, then expose to the room temperature for 2 hours without applying power.
2-2	Storage in Low temp.	Storage in $-30^{\circ}\text{C} \pm 2^{\circ}\text{C}$ test box for 96 hours, then expose to the room temperature for 2 hours without applying power.
2-3	Storage in Humidity	Storage in $+30^{\circ}\text{C} \pm 2^{\circ}\text{C}$ 90-95%RH test box for 96 hours, then expose to the room temperature for 2 hours without applying power.
2-4	Thermal cycle test.	 <p>Make this test for 5 cycles without applying power, then expose to the room temperature for 2 hours.</p>
2-5	Vibration test	 <p>Amplitude: 1.5mm Time : 1min/axis</p> <p>Make this test for the directions of X,Y, Z for 2 hours each (total 6 hours).</p>
2-6	Drop test	Free drop a unit from the height 70cm to the surface of 10mm thick board ,three directions(X,Y,Z).
<p>PASS CRITERION :</p> <p>After these tests , the change of S.P.L shall be within $\pm 5 \text{ dB}$.</p>		

3. MEASURING METHOD (BUZZER MODE)

3-1 . Test Condition

3-1-1. STANDARD

Temperature : $25 \pm 3^{\circ}\text{C}$

Relative humidity : 60% ~ 70%,

Atmospheric pressure : 860mbar to 1060mbar

3-1-2. JUDGEMENT

Temperature : $15 \sim 35^{\circ}\text{C}$


Relative humidity : 45% ~ 85%,

Atmospheric pressure : 860mbar to 1060mbar.

3-2 . Standard Test Fixture


3-2-1. rated Voltage: 12VDC

3-2-2. Resonant Frequency: $2800\text{Hz} \pm 500$



4.DIMENSIONS

Unless otherwise specified, tolerance: ± 0.5 (unit:mm)



- 1) All parts must be meet to ROHS.
- 2) Wave solder and wash not allowed.

5	Cover	1	Black ABS	
4	Housing	1	Black ABS	
3	Lead Wire	2	UL1007 AWG24(Red&Black)	
2	Piezo element	1	Brass	
1	PCB	1	Epoxy Board	
Part No.	Part Name	Q'TY	Material	Remark