

SIMATIC CFU CIO HART with aluminum enclosure, bundle consisting of: 1x SIMATIC CFU CIO HART (6ES7655-5PX41-1XX0), 1x aluminum enclosure with cable glands, shield busbar, shield terminals, preassembled and checked



| General information   |                                      |
|---|--------------------------------------|
| Product type designation  | CFU CIO HART with aluminum enclosure |
| HW functional status  | FS01                                 |
| Firmware version  | V1.0                                 |
| • FW update possible  | Yes                                  |
| Vendor identification (VendorID)                                      | 002AH                                |
| Device identifier (DeviceID)  | 0319H                                |
| Number of channels  | 16                                   |
| Product function  |                                      |
| • I&M data  | Yes; I&M0 to I&M3                    |
| • Isochronous mode  | No                                   |
| • The user can configure digital channels as input/output as required | Yes                                  |
| • Digital channels can be parameterized                               | Yes                                  |
| Engineering with  |                                      |
| • STEP 7 TIA Portal configurable/integrated from version              | V19 Update 2                         |
| • STEP 7 configurable/integrated from version                         | STEP 7 V5.7.1.4                      |
| • PCS 7 configurable/integrated from version                          | V9.1 SP2 UC7 (+PDM V9.3 Upd1)        |
| • PROFIBUS from GSD version/GSD revision                              | - / -                                |
| • PROFINET from GSD version/GSD revision                              | GSDML V2.43 2024.03.04               |
| Operating mode  |                                      |
| • DI  | Yes                                  |
| • Counter   | Yes                                  |
| • DQ  | Yes                                  |
| CiR - Configuration in RUN  |                                      |
| Reparameterization possible in RUN                                    | Yes                                  |
| Installation type/mounting  |                                      |
| Mounting  | For horizontal and vertical mounting |
| Mounting position   | Horizontal, vertical                 |
| Recommended mounting position   | horizontal set up                    |
| Supply voltage  |                                      |
| Type of supply voltage  | 24 V DC                              |
| Rated value (DC)  | 24 V                                 |
| permissible range, lower limit (DC)                                   | 19.2 V                               |
| permissible range, upper limit (DC)                                   | 28.8 V                               |
| Reverse polarity protection   | Yes                                  |
| Short-circuit protection  | Yes                                  |
| Redundant power supply  | Yes                                  |
| Mains buffering   |                                      |

|   |   |
|---|---|
| <ul style="list-style-type: none"> <li>• Mains/voltage failure stored energy time</li> </ul>  | 1 ms; For communication   |
| <b>Input current</b>  |   |
| Current consumption (rated value)   | 4.1 A; RJ45 BusAdapter, 8xDI, 4xAI, 2xAQ, 2xDQ with 2 A each  |
| Current consumption, max.   | 9 A   |
| Inrush current, max.  | 7 A   |
| I <sup>2</sup> t  | 0.5 A <sup>2</sup> ·s   |
| <b>Encoder supply</b>   |   |
| Number of outputs   | 16  |
| Output voltage, min.  | 12 V  |
| Short-circuit protection  | Yes; Electronic   |
| <b>Output current</b>   |   |
| <ul style="list-style-type: none"> <li>• up to 60 °C, max.</li> </ul>   | 6 A; total current DQ + additional current for analog channels  |
| <b>Power loss</b>   |   |
| Power loss, typ.  | 6.6 W; RJ45 BusAdapter, 8xDI, 4xAI, 2xAQ, 2xDQ with 12 ohms load each   |
| <b>Address area</b>   |   |
| Address space per station   |   |
| <ul style="list-style-type: none"> <li>• Address space per station, max.</li> </ul>   | 1 440 byte; Dependent on configuration  |
| <b>Digital inputs</b>   |   |
| Number of digital inputs  | 16  |
| Digital inputs, parameterizable   | Yes   |
| Sourcing/sinking input  | Yes   |
| Input characteristic curve in accordance with IEC 61131, type 1   | Yes   |
| Input characteristic curve in accordance with IEC 61131, type 2   | No  |
| Input characteristic curve in accordance with IEC 61131, type 3   | Yes   |
| Pulse extension   | Yes; off, 50 ms, 100 ms, 200 ms, 500 ms, 1 s, 2 s   |
| <b>Digital input functions, parameterizable</b>   |   |
| <ul style="list-style-type: none"> <li>• Gate start/stop</li> <li>• Freely usable digital input</li> <li>• Counter <ul style="list-style-type: none"> <li>— Number, max.</li> <li>— Counting frequency, max.</li> <li>— Counting width</li> <li>— Counting direction up/down</li> </ul> </li> </ul> | <ul style="list-style-type: none"> <li>Yes; hardware gate, usable by multiple DI counters</li> <li>Yes; Parameterizable input filter</li> <li>Yes</li> <li>16</li> <li>5 kHz; fast counter mode, sinking input; 1 kHz for sourcing input, NAMUR</li> <li>32 bit</li> <li>Yes; Up</li> </ul> |
| <b>Input voltage</b>  |   |
| <ul style="list-style-type: none"> <li>• Rated value (DC)</li> <li>• for signal "0"</li> <li>• for signal "1"</li> <li>• permissible voltage at input, min.</li> <li>• permissible voltage at input, max.</li> </ul>  | <ul style="list-style-type: none"> <li>24 V</li> <li>-9 V to +5 V</li> <li>+11 to +30V</li> <li>-9 V</li> <li>30 V</li> </ul>   |
| <b>Input current</b>  |   |
| <ul style="list-style-type: none"> <li>• for signal "1", typ.</li> </ul>  | 2.5 mA; max: 2.5 mA sourcing input; 2.3 mA sinking input; 10 mA fast counter; 6.5 mA NAMUR  |
| <b>Input delay (for rated value of input voltage)</b>   |   |
| for standard inputs   |   |
| <ul style="list-style-type: none"> <li>— parameterizable</li> </ul>   | Yes; none / 0.05 / 0.1 / 0.2 / 0.4 / 0.8 / 1.6 / 3.2 / 12.8 / 20 ms   |
| <b>Cable length</b>   |   |
| <ul style="list-style-type: none"> <li>• shielded, max.</li> <li>• unshielded, max.</li> </ul>  | <ul style="list-style-type: none"> <li>1 000 m</li> <li>600 m</li> </ul>  |
| <b>Digital outputs</b>  |   |
| Type of digital output  | Transistor  |
| Number of digital outputs   | 16  |
| Current-sinking   | No  |
| Current-sourcing  | Yes   |
| Short-circuit protection  | Yes   |
| <ul style="list-style-type: none"> <li>• Response threshold, typ.</li> </ul>  | 4.1 A   |
| Open-circuit detection  | Yes   |
| Overload protection   | Yes   |
| Limitation of inductive shutdown voltage to   | typ. L+ (-11 V)   |
| Controlling a digital input   | Yes   |

|  |  |
|--|--|
| <b>Switching capacity of the outputs</b>         |  |
| • with resistive load, max.                      | 2 A  |
| • on lamp load, max.                             | 5 W  |
| <b>Load resistance range</b>                     |  |
| • lower limit                                    | 12 Ω   |
| • upper limit                                    | 12 kΩ  |
| <b>Output voltage</b>                            |  |
| • Type of output voltage                         | DC   |
| • for signal "1", min.                           | U <sub>e</sub> minus 1 V                       |
| <b>Output current</b>                            |  |
| • for signal "1" rated value                     | 2 A  |
| • for signal "0" residual current, max.          | 0.1 mA   |
| <b>Output delay with resistive load</b>          |  |
| • "0" to "1", typ.                               | 50 μs  |
| • "0" to "1", max.                               | 100 μs   |
| • "1" to "0", typ.                               | 50 μs  |
| • "1" to "0", max.                               | 100 μs   |
| <b>Parallel switching of two outputs</b>         |  |
| • for uprating                                   | No   |
| • for redundant control of a load                | No   |
| <b>Switching frequency</b>                       |  |
| • with resistive load, max.                      | 100 Hz   |
| • with inductive load, max.                      | 1 Hz; at 2 A; 2 Hz at 0.5 A                    |
| • on lamp load, max.                             | 10 Hz  |
| <b>Total current of the outputs</b>              |  |
| • Current per channel, max.                      | 2 A  |
| <b>horizontal installation</b>                   |  |
| — up to 60 °C, max.                              | 6 A  |
| <b>vertical installation</b>                     |  |
| — up to 60 °C, max.                              | 6 A  |
| <b>Cable length</b>                              |  |
| • shielded, max.                                 | 1 000 m  |
| • unshielded, max.                               | 600 m  |
| <b>Analog inputs</b>                             |  |
| Number of analog inputs                          | 16   |
| <b>Input ranges (rated values), currents</b>     |  |
| • 0 to 20 mA                                     | Yes; 16 bit incl. sign                         |
| — Input resistance (0 to 20 mA)                  | 233 Ω  |
| • 4 mA to 20 mA                                  | Yes; 16 bit incl. sign                         |
| — Input resistance (4 mA to 20 mA)               | 233 Ω  |
| <b>HART communication</b>                        |  |
| • Primary Master                                 | Yes  |
| • input resistance (with HART communication)     | 233 Ω  |
| <b>Cable length</b>                              |  |
| • shielded, max.                                 | 1 000 m  |
| • unshielded, max.                               | 600 m  |
| <b>Analog outputs</b>                            |  |
| Number of analog outputs                         | 16; short-circuit proof with respect to ground |
| Current output, no-load voltage, max.            | 24 V   |
| <b>Output ranges, current</b>                    |  |
| • 0 to 20 mA                                     | Yes; 15 bit                                    |
| • -20 mA to +20 mA                               | No   |
| • 4 mA to 20 mA                                  | Yes; 16 bit incl. sign                         |
| <b>Connection of actuators</b>                   |  |
| • for current output two-wire connection         | Yes  |
| <b>Load impedance (in rated range of output)</b> |  |
| • for current outputs, min.                      | 50 Ω   |
| • with current outputs, max.                     | 750 Ω  |
| • with current outputs, inductive load, max.     | 10 mH  |

|  |   |
|--|---|
| <b>Destruction limits against externally applied voltages and currents</b> |   |
| • Voltages at the outputs  | 36 V; Minus 0.3 V lower limit                       |
| <b>Cable length</b>  |   |
| • shielded, max.   | 1 000 m   |
| • unshielded, max.   | 600 m   |
| <b>Analog value generation for the inputs</b>                              |   |
| Measurement principle  | integrating (Sigma-Delta)                           |
| <b>Integration and conversion time/resolution per channel</b>              |   |
| • Resolution with overrange (bit including sign), max.                     | 16 bit  |
| • Integration time, parameterizable  | Yes; channel by channel                             |
| <b>Smoothing of measured values</b>  |   |
| • parameterizable  | Yes; none, weak, medium, strong, channel-by-channel |
| <b>Analog value generation for the outputs</b>                             |   |
| <b>Settling time</b>   |   |
| • for resistive load   | 2 ms; 750 ohm                                       |
| • for inductive load   | 1.2 ms  |
| <b>Encoder</b>   |   |
| <b>Connection of signal encoders</b>                                       |   |
| • for current measurement as 2-wire transducer                             | Yes   |
| <b>Connectable encoders</b>  |   |
| • NAMUR encoder/changeover contact according to EN 60947                   | Yes; no CO contact                                  |
| • 2-wire sensor  | Yes   |
| — permissible quiescent current (2-wire sensor), max.                      | 1.5 mA  |
| <b>Errors/accuracies</b>   |   |
| Linearity error (relative to input range), (+/-)                           | 0.05 %  |
| Temperature error (relative to input range), (+/-)                         | 0.005 %/K   |
| Crosstalk between the inputs, min.   | 60 dB   |
| Repeat accuracy in steady state at 25 °C (relative to input range), (+/-)  | 0.05 %  |
| Linearity error (relative to output range), (+/-)                          | 0.02 %  |
| Temperature error (relative to output range), (+/-)                        | 0.003 %/K   |
| Crosstalk between the outputs, min.  | 70 dB   |
| Repeat accuracy in steady state at 25 °C (relative to output range), (+/-) | 0.02 %  |
| <b>Operational error limit in overall temperature range</b>                |   |
| • Current, relative to input range, (+/-)                                  | 0.5 %   |
| • Current, relative to output range, (+/-)                                 | 0.5 %; 0 ... 60 °C: 0.2 %                           |
| <b>Basic error limit (operational limit at 25 °C)</b>                      |   |
| • Current, relative to input range, (+/-)                                  | 0.1 %   |
| • Current, relative to output range, (+/-)                                 | 0.1 %   |
| <b>Interfaces</b>  |   |
| Number of PROFINET interfaces  | 1   |
| <b>1. Interface</b>  |   |
| Interface type   | PROFINET  |
| Isolated   | Yes   |
| <b>Interface types</b>   |   |
| • Number of ports  | 2; via BusAdapter                                   |
| • integrated switch  | Yes   |
| • BusAdapter (PROFINET)  | Yes   |
| <b>Protocols</b>   |   |
| • PROFINET IO Device   | Yes   |
| • Media redundancy   | Yes; as MRP client                                  |
| <b>Interface types</b>   |   |
| <b>RJ 45 (Ethernet)</b>  |   |
| • 100 Mbps   | Yes   |
| • Autonegotiation  | Yes   |
| • Autocrossing   | Yes   |
| <b>Protocols</b>   |   |

|  |   |
|--|---|
| Supports protocol for PROFINET IO                              | Yes   |
| HART protocol  | Yes   |
| • Protocol version   | up to Revision 7  |
| <b>PROFINET IO Device</b>                                      |   |
| <b>Services</b>  |   |
| — Shared device  | No  |
| <b>Redundancy mode</b>   |   |
| • PROFINET system redundancy (S2)                              | Yes   |
| <b>Media redundancy</b>  |   |
| — MRP  | Yes   |
| <b>Open IE communication</b>                                   |   |
| • LLDP   | Yes   |
| <b>Interrupts/diagnostics/status information</b>               |   |
| Status indicator   | Yes   |
| Alarms   | Yes   |
| Diagnostics function   | Yes   |
| Substitute values connectable                                  | Yes   |
| <b>Alarms</b>  |   |
| • Diagnostic alarm   | Yes   |
| • Maintenance interrupt  | Yes   |
| • Limit value alarm  | Yes   |
| • Hardware interrupt   | Yes   |
| <b>Diagnoses</b>   |   |
| • Monitoring the supply voltage                                | Yes   |
| • Wire-break   | Yes; channel by channel   |
| • Short-circuit  | Yes; channel by channel   |
| • Group error  | Yes   |
| • Overflow/underflow   | Yes; channel by channel   |
| <b>Diagnostics indication LED</b>                              |   |
| • RUN LED  | Yes; green LED  |
| • ERROR LED  | Yes; red LED  |
| • MAINT LED  | Yes; Yellow LED   |
| • Monitoring of the supply voltage (PWR-LED)                   | Yes; green/red LED  |
| • Channel status display                                       | Yes; green/red LED  |
| • Status indicator digital input (green)                       | Yes   |
| • Status indicator digital output (green)                      | Yes   |
| • Connection display LINK TX/RX                                | Yes; 2x green link LEDs on BusAdapter                                 |
| <b>Integrated Functions</b>                                    |   |
| Frequency measurement  | Yes   |
| • Number of frequency meters                                   | 16  |
| <b>Counting functions</b>                                      |   |
| • Continuous counting  | Yes   |
| • Counter response parameterizable                             | Yes   |
| • Hardware gate via digital input                              | Yes   |
| • Software gate  | Yes   |
| <b>Measuring functions</b>                                     |   |
| • Dynamic measurement period adjustment                        | Yes   |
| <b>Measuring range</b>   |   |
| — Frequency measurement, min.                                  | 0.1 Hz  |
| — Frequency measurement, max.                                  | 25 kHz; fast counter mode, sinking input; 1 kHz sourcing input, NAMUR |
| <b>Accuracy</b>  |   |
| — Frequency measurement  | 100 ppm; depending on measuring interval and signal evaluation        |
| <b>Potential separation</b>                                    |   |
| <b>Potential separation digital inputs</b>                     |   |
| • between the channels   | No  |
| • between the channels and the power supply of the electronics | No  |
| <b>Potential separation digital outputs</b>                    |   |
| • between the channels   | No  |

• between the channels and the power supply of the electronics

No

**Isolation**

Isolation tested with 1 500 V AC between PROFINET and other electronics

**Degree and class of protection**

IP degree of protection IP66

**Ambient conditions**

Ambient temperature during operation

- horizontal installation, min. -40 °C
- horizontal installation, max. 60 °C; Observe derating
- vertical installation, min. -40 °C
- vertical installation, max. 60 °C; Observe derating

Ambient temperature during storage/transportation

- min. -40 °C
- max. 70 °C

Relative humidity

- Operation, max. 95 %

**Connection method**

Design of electrical connection Connection plug

**Dimensions**

Width 414 mm

Height 266 mm

Depth 111 mm

**Weights**

Weight, approx. 5.5 kg

**Classifications**

|        | Version | Classification |
|--------|---------|----------------|
| eClass | 14      | 27-24-26-90    |
| eClass | 12      | 27-24-26-90    |
| eClass | 9.1     | 27-24-26-90    |
| eClass | 9       | 27-24-26-90    |
| eClass | 8       | 27-24-92-90    |
| eClass | 7.1     | 27-24-92-90    |
| eClass | 6       | 27-24-92-90    |
| ETIM   | 10      | EC002584       |
| ETIM   | 9       | EC002584       |
| ETIM   | 8       | EC002584       |
| ETIM   | 7       | EC002584       |

**Approvals / Certificates**

General Product Approval EMV For use in hazardous locations



[Type Examination Certificate](#)

For use in hazardous locations Environment



last modified: 10/23/2025