

FEATURES

- **Sintered Bronze Material:** Provides excellent durability and resistance to wear, ensuring a long service life.
- **Flanged Design:** Offers additional support and stability, making it suitable for axial loads.
- **Dynamic Load Rating of 14 N/mm²:** Ensures efficient performance under varying load conditions.
- **Static Load Rating of 50 N/mm²:** Capable of handling high static loads, enhancing reliability.
- **0.37 in Bore Size:** Suitable for a wide range of shaft diameters, offering versatility in application.
- **0.62 in Outside Diameter:** Compatible with standard housing sizes for easy integration.
- **1/2 in Width:** Provides a compact solution for space-constrained applications.

RS PRO 0.37 in Flanged Plain Bearing

RS Stock No: 528-912



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

The RS PRO 0.37 in Flanged Plain Bearing is designed for applications requiring reliable and efficient rotational movement. Made from high-quality sintered bronze, this bearing is ideal for reducing friction and wear in mechanical systems, ensuring longevity and performance.

General Specifications

Bore Size	0.37 in
Dynamic Load Rating	14 N/mm ²
Product Type	Plain Bearing
Static Load Rating	50 N/mm ²
Sub Type	Flanged

Mechanical Specifications

Material	Sintered Bronze
Outside Diameter	0.62 in
Width	1/2 in

Approvals

Standards/Approvals	ISO 9001:2008, UKAS 001
---------------------	-------------------------