


Product data sheet

Specifications

Repacked, Cover frame, Odace Touch, 3 gangs, white



S520806W



This repacked option saves 0.247 over the standard condition

Main

Range	Odace
Product or component type	Cover frame
Aesthetic name	Touch
Installation direction	Horizontal/vertical
Distance between centers	71 mm
Colour tint	White (RAL 9003)
Type of packing	Flow-pack
Type of frame	Triple
Number of gangs	3 gangs

Complementary

Device mounting	Flush
fixing mode	Clip-in
Surface finish	Glossy
Material	Thermoplastic ABS-UV stabilised: decorative frame
Height	85 mm
Width	227 mm
Depth	10 mm
Product weight	0.03601 kg
IK degree of protection	IK04
IP degree of protection	IP21D
resistance to chemical agents	Resistant to alcohol (70 %) Resistant to alcohol (96 %) Resistant to A-Lactic Acid Resistant to diluted quaternary ammonium Resistant to diluted bleach Resistant to diluted ammonia Resistant to soapy water Resistant to crystal cleaner Resistant to hydrogen peroxide 10 volumes Resistant to hexane

Environment

Ambient air temperature for storage	-5...50 °C
Product certifications	AENOR: 030/2205 LCIE: NF 603415A N NF

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Ambient air temperature for operation	5...45 °C
Standards	2006/95/EEC UNE 20315-1-1 EN 60669-1 NF C 61-314 NBN C 61-112-1

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.000 cm
Package 1 Width	9.000 cm
Package 1 Length	23.000 cm
Package 1 Weight	40.000 g
Unit Type of Package 2	S01
Number of Units in Package 2	15
Package 2 Height	15.000 cm
Package 2 Width	15.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	788.000 g

Contractual warranty

Warranty (in months)	18
----------------------	----



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)



Environmental footprint

Lower carbon footprint

0.2 kg CO2 eq.

Use Better



Materials and Substances

SCIP Number

59bc1733-7007-4ba6-bfd5-f7904c7d9a13

EU RoHS Directive

[Compliant](#)

REACH Regulation

[Reference contains Substances of Very High Concern above the threshold](#)

Use Longer



Lifetime extension

Repair

No

Use Again



Repack and remanufacture

Take-back

No