

M12 X-coded Cable Assembly 11,0 m



Image is for illustration purposes only. Please refer to product description.

Part number	21 33 050 5810 110
Specification	M12 X-coded Cable Assembly 11,0 m
HARTING eCatalogue	https://harting.com/21330505810110

Identification

Category	System cabling
Series	Circular connectors M12
Element	Cable assemblies
Specification	Pre-assembled on both sides
Connector 1	M12 X-coding Male Straight Press&Go
Connector 2	M12 X-coding Male Straight Press&Go
Type of cable	Copper cable (round)

Version

Cable length	11 m
Number of cores	8
Core structure	4x 2x AWG 26/7
Shielding	Shielded
Coding	X-coding

Technical characteristics

Transmission characteristics	Cat. 6 _A Class E _A up to 500 MHz
------------------------------	--



Pushing Performance
Since 1945

Technical characteristics

Data rate	10 Mbit/s
	100 Mbit/s
	1 Gbit/s
	2.5 Gbit/s
	5 Gbit/s
	10 Gbit/s
Limiting temperature	-40 ... +80 °C moved
	-40 ... +80 °C unmoved
Cable diameter	6.7 mm ± 0.3 mm

Material properties

Material (cable)	PUR (polyurethane)
Colour (cable)	Yellow
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel

Specifications and approvals

Specifications	UN/ECE-R 118 fire protection for rolling stock
----------------	--

Commercial data

Packaging size	1
Net weight	600 g
Country of origin	Romania
European customs tariff number	85444290
GTIN	5713140248748
eCl@ss	27060390 Ready-made data cable (unspecified)
ETIM	EC002599