

Samsung USB Flash Drive : DUO Plus Lineup

2018 Data Sheet

Revision 1.0



DISCLAIMER

SAMSUNG ELECTRONICS RESERVES THE RIGHT TO CHANGE PRODUCTS, INFORMATION AND SPECIFICATIONS WITHOUT NOTICE.

Products and specifications discussed herein are for reference purposes only. All information discussed herein may change without notice and is provided on an "AS IS" basis, without warranties of any kind. This document and all information discussed herein remain the sole and exclusive property of Samsung Electronics. No license of any patent, copyright, mask work, trademark or any other intellectual property right is granted by one party to the other party under this document, by implication, estoppels or otherwise. Samsung products are not intended for use in life support, critical care, medical, safety equipment, or similar applications where product failure could result in loss of life or personal or physical harm, or any military or defense application, or any governmental procurement to which special terms or provisions may apply. For updates or additional information about Samsung products, contact your nearest Samsung office (www.samsung.com/USB).

COPYRIGHT © 2018

This material is copyrighted by Samsung Electronics. Any unauthorized reproductions, use or disclosure of this material, or any part thereof, is strictly prohibited and is a violation under copyright law. All other marks are property of their respective owners.

1. INTRODUCTION

Samsung's UFD (USB Flash Drive) is a USB 3.1 mass storage media that provides remarkable performance, outstanding reliability and minimalistic design in anticipation of tomorrow's memory needs. Samsung's UFD assorted high capacity and performance can store the data that the user wants to keep safely and quickly. For an easy adoption, Samsung's UFD is operable with modern operation systems such as Windows, Mac OS, Linux and other systems. And it is compatible with any device that uses a USB-C & USB-A Port. It also supports backward compatibility with USB 3.0 and USB 2.0.

2. PRODUCT LINEUP

Lineup	Design Option	Density	Model Name
DUO Plus	Standard	32GB	MUF-32DB
		64GB	MUF-64DB
		128GB	MUF-128DB
		256GB	MUF-256DB


3. PRODUCT FEATURE

- Compliance with USB 3.1 Specification
 - Bus Speed supports Super Speed mode (Up to 5Gbps)
 - Compliant with USB Mass Storage Class Specification
- Backwards Compatibility
 - Compatible with USB 3.0 and USB 2.0 systems
 - Bus Speed supports High Speed and Full Speed mode
- Dimensions
 - 57.9mm X 18.3mm X 7.3mm, Approx. 7.7g
- Performance
 - Read speed up to 200MB/s(32GB~64GB) and 300MB/s(128GB~256GB)
- Temperature
 - Operation : 0~60°C
 - Non-operation : -10~70°C
- System Requirements
 - Windows 10, Windows 8, Windows 7, Windows Vista, Windows XP, Windows 2000
 - Mac OS ver. 10.4 or later
 - Linux ver. 2.4 or later
 - Android 4.0 or later
- Support Plug and Play function

4. PRODUCT PERFORMANCE

Density	USB Interface	Sequential Read	Sequential Write
32GB	USB 3.1	Up to 200 MB/s	Up to 30MB/s
64GB	USB 3.1	Up to 200 MB/s	Up to 30MB/s
128GB	USB 3.1	Up to 300 MB/s	Up to 50MB/s
256GB	USB 3.1	Up to 300 MB/s	Up to 80MB/s

Performance measurement is based on Samsung's internal testing conditions.
The read/write speed may vary among different host devices and testing conditions.
Connect the USB Type-A Standard Adapter as described in the picture for use as USB 3.1.



5. USER CAPACITY

Density	User Capacity
32GB	32,063,307,776
64GB	64,157,122,560
128GB	128,315,424,768
256GB	256,632,029,184

Product user capacity is measured on Windows 7 with FAT File system.
User capacity can be different depending on the OS and PC environment.
1GB=1,000,000,000 bytes. The actual usable capacity may be less than the labeled capacity.

6. PHYSICAL SPECIFICATIONS

Specifications	
Dimensions	57.9 X 18.3 X 7.3 (mm) / 2.28 x 0.72 x 0.29 (in)
Weights	Approx. 7.7g / 0.27oz
Temperature	Operating : 0°C to 60°C Non-Operating : -10°C to 70°C
Water	1m depth 3% NaCl salt water, 72hrs
Shock	Acceleration :1,500 g (gravity), Shock times : 3 times/x,y,z direction
X-Ray	80KV, 50uA, 4W, 500 sec Radiation time.
Magnet	15,000 G (Gauss) ¹⁾
EMC Certifications	KC, FCC, CE, VCCI, RCM
Warranty	5 years limited ²⁾

1) MRI (Magnetic Resonance Imaging): 5,000~15,000 Gauss

2) For more detailed warranty information, please visit www.samsung.com/support.

7. REVISION HISTORY

Date	Revision	Description
June. 2018	1.0	Initial release