

# E/P pressure regulator, Series ED05

R414002007


Series  
ED05

2025-05-09

- Tailored, on-demand pressure control
- Robust poppet valve technology guarantees a long service life
- High flow for a wide range of tasks
- Highly dynamic direct acting technology
- No wearable pilot valves or diaphragm
- Various electrical connection options

## Series ED05

The AVENTICS ED05 direct-acting pressure regulator ensures sensitive pressure control by combining digital control electronics with innovative proportional technology. The robust poppet valve technology, a large opening cross-section and the use of a soft-sealing valve seat make the valve highly resistant to contamination.



## Technical data

Type	Current control with actual output value
Control	Directly controlled
Control	Analog
Function	Air exhaust
Output signal	Analog
Operational voltage DC	24 V
Actual output value	0 ... 20 mA
Nominal input value	0 ... 20 mA
Min. regulation range	0 bar
Max. regulation range	10 bar
Min. working pressure	0 bar
Max. working pressure	11 bar
Hysteresis	< 0,06 bar
Medium	Compressed air
Nominal flow Qn	1000 l/min
Min. ambient temperature	0 °C
Max. ambient temperature	70 °C
Min. medium temperature	0 °C
Max. medium temperature	70 °C

# E/P pressure regulator, Series ED05

R414002007

Series  
ED05

2025-05-09

Protection class	IP65
Permissible ripple	5%
Max. particle size	50 µm
Min. oil content of compressed air	0 mg/m <sup>3</sup>
Max. oil content of compressed air	1 mg/m <sup>3</sup>
Type	Poppet valve
Mounting orientation	$\alpha = 0-90^\circ$ $\beta = 0-90^\circ$
Certificates	CE declaration of conformity
Compressed air connection input	G 1/4
Compressed air connection output	G 1/4
Compressed air connection, exhaust	G 1/4
Electrical connection size	via signal connection
Signal connection	input and output
Signal connection	Plug
Signal connection	M12
Signal connection	5-pin
Industry	Industrial
Weight	0.95 kg

## Material

Housing material	Die-cast aluminum Steel, chrome-plated
Seal material	Hydrogenated acrylonitrile butadiene rubber
Part No.	R414002007

## Technical information

With oil-free, dry air, other installation positions are possible on request.

The protection class is only ensured when the plug is mounted properly. For detailed information, see operating instructions.

The min. control pressure must be adhered to, since otherwise faulty switching and valve failure may result!

The pressure dew point must be at least 15 °C less than ambient and medium temperature and may not exceed 3 °C.

The oil content of compressed air must remain constant during the life cycle.

Use only the approved oils from AVENTICS. Further information can be found in the "Technical information" document (available in <https://www.emerson.com/en-us/support>).


# E/P pressure regulator, Series ED05

R414002007

Series  
ED05


2025-05-09

## Dimensions




- 1) Core hole 15 mm deep for self-tapping screws M6
- 2) Universal threaded connection, suitable for G1/4 according to ISO 228/1:2000 and 1/4-27 NPTF
- 3) Through hole

## Functional diagram



- a) Nominal input value b) Actual output value The E/P pressure control valve modulates the pressure corresponding to an analog electrical nominal input value.
- 1) Operating pressure
- 2) Working pressure
- 3) Exhaust

## Characteristic and pin assignment for current control with actual output value




1) Operational voltage

2) Actual value (pin 4) and nominal value (pin 2) are related to 0 V (control voltage). Nominal input value current (ohmic load 100  $\Omega$ ). Actual output value (max. total resistance of downstream devices < 300  $\Omega$ ).

3) The operating voltage must be protected by an external M 1.6 A fuse. Connect plug 2 via a shielded cable to ensure EMC.

## Durchflussdiagramm für Druckbereich bis 10 bar



$P_v$  = Supply pressure

Connect the plug via a shielded cable to ensure EMC