




Connectors > PCB Connectors > Backplane Connectors > Eurocard Connectors



Circuit Application: **Signal**

Operating Temperature Range: -55 – 125 °C [-67 – 257 °F]

Features

Contact Features

Contact Mating Area Plating Material	Gold Flash over Palladium Nickel
Contact Base Material	Copper Alloy
Contact Type	Receptacle

Usage Conditions

Operating Temperature Range	-55 – 125 °C[-67 – 257 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Signal
---------------------	--------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Not Yet Reviewed for halogen content



Solder Process Capability

Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 024104-E
STVBUG C/2 48 CSI 172 9999 * J 2 484269



TE Part # 024069-E
STVBUG C 96 CSI 172 9999 * J 4 24069 FED




TE Part # 471555-E
VORCSI ENTRIEGELUNGSWERKZ. CSI-KONT. J 3



TE Part # 024070-E
STVBUG E 160 CSI 172 9999 * J 4 24070 FE

Customers Also Bought




TE Part #811465-000
462A421-50-0




TE Part #CAT-R21-7310654
Heat Shrink Boots: Non Lipped, Right Angle



TE Part #7710110001
D-SCE-9.5-50-4



TE Part #2176453-5
CPF 0201 6K34 0.1% 25ppm 1K RL




TE Part #811458-000
381A301-50-0



TE Part #5-2371899-3
PCIE G5 CONN,98P,ASSY,SLOT CUT, 30u,HT



TE Part #024070-E
STVBUG E 160 CSI 172 9999 * J 4 24070 FE



TE Part #6-2176452-8
CPF 0201 2K67 0.1% 25ppm 1K RL



Documents

Product Drawings

STVROL BUT 500 CSI 2026 207 * AL J 2 340

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_234063-E_L.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_234063-E_L.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_234063-E_L.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Product Specification

English