









TERMINAL PART NO	WIRE AWG	DIM A	DIM B	DIM C	DIM D
2043010001	22-24 AWG	1.36	2.35	0.90	1.88
2043010002	26 AWG	1.36	2.35	0.68	1.30

NOTES:

- MATERIAL: COPPER ALLOY
- FINISH:
 - 2.5µm MIN OVERALL ELECTROPLATE MATTE TIN OVER
 - 1.25µm MIN OVERALL ELECTROPLATED MATTE NICKEL
- PRODUCT SPECIFICATION: 2042200000-PS
- APPLICATION SPECIFICATION: 2042200000-AS
- PACKAGING SPECIFICATION: 2043010000-PK
- THIS CRIMP TERMINAL TO BE USED WITH ASSEMBLY SERIES 204220.
- THIS CRIMP TERMINAL MATES WITH RECEPTACLE CRIMP TERMINAL SERIES 2042261.
- THIS PART CONFORMS TO CLASS 'B' REQUIREMENTS OF COSMETIC SPECIFICATION PS-45499-002.
- WIRE SPECIFICATIONS:
 - AWG: 22 and 26 awg
 - INSULATION OD RANGE: 0.95mm - 1.4mm
- CRIMP TOOLING:
 - APPLICATOR PART NUMBER: REFER 2042200000-PS
 - HAND TOOL PART NUMBER: REFER 2042200000-PS

FUNCTIONAL SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION														
FA = 0 FC = 0 FP = 0	DIMENSION UNITS		SCALE		CURRENT REV DESC:			molex							
	mm		15:1												
	GENERAL TOLERANCES (UNLESS SPECIFIED)							EC NO: 814601 DRWN: MEGHRB 2024/10/22 CHK'D: MEGHRB 2025/03/07 APPR: ISHWARG 2025/03/10			RECEPTACLE CRIMP TERMINAL SQUBA 1.8				
ANGULAR TOL ± °															
DIVISIONAL SYMBOLS	4 PLACES		±		INITIAL REVISION: DRWN: TGREGORI 2018/01/03 APPR: RHODGE 2018/01/26						DOCUMENT NUMBER			DOC TYPE	DOC PART
	3 PLACES		±					2043010000-SD			PSD	000	A3		
	2 PLACES		±												
	1 PLACE		± 0.2												
	0 PLACES		±												
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				THIRD ANGLE PROJECTION		DRAWING		SERIES		MATERIAL NUMBER		CUSTOMER		SHEET NUMBER	
						D-SIZE		204301		2043010001		GENERAL MARKET		1 OF 1	

DOCUMENT STATUS	P1	RELEASE DATE	2025/03/10	09:33:00
-----------------	----	--------------	------------	----------