



Main

Commercial Status	Commercialised
Range of product	Zelio Relay
Series name	Miniature
Product or component type	Plug-in relay
Device short name	RXM
Contacts type and composition	4 C/O
Control circuit voltage	110 V DC
[Ithe] conventional enclosed thermal current	3 A at -40...55 °C
Status LED	With
Control type	Pushbutton
Utilisation coefficient	20 %

Complementary

Shape of pin	Flat
[Ui] rated insulation voltage	300 V conforming to UL 300 V conforming to CSA 250 V conforming to IEC
[Uimp] rated impulse withstand voltage	2.5 kV for 1.2/50 µs
Contacts material	Gold plated bifurcated silver
[Ie] rated operational current	3 A at 277 V AC conforming to UL 3 A at 28 V DC conforming to UL 1 A at 250 V AC (NC) conforming to IEC 1 A at 28 V DC (NC) conforming to IEC 2 A at 250 V AC (NO) conforming to IEC 2 A at 28 V DC (NO) conforming to IEC
Maximum switching voltage	250 V conforming to IEC
Resistive rated load	3 A at 28 V DC 3 A at 250 V AC
Maximum switching capacity	750 VA/84 W
Minimum switching capacity	15 mW at 3 mA, 5 V
Operating rate	<= 18000 cycles/hour no-load <= 1200 cycles/hour under load
Mechanical durability	10000000 cycles
Electrical durability	100000 cycles for resistive load depending on mounting position and working environment
Average coil consumption in W	0.9 W
Drop-out voltage threshold	>= 0.1 Uc
Operate time	20 ms
Release time	20 ms
Average coil resistance	13440 Ohm at 20 °C +/- 10 %
Rated operational voltage limits	88...121 V DC
Protection category	RT I
Operating position	Any position
Product weight	0.037 kg

Environment



Dielectric strength	2000 V AC between poles with basic insulation 2000 V AC between coil and contact with reinforced insulation 1300 V AC between contacts with micro disconnection insulation
Product certifications	CE CSA GOST RoHS UL REACH Lloyd's
Standards	EN/IEC 61810-1 UL 508 CSA C22.2 No 14
Ambient air temperature for storage	-40...85 °C
Ambient air temperature for operation	-40...55 °C
Vibration resistance	5 gn (f = 10...150 Hz), amplitude +/- 1 mm (on 5 cycles not operating) 3 gn (f = 10...150 Hz), amplitude +/- 1 mm (on 5 cycles in operation)
IP degree of protection	IP40 conforming to EN/IEC 60529
Shock resistance	30 gn not operating 10 gn in operation
Pollution degree	2

The technical drawing shows two views of the M6000-1000 module. The left view is a side profile showing a width of 7.7 mm (0.30 in.) for the mounting tab, a main body width of 40 mm (1.57 in.), and a rear flange width of 6 mm (0.23 in.). The right view is a top-down perspective showing a total length of 63 mm (2.48 in.), with segments of 16 mm (0.63 in.), 34 mm (1.34 in.), and 9 mm (0.35 in.). It also shows a depth of 27 mm (1.06 in.) and a central cutout width of 21 mm (0.82 in.).

Technical drawing of a mechanical part with dimensions in mm and in. The drawing shows a cross-section of a part with a central rectangular feature. The dimensions are as follows:

- Top horizontal dimensions: 4.4 (0.17), 4.6 (0.18), 4.4 (0.17).
- Bottom horizontal dimensions: 2.5 (0.9), 4.4 (0.17), 2.5 (0.9).
- Bottom horizontal dimensions (total): 13.2 (0.51).

Wiring Diagram




Symbols shown in blue correspond to Nema marking.

Electrical Durability of Contacts


Durability (inductive load) = durability (resistive load) x reduction coefficient.

Resistive AC load




- X Switching capacity (kVA)
Y Durability (Number of operating cycles)
A RXM2AB...
B RXM3AB...
C RXM4AB...
D RXM4GB...

Reduction coefficient for inductive AC load (depending on power factor $\cos \phi$)



- Y Reduction coefficient (A)

Maximum switching capacity on resistive DC load



- X Voltage DC
Y Current DC
A RXM2AB...
B RXM3AB...
C RXM4AB...
D RXM4GB...

Note : These are typical curves, actual durability depends on load, environment, duty cycle, etc.