

## Bi-Metalloy® Hand Hacksaw Blades



### Standard Packs

- Molybdenum alloy tool steel edge
- Tough flexible high carbon steel backing
- Lasts twice as long as high-speed steel
- Lasts up to ten times longer than carbon steel
- Operates 20% to 50% faster
- High tooth hardness and shock resistance
- Boxed: 100 blades per box

Type	Set Type	Code No.	Length		Teeth Per Inch	Width		Gauge		Weight per 100 Boxed kg
			Inch	mm		Inch	mm	Inch	mm	
NF1218	Wavy	62723	12	304	18	1/2	12,70	0,025	0,65	2,050
NF1224	Wavy	62749	12	304	24	1/2	12,70	0,025	0,65	2,050
NF1232	Wavy	62776	12	304	32	1/2	12,70	0,025	0,65	2,050

## Solid Flexible Carbon Steel



- Solid high carbon steel
- Tempered to provide hard edge with flexible back
- Specially hardened to induce toughness
- Economy blade for sawing light to medium-hard materials
- A good balance of wear resistance and mechanical shock absorbing properties
- Virtually unbreakable
- Boxed: 100 blades per box

Type	Set Type	Code No.	Length		Teeth Per Inch	Width		Gauge		Weight per 100 Boxed kg
			Inch	mm		Inch	mm	Inch	mm	
MH1812	Wavy	0023151812	12	304	18	1/2	12,70	0,025	0,65	2,050
MH2412	Wavy	0023152412	12	304	24	1/2	12,70	0,025	0,65	2,050
MH3212	Wavy	0023153212	12	304	32	1/2	12,70	0,025	0,65	2,050