




PRODUCT DATASHEET

Datasheet creation date: 2025/06/02 9:27 (UTC)

MOTION & CONTROL
NSK



NJ2210ET

Single-Row Cylindrical Roller Bearings

Boundary Dimensions


d	50	mm	Bore diameter
D	90	mm	Outside diameter
B	23	mm	Width
FW	59.5	mm	Raceway diameter of inner ring
r (min.)	1.1	mm	Chamfer dimension
r1 (min.)	1.1	mm	Chamfer dimension

Basic Load Ratings

Cr	102000	N	Basic dynamic load rating
C0r	97000	N	Basic static load rating

Speeds

Thermal Speed Rating (Oil-bath)	7500	min-1	Oil-bath lubrication subject to conditions outlined in ISO 15312
Mechanical (forced-circulation oil)	9000	min-1	Properly designed and controlled forced-circulation oil lubrication
Grease	6300	min-1	Grease lubrication
Oil (Oil-bath)	8000	min-1	Oil-bath lubrication



Abutment and Fillet Dimensions

da (min.)	56.5	mm	Diameter of shaft abutment
db (min.)	56.5	mm	Diameter of shaft / spacer sleeve abutment
db (max.)	57	mm	Diameter of shaft / spacer sleeve abutment
dc (min.)	62	mm	Diameter of shaft abutment
dd (min.)	67	mm	Diameter of shaft abutment
Da (max.)	83.5	mm	Diameter of housing abutment
ra (max.)	1	mm	Radius of shaft or housing fillet
rb (max.)	1	mm	Radius of shaft or housing fillet

Mass

Mass approx.	0.582	kg	Mass approx.
--------------	-------	----	--------------

