

# Safety Blow Gun



## Description

Combines dynamic progressive action, safety and ergonomic design. This blowgun ensures the safety of the operator and machinery thanks to an integrated pressure regulator that gives active protection for the user.

## Technical Specifications

|                          |  |
|--------------------------|--|
| Maximum Working Pressure | 10 bar<br>1 Mpa<br>145 psi                   |
| Working temperature      | -15 to 50 °C<br>5 to 122 °F<br>258 to 323 °K |
| Body                     | Technical Polymer                            |
| Sub-base                 | Nickel Plated Brass                          |
| Nozzle                   | Nickel Plated Brass                          |
| Trigger                  | Technical Polymer                            |

## Dimensions

| C    | F (MM) | H (MM) | H1 (MM) | L (MM) | L1 (MM) | Weight (kg) |
|------|--------|--------|---------|--------|---------|-------------|
| G1/8 | 20     | 11     | 35      | 148    | 73      | 0.189       |

