

Interface module - VIP-3/PT/FLK34/LED - 2904253

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




VARIOFACE module, with push-in connection and flat-ribbon cable connector, for mounting on NS 35 rails, with pin strip and short and long locking latches for socket strips, 34-pos., with LED

The illustration shows a 50-pos. version



Key commercial data

Packing unit	1 pc
GTIN	 4 046356 813648
Weight per Piece (excluding packing)	181.3 g
Custom tariff number	85369010
Country of origin	United States
Note	Made to Order (non-returnable)

Technical data

Dimensions

Width	67.3 mm
Height	75.8 mm
Depth	63 mm

Ambient conditions

Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C

General

Max. permissible operating voltage	24 V DC
Max. perm. current (per branch)	1 A
Number of positions	34
Status display	LED
Mounting position	any

Interface module - VIP-3/PT/FLK34/LED - 2904253

Technical data

General

Standards/regulations	IEC 60664
	DIN EN 50178
	IEC 62103
Pollution degree	2
Surge voltage category	II

Connection data for connection 1

Connection name	PCB connection
Connection method	Push-in connection
Conductor cross section solid min.	0.14 mm ²
Conductor cross section solid max.	2.5 mm ²
Conductor cross section stranded min.	0.14 mm ²
Conductor cross section stranded max.	2.5 mm ²
Conductor cross section AWG/kcmil min.	26
Conductor cross section AWG/kcmil max	14
Stripping length	8 mm

Connection data for connection 2

Connection name	Flat-ribbon cable connection
Number of connections	1
Connection method	IDC/FLK pin strip (2.54 mm)
Number of positions	34

Classifications

eCl@ss

eCl@ss 4.0	27250313
eCl@ss 4.1	27250313
eCl@ss 5.0	27250313
eCl@ss 5.1	27250313
eCl@ss 6.0	27242608
eCl@ss 7.0	27141152
eCl@ss 8.0	27141152

ETIM

ETIM 3.0	EC001604
ETIM 4.0	EC001604
ETIM 5.0	EC002780

UNSPSC

UNSPSC 6.01	30211824
UNSPSC 7.0901	39121421

Interface module - VIP-3/PT/FLK34/LED - 2904253

Classifications

UNSPSC

UNSPSC 11	39121421
UNSPSC 12.01	39121421
UNSPSC 13.2	39121421

Approvals

Approvals

Approvals

CSA / UL Recognized / cUL Recognized / EAC / cULus Recognized

Ex Approvals

Approvals submitted

Approval details

CSA	
mm ² /AWG/kcmil	26-14
Nominal current IN	1 A
Nominal voltage UN	24 V

UL Recognized	
mm ² /AWG/kcmil	26-14
Nominal current IN	1 A

cUL Recognized	
mm ² /AWG/kcmil	26-14
Nominal current IN	1 A

Interface module - VIP-3/PT/FLK34/LED - 2904253

Approvals

EAC

cULus Recognized  US

Accessories

Accessories

System cable

Cable - FLK 34/EZ-DR/ 50/KONFEK - 2299479



Round cable set, with two 34-pos. socket strips (1:1 connection), cable length: 0.5 m

Cable - FLK 34/EZ-DR/ 100/KONFEK - 2299482



Round cable set, with two 34-pos. socket strips (1:1 connection), cable length: 1 m

Cable - FLK 34/EZ-DR/ 150/KONFEK - 2299495



Round cable set, with two 34-pos. socket strips (1:1 connection), cable length: 1.5 m

Cable - FLK 34/EZ-DR/ 200/KONFEK - 2299505



Round cable set, with two 34-pos. socket strips (1:1 connection), cable length: 2 m

Interface module - VIP-3/PT/FLK34/LED - 2904253

Accessories

Cable - FLK 34/EZ-DR/ 300/KONFEK - 2299518



Round cable set, with two 34-pos. socket strips (1:1 connection), cable length: 3 m

Cable - FLK 34/EZ-DR/ 400/KONFEK - 2299521



Round cable set, with two 34-pos. socket strips (1:1 connection), cable length: 4 m

Cable - FLK 34/EZ-DR/ 600/KONFEK - 2299534



Round cable set, with two 34-pos. socket strips (1:1 connection), cable length: 6 m

Cable - FLK 34/EZ-DR/ 800/KONFEK - 2299547



Round cable set, with two 34-pos. socket strips (1:1 connection), cable length: 8 m

Cable - FLK 34/EZ-DR/1000/KONFEK - 2299550



Round cable set, with two 34-pos. socket strips (1:1 connection), cable length: 10 m

Interface module - VIP-3/PT/FLK34/LED - 2904253

Accessories

Cable - FLK EZ-DR.../.../... - 2295059



Round cable, with preassembly, not shielded, variable cable length

Drawings

Circuit diagram

