


# Neodymium Block Magnet datasheet

- Neodymium iron boron 'rare earth' material
- Strongest magnet material available
- 80°C max. operating temp.
- High resistance to de-magnetisation
- Anisotropic
- N35 grade



## Product Information

Product No.	Length	Width	Height*	Weight	Pull force	Units / pack
		<i>mm</i>		<i>kg</i>		
<b>N817</b>	25	10	3	0.0056	4.7	4
<b>N818</b>	25	10	5	0.0094	4.9	4
<b>N819</b>	35	10	5	0.0131	5.8	4
<b>N820</b>	50	20	3	0.0225	5.8	1
<b>N821</b>	50	50	12.5	0.2438	40.1	1

\*magnetic axis