# A GUIDE TO BUYING SPILL CONTROL ESSENTIALS

R5

UK.RS-ONLINE (UK customers) WWW.RS-COMPONENTS.COM (international customers)





### **INTRODUCTION**

Slips, trips and falls are the most common workplace accidents causing around 40% of all reported major injuries. This coupled with increasing legislation around spill control within today's workplace environment makes it more important than ever before to take control of your organisation's spill management system.

To help take the hassle out of choosing the right products for your business, RS Components and Lubetech – our key supplier of spill control and containment products – worked together to produce this handy guide to shopping for spill control products within the RS range.

### **UNDERSTANDING ABSORBENT TYPES**

#### **SPILL CONTROL ABSORBENTS**

#### PADS

- For everyday spills
- Use singly or multiple pads together according to spill size
- Great for lower volume use

#### ROLLS

- For everyday spills
- Like pads just on a roll making them versatile for higher (or lower) volume use
- Tear off what you need when and where you need it

#### SOCKS

- Designed to contain spill and prevent it travelling
- Ideal for volume flow containment
- Great for getting larger spills under control

USE ABSORBENT TYPES INDIVIDUALLY OR TOGETHER TO CONTAIN AND CONTROL ANY SIZE OF SPILL.

### **SPILL CONTROL EQUIPMENT**

#### TRAYS

 Includes all types and sizes of spill trays

#### DRUM BUNDING

 Includes pallets, work floors or trays for use with drum containers



#### **IBC BUNDING**

 Includes Intermediate Bulk Containers (IBC) and relevant spill pallets

#### **DISPOSAL BAGS**

• Bags for the safe disposal of absorbents used for chemical or hazardous spills

### **UNDERSTANDING ABSORBENT APPLICATIONS**

Our range is divided into three application types:

### **MAINTENANCE ABSORBENTS**

- These are for general purpose use; ideal in industrial environments where many different liquids are present
- Generally dark grey or black in colour and produced from meltblown polypropylene and other materials
- Suitable for ALL fluid spills, including water-based fluids, oil and oil-based fluids, as well as non-aggressive chemicals, making maintenance absorbents the most versatile absorbent type capable of dealing with most spills
- Maintenance absorbents are available in a variety of formats, including Pads, Rolls, Socks and Pillows, and in a wide range of Spill Kits
- Larger Spill Kits are available with compatible refill kits to reduce costs

### **OIL-ONLY ABSORBENTS**

- Designed for use specifically with oil and hydrocarbon spills
- Always white in colour to be easily recognised
- Produced from materials designed for use in the toughest, oiliest environments
- Incorporating hydrophobic technology, oil-only absorbents do not absorb water so they are ideal for use outdoors, or anywhere you need to target oil spills without absorbing water or other fluids
- Description of the sector of t
- Remain buoyant in water even when fully saturated with oil – allowing easy collection and disposal
- Oil-only absorbents are available in a variety of formats, including Pads, Rolls, Socks and Pillows, and in a range of dedicated Spill Kits to suit any requirements
- Larger Spill Kits are available with compatible refill kits to minimise costs



- Designed specifically for use with chemicals, including more aggressive chemicals, such as acids, kerosene and detergents
- Always yellow in colour for easy recognition of chemical spill application, but also to alert users that once used, the product must only be handled using full Personal Protective Equipment (PPE) clothing and disposed of in the approved manner for the type of chemical spilt
- Ideal for use in chemical plants and laboratories
- Chemical absorbents can also be used for water-based spills
- Chemical absorbents are available in a variety of formats, including Pads, Rolls, Socks and Pillows, and in a range of specialist Spill Kits to suit your requirements
- Larger Spill Kits are available with compatible refill kits to help reduce costs





### WHAT SPILL CONTROL EQUIPMENT & WHY?

Compliance and regulations pertaining to spill control differs between countries: England and Wales are governed by a slightly different set of regulations to Scotland;

There are specific regulations for the storage and control



of different substances. In terms of oil-based substances, in general, legislation applies to anyone who stores and controls oil above ground. There is multiple chemical-related legislation for chemical storage and handling which again

is different from country to country. For these reasons it is vital that you check local laws and requirements as failure to comply could result in penalties.

### SPILL CONTROL KITS



### uk.rs-online.com

### SEARCHING THE RS WEB SITE FOR SPILL CONTROL PRODUCTS

To keep it simple, we have divided our Spill Clean Up range into three categories:

### SPILL ABSORBENTS SPILL CONTROL EQUIPMENT SPILL KITS

Each section can then be refined using a series of specifications to select your requirements making it simple to find the right product for you:

| SPILL ABSORBENTS  | SPILL CONTROL EQUIP'T  | SPILL KITS   |
|---|--|--|
| <ul> <li>Application:</li> <li>Chemical</li> <li>Maintenance</li> <li>Oil-Only</li> </ul>   | <ul> <li>Application:</li> <li>Chemical</li> <li>Maintenance</li> <li>Oil-Only</li> </ul>  | <ul> <li>Application:</li> <li>Chemical</li> <li>Maintenance</li> <li>Oil-Only</li> <li>Hazardous</li> </ul>   |
| <ul> <li>Type:</li> <li>✓ Pad</li> <li>✓ Roll</li> <li>✓ Pillow</li> <li>✓ Mat</li> <li>✓ Sock</li> <li>✓ Granules</li> <li>✓ Powder</li> <li>Absorbent Capacity:</li> <li>✓ 0.8 L</li> <li>✓ 2 L</li> <li>✓ 20 L</li> <li>✓ 50 L</li> <li>✓ Quantity per Pack</li> <li>✓ 1</li> <li>✓ 20</li> <li>✓ 25</li> <li>✓ 50</li> <li>✓ 100</li> </ul> | <ul> <li>Type:</li> <li>Disposal Bags</li> <li>Drain Mats</li> <li>Trays</li> <li>Drum Bunding</li> <li>IBC Bunding</li> <li>IBC Bunding</li> <li>Material:</li> <li>Neoprene</li> <li>Polyethylene</li> </ul> | <ul> <li>Mercury</li> <li>Battery Acid</li> <li>Size:</li> <li>5 L</li> <li>10 L</li> <li>20 L</li> <li>50 L</li> <li>100 L</li> <li>180 L</li> <li>Kit Contents:</li> <li>Bag, Pad x 8, Socks x 3, Tie</li> <li>Clear Bag, Pads, Socks</li> <li>Cushion, Disposable Bag, Sheet x 10, Tie</li> <li>Marking Tape, Pads, Pillows, Socks, Wheel Bin</li> <li>Pads, Pillows, Plastic Bin, Socks</li> </ul> |

### uk.rs-online.com





## **COMPATIBILITY CHART**

| laintenance 🔵         | Oil 🔘 | Che | mical 🤇    |
|-----------------------|-------|-----|------------|
| Acetaldehyde          |       |     | 0          |
| Acetic Acid           |       |     | $\bigcirc$ |
| Acetic Acid Amyl Este | er 🕒  | 0   | 0          |
| Acetic Anhydride      |       |     | 0          |
| Acetone               |       | 0   | 0          |
| Acetyl Chloride       |       | 0   | 0          |
| Acrolein              |       | 0   | 0          |
| Acrylic Acid          |       |     | 0          |
| Acrylic Emulsions     |       |     | 0          |
| Acrylonitrile         |       |     | 0          |
| Allyl Alcohol         |       |     | 0          |
| Aminobenzoic Acid     |       |     | 0          |
| Ammonia (anhydrous)   |       | 0   | $\bigcirc$ |
| Ammonium Hydroxide    | e 🔴   | 0   | $\bigcirc$ |
| Amyl Acetate          |       | 0   | $\bigcirc$ |
| Amyl Alcohol          |       |     | $\bigcirc$ |
| Aniline               |       |     | $\bigcirc$ |
| Aqua Regia            |       |     | $\bigcirc$ |
| Aviation Fuel         |       | 0   | $\bigcirc$ |
| Benzene               |       | 0   | $\bigcirc$ |
| Benzoic Ether         |       | 0   | $\bigcirc$ |
| Benzonitrile          |       |     | $\bigcirc$ |
| Benzyl Alcohol        |       |     | 0          |
| Benzyl Chloride       |       |     | 0          |
| Boric Acid            |       |     | 0          |
| Brake Fluid           |       | 0   | 0          |
| Bromine               |       |     | 0          |
| Butyl Acetate         |       | 0   | 0          |
| Butyl Alcohol         |       | 0   | 0          |
| Butylamine            |       |     | 0          |
| Butyric Acid          |       | 0   | 0          |
| Calcium Hydroxide     |       | 0   | $\bigcirc$ |

| Carbolic Acid         |        | $\bigcirc$ |
|-----------------------|--------|------------|
| Castor Oil            |        | $\bigcirc$ |
| Chloracetic Acid      |        | $\bigcirc$ |
| Chlorbenzene          |        | $\bigcirc$ |
| Chlorine              |        | $\bigcirc$ |
| Chlorine Soda         |        | $\bigcirc$ |
| Chloroform            | 0      | $\bigcirc$ |
| Chlorosulphuric Acid  |        | $\bigcirc$ |
| Chlorox (full bleach) |        | $\bigcirc$ |
| Chromic Acid          |        | $\bigcirc$ |
| Citric Acid           |        | $\bigcirc$ |
| Corn Oil              | 0      | $\bigcirc$ |
| Cottonseed Oil        | 0      | $\bigcirc$ |
| Cresol                | 0      | $\bigcirc$ |
| Cyclohexane           | 0      | $\bigcirc$ |
| Detergents            |        | $\bigcirc$ |
| Dichlorbenzol         | 0      | $\bigcirc$ |
| Diethyl Amine         | 0      | $\bigcirc$ |
| Diethyl Ether         | 0<br>0 | $\bigcirc$ |
| Di-Nitrobenzene       | 0      | $\bigcirc$ |
| Dioxan                |        | $\bigcirc$ |
| Disooctyl Phthalate   | 0      | $\bigcirc$ |
| Ether                 | 0      | $\bigcirc$ |
| Ethyl Acetate         | 0      | $\bigcirc$ |
| Ethyl Alcohol         | 0      | $\bigcirc$ |
| Ethyl Chloride        | 0      | $\bigcirc$ |
| Ethyl Ether           | 0      | $\bigcirc$ |
| Ethylene Glycol       |        | $\bigcirc$ |
| Ethyl Propianate      | 0      | $\bigcirc$ |
| Formaldehyde          |        | $\bigcirc$ |
| Formic Acid           |        | 0          |
| Fuel Oil              | 0      | $\bigcirc$ |
| Galvanic Liquids      |        | 0          |
| Gearbox Oil           | 0      | 0          |
| Heptane               | 0      | 0          |
|                       |        |            |

| Hexane                  | 0      | 0          |
|-------------------------|--------|------------|
| Hydrazine               |        | 0          |
| Hydrochloric Acid       |        | $\bigcirc$ |
| Hydrofluoric Acid       |        | $\bigcirc$ |
| Hydrogen Cyanide        | 0      | $\bigcirc$ |
| Hydrogen Peroxide       |        | $\bigcirc$ |
| Isobutyl Alcohol        | 0      | $\bigcirc$ |
| Isobutyric Acid         | 0      | $\bigcirc$ |
| Isopropyl Acetate       | 0      | $\bigcirc$ |
| Isopropyl Alcohol       | 0      | $\bigcirc$ |
| Kerosene                | 0      | $\bigcirc$ |
| Ketones                 | 0      | $\bigcirc$ |
| Linseed Oil             | 0      | $\bigcirc$ |
| Lubricating Oil         | 0      | $\bigcirc$ |
| Magnesium Oxide Hydrate |        | $\bigcirc$ |
| Methyl Alcohol          | 0      | $\bigcirc$ |
| Methyl Chloride         | 0      | $\bigcirc$ |
| Methyl Ether            | 0      | $\bigcirc$ |
| Methyl Ethyl Ketone     | 0      | $\bigcirc$ |
| Methyl Methacrylate     | 0      | $\bigcirc$ |
| Methyl Propionate       | 0      | $\bigcirc$ |
| Milk                    |        | $\bigcirc$ |
| Mineral Oil             | 0      | $\bigcirc$ |
| Mineral Sprits          | 0      | $\bigcirc$ |
| Motor Oil               | 0<br>0 | $\bigcirc$ |
| Naphthalene             | 0      | $\bigcirc$ |
| Nitric Acid             |        | $\bigcirc$ |
| Nitrobenzene Acid       |        | $\bigcirc$ |
| Nitrobenzol             |        | $\bigcirc$ |
| Nitrotoluene            | 0      | $\bigcirc$ |
| Octane                  | 0      | $\bigcirc$ |
| Oleic Acid              | 0      | 0          |
| Olive Oil               | 0      |            |
| Petroleum Ether         | 0      | 0          |
| Phenol                  |        | 0          |
|                         |        |            |

| Phenyl Formic Acid        |   | 0          |
|---------------------------|---|------------|
| Phosphoric Acid           |   | 0          |
| Potassium Hydroxide       |   | 0          |
| Propanol                  |   | $\bigcirc$ |
| Propionic Acid            | 0 | $\bigcirc$ |
| Propyl Alcohol            | 0 | $\bigcirc$ |
| Propylene Glycol          | 0 | $\bigcirc$ |
| Quinoline                 |   | $\bigcirc$ |
| Resorcinol                |   | $\bigcirc$ |
| Saccharose                |   | $\bigcirc$ |
| Salt Solutions (metallic) |   | $\bigcirc$ |
| Silicone Oil              | 0 | $\bigcirc$ |
| Silver Nitrate            |   | 0          |
| Soap Solutions            | 0 | 0          |
| Sodium Bicarbonate        |   | 0          |
| Sodium Chloride           |   | $\bigcirc$ |
| Sodium Hydroxide          | 0 | 0          |
| Sodium Nitrate            |   | 0          |
| Stannic Chloride          |   | $\bigcirc$ |
| Starch                    |   | 0          |
| Styrene                   | 0 | $\bigcirc$ |
| Sucrose                   |   | $\bigcirc$ |
| Sulphuric Acid            |   | $\bigcirc$ |
| Synthetic Motor Oil       | 0 | $\bigcirc$ |
| Tannic Acid               |   | $\bigcirc$ |
| Tin Chloride              |   | 0          |
| Toluene                   | 0 | 0          |
| Transformer Oil           | 0 | 0          |
| Trichlorethylene          | 0 | $\bigcirc$ |
| Triethylene Glycol        | 0 | $\bigcirc$ |
| Turpentine                | 0 | $\bigcirc$ |
| Urine                     |   | $\bigcirc$ |
| Vinegar                   |   | $\bigcirc$ |
| Vinyl Acetate             | 0 | 0          |
| Water                     |   | 0          |