


**KEMET Part Number: PME271E522MR30**  
(P277QN223M300A)

PME271E/P277, Film, Metallized Paper, Safety, 0.022 uF, 20%, 300 VAC (X1), 630 VDC, 110°C, Lead Spacing = 15.2mm



**Dimensions**

L	19mm MAX
H	13mm MAX
T	7.3mm MAX
S	15.2mm +/-0.4mm
LL	30mm +5mm
F	0.8mm +/-0.05mm

**Packaging Specifications**

Packaging:	Bulk, Bag
Packaging Quantity:	400

**General Information**

Supplier:	KEMET
Series:	PME271E/P277
Dielectric:	Metallized Paper
Style:	Radial
Features:	EMI Safety
RoHS:	Yes
Lead:	Wire Leads
Qualifications:	ENEC, UL, cUL
AEC-Q200:	No
Construction:	Molded
Miscellaneous:	SRF= 9.8 MHz

**Specifications**

Capacitance:	0.022 uF
Capacitance Tolerance:	20%
Voltage AC:	300 VAC (X1)
Voltage DC:	630 VDC
Temperature Range:	-40/+110°C
Rated Temperature:	110°C
Dissipation Factor:	1.30% 1kHz
Insulation Resistance:	12 GOhms
Max dV/dt:	1200 V/us
Safety Class:	X1