


Part Number: 1505DNH

COAX RG59/U LSZH HDTV PRECISION VIDEO



Product Description

COAX [0.8/3.7] RG59/U LSZH HDTV CLASSICS PRO

Technical Specifications

Product Overview

Environmental Space:	Indoor - Euroclass Dca
Suitable Applications:	Low loss HDTV/SDI Digital coax used in analog and digital video circuits and high quality applications; The outer conductor is designed for high screening attenuation and low transfer impedance; The cable is suitable for indoor and outdoor use

Physical Characteristics (Overall)

Conductor

Stranding	Material	Nominal Diameter	Diameter +/- Tolerance	No. of Coax
Solid	BC - Bare Copper	0.81 mm	0.03 mm	1

Conductor Count:	1
Conductor Size:	20 AWG

Insulation

Type	Material	Nominal Diameter	Diameter +/- Tolerance
Dielectric	FPE - Foamed Polyethylene	3.68 mm	0.15 mm

Outer Shield Material

Type	Layer	Material	Coverage [%]	Min. Overlap	Nominal Diameter	Coverage +/- Tolerance
Tape, bonded to dielectric	1	Aluminum/Polyester/Aluminum		2 mm		
Braid	2	TC - Tinned Copper	80 %		4.4 mm	5 %
Tape, (L-folded) bonded to sheath	3	Aluminum/Polyester		2 mm		

Outer Jacket Material

Material	Nominal Diameter	Diameter +/- Tolerance
LSZH / FRNC	5.92 mm	0.2 mm

Construction and Dimensions

Min Elongation at Breakof Jacket:	125 %
Min Tensile Strength of Jacket:	9 MPa

Electrical Characteristics

Conductor DCR

Nominal Conductor DCR	Nominal Outer Shield DCR
32 Ohm/km	12 Ohm/km

Capacitance

Nom. Capacitance	Capacitance Tolerance
53 pF/m	2 pF/m

Impedance

Nominal Characteristic Impedance	Nominal Characteristic Tolerance
75 Ohm	3 Ohm

High Frequency (Nominal/Typical)

Frequency [MHz]	Nom. Insertion Loss
1 MHz	1 dB/100m
3.6 MHz	2 dB/100m
10 MHz	3 dB/100m
71.5 MHz	6.9 dB/100m
135 MHz	8.9 dB/100m
270 MHz	12.5 dB/100m
360 MHz	14.4 dB/100m
540 MHz	18.1 dB/100m
720 MHz	21.0 dB/100m
750 MHz	21.3 dB/100m
1000 MHz	24.9 dB/100m
1500 MHz	31.2 dB/100m
2250 MHz	39.0 dB/100m
3000 MHz	45.9 dB/100m
4500 MHz	57.4 dB/100m

Delay

Nominal Delay	Nominal Velocity of Propagation (VP) [%]	Velocity of Propagation Tolerance
400 ns/ft	83 %	2 %

High Freq

Frequency [MHz]	Min. RL (Return Loss) [dB]
5 - 1600 MHz	23 dB
1600 - 4500 MHz	21 dB

High Freq Table Note:	In each frequency band, 1 peak value up to 4 dB lower is allowed
-----------------------	--

Screening

Frequency [MHz]	Min. Screening Attenuation
30 - 1000 MHz	95 dB
1000 - 2000 MHz	85 dB
2000 - 3000 MHz	75 dB
3000 - 4500 MHz	65 dB

Screening Class:	A+
------------------	----

Transfer Impedance

Transfer Impedance
Max. 2.5 mOhm/m

Voltage

Voltage Test Dielectric
2.0 kV DC

Temperature Range

Installation Temp Range:	-5°C To +50°C
Storage Temp Range:	-30°C To +70°C
Operating Temp Range:	-30°C To +70°C

Mechanical Characteristics

Max Recommended Pulling Tension:	200 N
Min Bend Radius (W/o Pulling Strength):	60 mm

Standards

CPR Euroclass:	Dca-s1,d1,a1
CENELEC Compliance:	EN 50117-1
RG Type:	59/U Type

Applicable Environmental and Other Programs

EU RoHS Compliance Date (yyyy-mm-dd):	2005-01-01
--	------------

Flammability, LS0H, Toxicity Testing

ISO/IEC Flammability:	IEC 60332-1-2 and IEC 60332-3-24
Other Flammability:	CEI 20-22-3
Amount of Halogen acc. to IEC 60754-1 & EN50267-1:	Zero

Part Number

Variants

Item #	Color	Length
1505DNH.03500	Black	500 m
1505DNH.04500	Green	500 m
1505DNH.00500	Purple	500 m
1505DNH.02500	Yellow	500 m

History

Revision Number:	3
------------------	---

© 2019 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.