

1919FE1/4

Filter-regulator-lubricator



- Modular unit composed of one condensate separator-filter and one lubricator
- The unit comprises the following: pressure regulator with locking device, air/oil micro-fog mixer with intensity regulator, polycarbonate cups with semiautomatic water exhaust valve, double graduated (bars-psi) analogue pressure gauge, fixing support

Air in/outlet	1/4" GAS BSPT
Pressure gauge inlet	1/8" GAS BSPT
Maximum air capacity	750 l/min
Maximum pressure	9,5 bar
Operating pressure	0,5 - 8,5 bar
Operating temperature	5 - 60 °C
Filter capacity	5 micron
Cup capacity	15 cc air / 25 cc oil
Weight	700 g



	art.		 g
019190200	1919FE1/4	1919 FE1/4-filter-regulator-lubricator	700