


### Polyethylene Spiral Binding with UL94V0 classification

#### SBPAV0

Due to its excellent flame protection properties, SBPAV0 spiral binding is particularly suitable for the rail and aviation industries as well as public buildings.


#### Features and Benefits

- Organises and protects cables and hoses
- Self-extinguishing according to UL94 V0
- Very good protection against abrasion
- Suitable for retro-fitting
- Cables branch out at any point
- Wide range of diameters



Spiral binding SBPAV0.

<b>MATERIAL</b>	Polyamide 6 V0 (PA6V0)
<b>Operating Temperature</b>	-40 °C to +90 °C, intermittent +120 °C
<b>Flammability</b>	UL94 V0
<b>Specifications</b>	CEN TS 45545-2: 2009, DIN 5510-2



Spiral binding

TYPE	Nominal Ø	Wall (WT)	Pitch (P)	Bundle Ø min.	Bundle Ø max.	Colour	Reel Length	Article-No.
SBPAV01.5	1.5	0.40	6.0	1.6	8.0	Black (BK)	30 m	161-44000
SBPAV04	4	0.60	7.8	5.0	20.0	Black (BK)	30 m	161-44100
SBPAV09	9	1.00	12.5	10.0	100.0	Black (BK)	30 m	161-44200
SBPAV016	16	1.20	16.0	20.0	150.0	Black (BK)	30 m	161-44300

All dimensions in mm. Subject to technical changes.  
Minimum Order Quantity (MOQ) may differ from package content.



For product specific approvals and specifications please refer to the Appendix.