Safety data sheet
according to UK REACH

Printing date 27.03.2026 Version number 7 (replaces version 6) Revision: 13.12.2021

SECTION 1: Identification of the substance/mixture and of the company/undertaking

· **1.1 Product identifier**

· **Trade name: PressurePro Grease and Protein Remover RM 731**

· **1.2 Relevant identified uses of the substance or mixture and uses advised against**
Restricted to professional users.
· **Application of the substance / the mixture** High pressure cleaner

· **1.3 Details of the supplier of the safety data sheet**
· **Manufacturer/Supplier:**

Alfred Kärcher SE & Co. KG
Alfred-Kärcher-Str. 28-40
D - 71364 Winnenden
Tel.: +49-7195-14-0

Kärcher (UK) Ltd.
Kärcher House
Brookhill Way
Banbury
Oxon OX16 3ED
Great Britain
Tel.: +44-1295-752-000

Internet: www.karcher.com

· **Further information obtainable from:**

Regulatory Affairs
Tel.: +49-7195-14-0
productsafety.management.de@karcher.com

· **1.4 Emergency telephone number:**

For Hazardous Materials [or Dangerous Goods] Incidents
Spill, Leak, Fire, Exposure, or Accident
Call CHEMTREC Day or Night
Within USA and Canada: 1-800-424-9300
Outside USA and Canada: +1-703-527-3887 (collect calls accepted)

SECTION 2: Hazards identification

· **2.1 Classification of the substance or mixture**
· **Classification according to Regulation (EC) No 1272/2008**

Met. Corr.1	H290 May be corrosive to metals.
Skin Corr. 1B	H314 Causes severe skin burns and eye damage.
Eye Dam. 1	H318 Causes serious eye damage.

· **2.2 Label elements**
· **Labelling according to Regulation (EC) No 1272/2008**
The product is classified and labelled according to the GB CLP regulation.

(Contd. on page 2)

Safety data sheet
according to UK REACH

Printing date 27.03.2026 Version number 7 (replaces version 6) Revision: 13.12.2021

Trade name: PressurePro Grease and Protein Remover RM 731

(Contd. of page 1)

· **Hazard pictograms**



GHS05

· **Signal word** Danger

· **Hazard-determining components of labelling:**
sodium hydroxide
fatty alcohol ethoxylate
isotridecanolethoxylate + 8 EO

· **Hazard statements**
H290 May be corrosive to metals.
H314 Causes severe skin burns and eye damage.

· **Precautionary statements**

P280	Wear protective gloves/protective clothing/eye protection/face protection.
P303+P361+P353	IF ON SKIN (or hair): Take off immediately all contaminated clothing. Rinse skin with water [or shower].
P305+P351+P338	IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.
P310	Immediately call a POISON CENTER/doctor.
P405	Store locked up.
P501	Dispose of contents/container in accordance with local/regional/national/international regulations.

SECTION 3: Composition/information on ingredients

· **3.2 Mixtures**

· **Description:** Cleaning agent

· **Dangerous components:**

CAS: 1310-73-2 EINECS: 215-185-5 Index number: 011-002-00-6 Reg.nr.: 01-2119457892-27-xxxx	sodium hydroxide Met. Corr.1, H290; Skin Corr. 1A, H314; Eye Dam. 1, H318 Specific concentration limits: Skin Corr. 1A; H314: C ≥ 5 % Skin Corr. 1B; H314: 2 % ≤ C < 5 % Skin Irrit. 2; H315: 0.5 % ≤ C < 2 % Eye Irrit. 2; H319: 0.5 % ≤ C < 2 %	≥2-<5%
CAS: 15763-76-5 EINECS: 239-854-6 Reg.nr.: 01-2119489411-37-xxxx	sodium p-cumenesulphonate Eye Irrit. 2, H319	1-5%
CAS: 78330-20-8	fatty alcohol ethoxylate Eye Dam. 1, H318; Acute Tox. 4, H302	≥1-<3%
CAS: 69011-36-5	isotridecanolethoxylate + 8 EO Eye Dam. 1, H318; Acute Tox. 4, H302	≥1-<3%

· **Additional information** For the wording of the listed hazard phrases refer to section 16.

(Contd. on page 3)

Safety data sheet
according to UK REACH

Printing date 27.03.2026 Version number 7 (replaces version 6) Revision: 13.12.2021

Trade name: PressurePro Grease and Protein Remover RM 731

(Contd. of page 2)

SECTION 4: First aid measures

· **4.1 Description of first aid measures**
· **General information**
Immediately remove any clothing soiled by the product.
Involve doctor immediately.
· **After inhalation**
In case of unconsciousness place patient stably in side position for transportation.
Supply fresh air; consult doctor in case of complaints.
· **After skin contact** Immediately wash with water and soap and rinse thoroughly.
· **After eye contact** Rinse opened eye for several minutes under running water. Then consult a doctor.
· **After swallowing**
Rinse out mouth and then drink plenty of water.
Do not induce vomiting; call for medical help immediately.
Drink plenty of water and provide fresh air. Call for a doctor immediately.

· **4.2 Most important symptoms and effects, both acute and delayed** No further relevant information available.

· **4.3 Indication of any immediate medical attention and special treatment needed**
No further relevant information available.

SECTION 5: Firefighting measures

· **5.1 Extinguishing media**
· **Suitable extinguishing agents**
CO2, powder or water spray. Fight larger fires with water spray or alcohol resistant foam.

· **5.2 Special hazards arising from the substance or mixture** No further relevant information available.

· **5.3 Advice for firefighters**
· **Protective equipment:** No special measures required.
· **Additional information** Collect contaminated fire fighting water separately. It must not enter the sewage system.

SECTION 6: Accidental release measures

· **6.1 Personal precautions, protective equipment and emergency procedures**
Wear protective equipment. Keep unprotected persons away.

· **6.2 Environmental precautions:**
Dilute with plenty of water.
Do not allow to enter sewers/ surface or ground water.
Do not allow to penetrate the ground/soil.

· **6.3 Methods and material for containment and cleaning up:**
Absorb with liquid-binding material (sand, diatomite, acid binders, universal binders).
Use neutralising agent.
Dispose contaminated material as waste according to section 13.

(Contd. on page 4)

Safety data sheet
according to UK REACH

Printing date 27.03.2026 Version number 7 (replaces version 6) Revision: 13.12.2021

Trade name: PressurePro Grease and Protein Remover RM 731

(Contd. of page 3)

Ensure adequate ventilation.

· **6.4 Reference to other sections**
See Section 7 for information on safe handling
See Section 8 for information on personal protection equipment.
See Section 13 for disposal information.

SECTION 7: Handling and storage

· **7.1 Precautions for safe handling**
Ensure good ventilation/exhaustion at the workplace.
Prevent formation of aerosols.
Avoid contact with eyes and skin.
· **Information about fire - and explosion protection:** No special measures required.

· **7.2 Conditions for safe storage, including any incompatibilities**
· **Storage**
· **Requirements to be met by storerooms and receptacles:** Store only in the original receptacle.
· **Information about storage in one common storage facility:**
Do not store together with acids.
Keep away from food, beverages and feed.
· **Further information about storage conditions:** Keep receptacle tightly sealed.

· **7.3 Specific end use(s)** No further relevant information available.

*
SECTION 8: Exposure controls/personal protection

· **8.1 Control parameters**

· **Ingredients with limit values that require monitoring at the workplace:**	
1310-73-2 sodium hydroxide	
WEL	Short-term value: 2 mg/m³

· **DNELs**		
1310-73-2 sodium hydroxide		
Inhalative	DNEL	1 mg/m3 (employee) 1 mg/m3 (consumer)
15763-76-5 sodium p-cumenesulphonate		
Oral	DNEL	3.8 mg/kg×d (consumer)
Dermal	DNEL	136.25 mg/kg×d (employee) 68.1 mg/kg×d (consumer)
Inhalative	DNEL	26.9 mg/m3 (employee) 6.6 mg/m3 (consumer)

· **PNECs**	
15763-76-5 sodium p-cumenesulphonate	
PNEC	0.23 mg/l (freshwater)

(Contd. on page 5)

(Contd. of page 4)

	0.023 mg/l (marine water)
	100 mg/l (STP)
PNEC sediment	0.862 mg/kg (freshwater)
	0.086 mg/kg (marine water)
PNEC soil	0.037 mg/kg (soil)

· **8.2 Exposure controls**
· **Appropriate engineering controls** No further data; see section 7.
· **Individual protection measures, such as personal protective equipment**
· **General protective and hygienic measures**
Keep away from foodstuffs, beverages and feed.
Immediately remove all soiled and contaminated clothing
Wash hands before breaks and at the end of work.
Do not inhale gases / fumes / aerosols.
Avoid contact with the eyes and skin.
· **Respiratory protection:**
In case of brief exposure or low pollution use respiratory filter device. In case of intensive or longer exposure use self-contained respiratory protective device.
Filter A/P2.
· **Hand protection**



Protective gloves.

· **Material of gloves** Butyl rubber, BR
· **Penetration time of glove material**
The exact break trough time has to be found out by the manufacturer of the protective gloves and has to be observed.
· **For the permanent contact gloves made of the following materials are suitable:**
* butyl rubber 0,7 mm, 480 min (EN 374)
· **For the permanent contact of a maximum of 15 minutes gloves made of the following materials are suitable:**
Nitrile rubber, NBR
· **Eye/face protection**



Tightly sealed goggles (EN 166)

· **Body protection:**
Boots
Apron

*

SECTION 9: Physical and chemical properties

· **9.1 Information on basic physical and chemical properties**
· **General Information**

· **Physical state**	Liquid
· **Colour:**	Light yellow

(Contd. on page 6)

Safety data sheet
according to UK REACH

Printing date 27.03.2026 Version number 7 (replaces version 6) Revision: 13.12.2021

Trade name: PressurePro Grease and Protein Remover RM 731

(Contd. of page 5)

· **Odour:**	Product specific
· **Odour threshold:**	Not determined
· **Melting point/freezing point:**	-7 °C
· **Boiling point or initial boiling point and boiling range**	100 °C
· **Flammability**	Not applicable
· **Lower and upper explosion limit**	
· **Lower:**	Not determined
· **Upper:**	Not determined
· **Flash point:**	Not applicable
· **Auto-ignition temperature:**	not applicable
· **Decomposition temperature:**	Not determined
· **pH at 20 °C**	13
· **pH-value 1 %:**	11-12
· **Viscosity:**	
· **Kinematic viscosity**	Not determined
· **dynamic at 20 °C:**	6 mPas
· **Solubility**	
· **Water:**	Fully miscible
· **Partition coefficient n-octanol/water (log value)**	Not determined
· **Vapour pressure:**	Not determined
· **Density and/or relative density**	
· **Density at 20 °C:**	1.103 g/cm³
· **Relative density**	Not determined
· **Vapour density**	Not determined
· **Relative gas density**	Not determined

· **9.2 Other information**

· **Appearance:**

· **Form:**	Fluid

· **Important information on protection of health and environment, and on safety.**

· **Ignition temperature:**	Product is not selfigniting.
· **Explosive properties:**	Product does not present an explosion hazard.
· **Solvent content:**	
· **Solids content:**	22.0 %

· **Change in condition**

· **Evaporation rate**	Not determined

· **Information with regard to physical hazard classes**

· **Explosives**	Void
· **Flammable gases**	Void
· **Aerosols**	Void
· **Oxidising gases**	Void
· **Gases under pressure**	Void
· **Flammable liquids**	Void
· **Flammable solids**	Void
· **Self-reactive substances and mixtures**	Void
· **Pyrophoric liquids**	Void
· **Pyrophoric solids**	Void

(Contd. on page 7)

Safety data sheet
according to UK REACH

Printing date 27.03.2026 Version number 7 (replaces version 6) Revision: 13.12.2021

Trade name: PressurePro Grease and Protein Remover RM 731

(Contd. of page 6)

· **Self-heating substances and mixtures**	Void
· **Substances and mixtures, which emit flammable gases in contact with water**	Void
· **Oxidising liquids**	Void
· **Oxidising solids**	Void
· **Organic peroxides**	Void
· **Corrosive to metals**	May be corrosive to metals.
· **Desensitised explosives**	Void

SECTION 10: Stability and reactivity

· **10.1 Reactivity** corresponds to 10.3

· **10.2 Chemical stability**
· **Thermal decomposition / conditions to be avoided:** No decomposition if used according to specifications.

· **10.3 Possibility of hazardous reactions**
Strong exothermic reaction with acids
Reacts with light alloys to form hydrogen
Corrodes aluminium

· **10.4 Conditions to avoid** No further relevant information available.

· **10.5 Incompatible materials:** Not compatible with alkali-sensitive substances like Sn, Zn, Al and paintings.

· **10.6 Hazardous decomposition products:** No dangerous decomposition products known

SECTION 11: Toxicological information

· **11.1 Information on hazard classes as defined in Regulation (EC) No 1272/2008**
· **Acute toxicity** Based on available data, the classification criteria are not met.

· **LD/LC50 values relevant for classification:**		
15763-76-5 sodium p-cumenesulphonate		
Oral	LD50	>5000 mg/kg (Rat) (OECD 401)
Dermal	LD50	>2000 mg/kg (Rabbit)
78330-20-8 fatty alcohol ethoxylate		
Oral	ATE	500 mg/kg (Rat)
69011-36-5 isotridecanolethoxylate + 8 EO		
Oral	ATE	500 mg/kg (Rat)

· **Primary irritant effect:**
· **Skin corrosion/irritation** Causes severe skin burns and eye damage.
· **Serious eye damage/irritation** Causes serious eye damage.
· **Respiratory or skin sensitisation** Based on available data, the classification criteria are not met.
· **Germ cell mutagenicity** Based on available data, the classification criteria are not met.

(Contd. on page 8)

(Contd. of page 7)

· **Carcinogenicity** Based on available data, the classification criteria are not met.
· **Reproductive toxicity** Based on available data, the classification criteria are not met.
· **STOT-single exposure** Based on available data, the classification criteria are not met.
· **STOT-repeated exposure** Based on available data, the classification criteria are not met.
· **Aspiration hazard** Based on available data, the classification criteria are not met.
· **11.2 Information on other hazards**

· **Endocrine disrupting properties**
None of the ingredients is listed.

*

SECTION 12: Ecological information

· **12.1 Toxicity**

· **Aquatic toxicity:**	
1310-73-2 sodium hydroxide	
LC50/96 h	125 mg/l (Gambusia affinis)
EC50/48 h	76 mg/l (Daphnia magna)
	40.4 mg/l (Ceriodaphnia dubia)
EC50/15 min	22 mg/l (Photobacterium phosphoreum)
15763-76-5 sodium p-cumenesulphonate	
LC50/96 h (static)	>100 mg/l (Oncorhynchus mykiss)
EC50/48 h (static)	>100 mg/l (Daphnia magna)
EC50/96 h (static)	>100 mg/l (Pseudokirchneriella subcapitata)
78330-20-8 fatty alcohol ethoxylate	
LC50/96 h	>10-100 mg/l (Leuciscus idus)
EC50/48 h	>10-<100 mg/l (Aquatic invertebrates)
EC50/72 h	>10-<100 mg/l (Aquatic plants)
69011-36-5 isotridecanolethoxylate + 8 EO	
LC50/96 h	>1-10 mg/l (Leuciscus idus)
EC50/48 h	>1-10 mg/l (Aquatic invertebrates)
EC50/72 h	>1-10 mg/l (Aquatic plants)
NOEC	>1 mg/l /(21 d)

· **12.2 Persistence and degradability** No further relevant information available.

· **Degree of elimination:**	
69011-36-5 isotridecanolethoxylate + 8 EO	
OECD 301B	>60 % (28 d)
OECD 301E	≥90 % (28 d)

· **12.3 Bioaccumulative potential** No further relevant information available.

· **12.4 Mobility in soil** No further relevant information available.

(Contd. on page 9)

(Contd. of page 8)

· **12.5 Results of PBT and vPvB assessment**
· **PBT:** Not applicable
· **vPvB:** Not applicable
· **12.6 Endocrine disrupting properties** The product does not contain substances with endocrine disrupting properties.

· **12.7 Other adverse effects**
· **Additional ecological information:**
· **COD-value:** 300.000 mg/l

· **General notes:**

Do not allow undiluted product or large quantities of it to reach ground water, water course or sewage system.

Must not reach sewage water or drainage ditch undiluted or unneutralised.

The surfactant(s) contained in this preparation complies(comply) with the biodegradability criteria as laid down in Regulation (EC) No.648/2004 on detergents. Data to support this assertion are held at the disposal of the competent authorities of the Member States and will be made available to them, at their direct request or at the request of a detergent manufacturer.

The product does not contain organically bounded halogens (AOX-free).

The contained organic complexing agents reach a DOC-elimination grade of 80% (corresponding to No. 406 of Annex "Analytic and measuring methods") and with this meet the tightened demands of Annex 49 of the revised Direction on liqid waste.

Rinse off of bigger amounts into drains or the aquatic environment may lead to increased pH-values. A high pH-value harms aquatic organisms. In the dilution of the use-level the pH-value is considerably reduced, so that after the use of the product the aqueous waste, emptied into drains, is only low water-dangerous.

SECTION 13: Disposal considerations

· **13.1 Waste treatment methods**
· **Recommendation**
Must not be disposed together with household garbage. Do not allow product to reach sewage system.
Must be specially treated adhering to official regulations.

· **European waste catalogue**	
20 01 29*	detergents containing hazardous substances

· **Uncleaned packaging:**
· **Recommendation:**
Non contaminated packagings may be recycled.
Empty contaminated packagings thoroughly. They may be recycled after thorough and proper cleaning.
· **Recommended cleansing agents:** Water, if necessary together with cleaning agents.

(Contd. on page 10)

Safety data sheet
according to UK REACH

Printing date 27.03.2026 Version number 7 (replaces version 6) Revision: 13.12.2021

Trade name: PressurePro Grease and Protein Remover RM 731

(Contd. of page 9)

SECTION 14: Transport information

· **14.1 UN number or ID number**	
· **ADR, IMDG, IATA**	UN1824
· **14.2 UN proper shipping name**	
· **ADR**	1824 SODIUM HYDROXIDE SOLUTION
· **IMDG, IATA**	SODIUM HYDROXIDE SOLUTION
· **14.3 Transport hazard class(es)**	
· **ADR**	



· **Class**	8 (C5) Corrosive substances.
· **Label**	8
· **IMDG, IATA**	



· **Class**	8 Corrosive substances.
· **Label**	8
· **14.4 Packing group**	
· **ADR, IMDG, IATA**	III
· **14.5 Environmental hazards:**	
· **Marine pollutant:**	No
· **14.6 Special precautions for user**	Warning: Corrosive substances.
· **Hazard identification number (Kemler code):**	80
· **EMS Number:**	F-A,S-B
· **Segregation groups**	(SGG18) Alkalis
· **Stowage Category**	A
· **Segregation Code**	SG35 Stow "separated from" SGG1-acids
· **14.7 Maritime transport in bulk according to IMO instruments**	Not applicable
· **Transport/Additional information:**	
· **ADR**	
· **Limited quantities (LQ)**	5L
· **Excepted quantities (EQ)**	Code: E1 Maximum net quantity per inner packaging: 30 ml Maximum net quantity per outer packaging: 1000 ml
· **Transport category**	3

(Contd. on page 11)

Safety data sheet
according to UK REACH

Printing date 27.03.2026 Version number 7 (replaces version 6) Revision: 13.12.2021

Trade name: PressurePro Grease and Protein Remover RM 731

(Contd. of page 10)

· **Tunnel restriction code**	E
· **IMDG**	
· **Limited quantities (LQ)**	5L
· **Excepted quantities (EQ)**	Code: E1 Maximum net quantity per inner packaging: 30 ml Maximum net quantity per outer packaging: 1000 ml
· **UN "Model Regulation":**	UN 1824 SODIUM HYDROXIDE SOLUTION, 8, III

SECTION 15: Regulatory information

· **15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture**

· **Directive 2012/18/EU**
· **Named dangerous substances - ANNEX I** None of the ingredients is listed.

· **National regulations**

· **Information about limitation of use:** Employment restrictions concerning juveniles must be observed.

· **15.2 Chemical safety assessment:** A Chemical Safety Assessment has not been carried out.

SECTION 16: Other information

This information is based on our present knowledge. However, this shall not constitute a guarantee for any specific product features and shall not establish a legally valid contractual relationship.
A product information sheet can be provided if requested.

· **Relevant phrases**
H290 May be corrosive to metals.
H302 Harmful if swallowed.
H314 Causes severe skin burns and eye damage.
H315 Causes skin irritation.
H318 Causes serious eye damage.
H319 Causes serious eye irritation.
· **Contact:**
Regulatory Affairs
Tel.: +49-7195-14-0
productsafety.management.de@karcher.com
· **Abbreviations and acronyms:**
RID: Règlement international concernant le transport des marchandises dangereuses par chemin de fer (Regulations Concerning the International Transport of Dangerous Goods by Rail)
ICAO: International Civil Aviation Organisation
ADR: Accord relatif au transport international des marchandises dangereuses par route (European Agreement Concerning the International Carriage of Dangerous Goods by Road)
IMDG: International Maritime Code for Dangerous Goods
IATA: International Air Transport Association
GHS: Globally Harmonised System of Classification and Labelling of Chemicals
EINECS: European Inventory of Existing Commercial Chemical Substances
ELINCS: European List of Notified Chemical Substances

(Contd. on page 12)

Safety data sheet
according to UK REACH

Printing date 27.03.2026 Version number 7 (replaces version 6) Revision: 13.12.2021

Trade name: PressurePro Grease and Protein Remover RM 731

(Contd. of page 11)

CAS: Chemical Abstracts Service (division of the American Chemical Society)
DNEL: Derived No-Effect Level (UK REACH)
PNEC: Predicted No-Effect Concentration (UK REACH)
LC50: Lethal concentration, 50 percent
LD50: Lethal dose, 50 percent
PBT: Persistent, Bioaccumulative and Toxic
vPvB: very Persistent and very Bioaccumulative
Met. Corr.1: Corrosive to metals – Category 1
Acute Tox. 4: Acute toxicity – Category 4
Skin Corr. 1A: Skin corrosion/irritation – Category 1A
Skin Corr. 1B: Skin corrosion/irritation – Category 1B
Eye Dam. 1: Serious eye damage/eye irritation – Category 1
Eye Irrit. 2: Serious eye damage/eye irritation – Category 2

· *** Data compared to the previous version altered.**

· 0·011-673·0 RM 731/5 2·492