





MSPX-35-35-F

Ruland MSPX-35-35-F, 35mm x 35mm Rigid Coupling, Black Oxide Steel, Two-Piece Clamp Style, 67mm OD, 95mm Length



Description

Ruland MSPX-35-35-F is a two-piece rigid coupling with 35mm x 35mm bores, 67mm OD, and 95mm length. It has precision honed bores to ensure they are collinear and do not introduce misalignment or vibration into the system making it suitable for high precision servo applications as well as shaft to shaft connections. MSPX-35-35-F has opposing hardware for a balanced design. Proprietary Nypatch® anti-vibration coating on hardware allows for even seating of the screw, repeated screw installations, prevents galling, and maintains high holding power. It eliminates the need to treat screws upon receipt greatly reducing installation time. Forged screws test beyond DIN 912 12.9 standards to ensure maximum holding power. Tightly controlled bore tolerance of $\pm 0.050\text{mm}/\pm 0.012\text{mm}$ is maintained. MSPX-35-35-F is made from 1215 lead-free steel with a proprietary black oxide finish that produces a fine glossy finish while increasing holding power and resisting corrosion. It is machined from solid bar stock that is sourced exclusively from North American mills and is RoHS3 and REACH compliant. MSPX-35-35-F is manufactured in our Marlborough, MA factory under strict controls using proprietary processes.

Product Specifications

Bore (B1)	35 mm	Small Bore (B2)	35 mm
B1 Max Shaft Penetration	47.5 mm	B2 Max Shaft Penetration	47.5 mm
Outer Diameter (OD)	67 mm	Bore Tolerance	$\pm 0.050\text{ mm} / \pm 0.012\text{ mm}$
Length (L)	95 mm	Clearance Diameter (C) MAX	74.7 mm
Recommended Gap	2.38 mm	Recommended Shaft Tolerance	$\pm 0.000\text{ mm} / -0.013\text{ mm}$
Forged Clamp Screw	M8	Screw Material	Alloy Steel with Nypatch®
Hex Wrench Size	6.0 mm	Screw Finish	Black Oxide
Seating Torque	39 Nm	Screw Location (R)	26.7 mm
Number of Screws	8 ea	Rated Torque	1100 Nm
Moment of Inertia	$1.250 \times 10^{-3}\text{ kg}\cdot\text{m}^2$	Maximum Speed	4,000 RPM
Full Bearing Support Required?	No	Nypatch® Anti-Vibration Hardware?	Yes
Precision Honed Bores?	Yes	Zero-Backlash?	Yes
Balanced Design	Yes	Material Specification	1215 Carbon Steel Bar
Temperature	-40°F to 350°F (-40°C to 176°C)	Finish Specification	Hot Process Black Oxide, Impregnated with Naphthenic Oil, Centrifugally Dried
Manufacturer	Ruland Manufacturing	Country of Origin	USA
Weight (lbs)	3.860700	UPC	634529018309
Tariff Code	8483.60.8000	UNSPC	31163009
Note 1	Performance ratings are for guidance only. The user must determine suitability for a particular application.		
Prop 65	WARNING This product can expose you to the chemical Ethylene Thiourea, known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov .		

Installation Instructions

1. Align the MSPX-35-35-F two-piece rigid coupling on the two shafts to be connected. There should

- be no misalignment.
2. Tighten the Nypatch® screws in two stages, starting with the inside screws. Using a 6.0 mm torque wrench, tighten the inside screws to 19.5 Nm which is half the recommended seating torque. Repeat the process for the outside screws, tightening to half the recommended seating torque.
 3. Be sure to maintain the gap of 2.38 mm between the two halves during installation.
 4. Tighten the screws to the full recommended seating torque of 39 Nm following the same pattern, starting with the inside screws first.
 5. For optimum results do not exceed the shaft penetration length of 47.5 mm.
-