

FEATURES

- **Very flexible**
- **High 3:1 shrinkage ratio**
- **Flame retardant**
- **Resistant to common fluids and solvents**
- **Excellent electrical insulation properties**
- **Excellent abrasion resistance**

RS PRO Heat Shrink Tubing, Black 6mm Sleeve Dia. x 7m Length 3:1 Ratio

RS Stock No.: 700-4535



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

From RS Pro a range of high quality, easy to use general purpose heat shrink tubing made from flexible, flame retardant Polyolefin. This heat shrinkable tubing has a low shrink temperature of just 70°C (minimum) and a high shrink ratio of 3:1 which means it shrinks to a third of its original diameter and is ideal for covering irregular or awkward shapes

General Specifications

| | |
|------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Sleeve Type | Heat Shrink |
| Colour | Black |
| Adhesive Lined | No |
| Shrink Ratio | 3:1 |
| Material | Polyolefin |
| Flame Retardant | Yes |
| Halogen Free | No |
| Application | Electrical insulation and protection of resistors and capacitors, Environmental protection against moisture, dust, and chemicals, Mechanical protection to wires and small parts from abrasion, Mechanical strain relief on cable and connector joints to prevent damage caused by flexing or bending, Bundling and organizing harness wires, cable, and tubing, Colour coded identification of cables, wires, and components |

Electrical Specifications

| | |
|----------------------------|--------------------------|
| Dielectric Strength | 19.7KV/mm |
| Volume Resistivity | ≥10 ¹⁴ Ohm.cm |
| Voltage Resistance | AC2500V/60S |
| Voltage | 600V |

Mechanical Specifications

| | |
|------------------------------------|---------------------------------------|
| Sleeve Diameter | 6mm |
| Shrunk Diameter | 2mm |
| Sleeve Length | 7m |
| Wall Thickness | 0.70mm±0.10 |
| Tensile Strength | 10.3MPa |
| Elongation | >=100% |
| Low Temperature Flexibility | No cracking, ASTM D2671 (-55°C/4 hrs) |
| Heat Shock | No cracking, ASTM D2671 (200°C/4 hrs) |
| Longitudinal Change | -10%~10% |

Chemical Properties

| | |
|----------------------------|----------------|
| Flammability | Flame Retarded |
| Tensile Strength | 10.3MPa (min.) |
| Dielectric Strength | 19.7KV/mm |

Operation Environment Specifications

| | |
|----------------------------------|----------------|
| Operating Temperature | -55°C to 135°C |
| Shrink Temperature | 70°C |
| Full Recovery Temperature | Above 110°C |

Approvals

| | |
|----------------------------------|------------------------------------------------------|
| Compliance/Certifications | SAE-AMS-DTL-23053/5 class 1, UL224 File no. E337635. |
| Standards Met | UL |



| Part Number | Color | Dimensions | | |
|-------------|----------------|------------------|---------------------|-----------------------|
| | | As Supplied (mm) | After Recovery (mm) | Wall Thickness Shrunk |
| | | D (I.D.min.) | d (I.D.max.) | w (mm) |
| 700-4453 | Clear | 3.0 | 1.0 | 0.60±0.10 |
| 700-4456 | Clear | 6.0 | 2.0 | 0.70±0.10 |
| 700-4450 | Clear | 9.0 | 3.0 | 0.80±0.15 |
| 700-4469 | Clear | 12.0 | 4.0 | 0.85±0.15 |
| 700-4462 | Clear | 18.0 | 6.0 | 1.00±0.15 |
| 700-4466 | Clear | 24.0 | 8.0 | 1.20±0.20 |
| 700-4475 | Yellow | 3.0 | 1.0 | 0.60±0.10 |
| 700-4478 | Yellow | 6.0 | 2.0 | 0.70±0.10 |
| 700-4472 | Yellow | 9.0 | 3.0 | 0.80±0.15 |
| 700-4481 | Yellow | 12.0 | 4.0 | 0.85±0.15 |
| 700-4484 | Yellow | 18.0 | 6.0 | 1.00±0.15 |
| 700-4488 | Yellow | 24.0 | 8.0 | 1.20±0.20 |
| 700-4497 | Blue | 3.0 | 1.0 | 0.60±0.10 |
| 700-4490 | Blue | 6.0 | 2.0 | 0.70±0.10 |
| 700-4494 | Blue | 9.0 | 3.0 | 0.80±0.15 |
| 700-4504 | Blue | 12.0 | 4.0 | 0.85±0.15 |
| 700-4507 | Blue | 18.0 | 6.0 | 1.00±0.15 |
| 700-4501 | Blue | 24.0 | 8.0 | 1.20±0.20 |
| 700-4510 | Red | 3.0 | 1.0 | 0.60±0.10 |
| 700-4513 | Red | 6.0 | 2.0 | 0.70±0.10 |
| 700-4517 | Red | 9.0 | 3.0 | 0.80±0.15 |
| 700-4526 | Red | 12.0 | 4.0 | 0.85±0.15 |
| 700-4529 | Red | 18.0 | 6.0 | 1.00±0.15 |
| 700-4523 | Red | 24.0 | 8.0 | 1.20±0.20 |
| 700-4532 | Black | 3.0 | 1.0 | 0.60±0.10 |
| 700-4535 | Black | 6.0 | 2.0 | 0.70±0.10 |
| 700-4539 | Black | 9.0 | 3.0 | 0.80±0.15 |
| 700-4548 | Black | 12.0 | 4.0 | 0.85±0.15 |
| 700-4541 | Black | 18.0 | 6.0 | 1.00±0.15 |
| 700-4545 | Black | 24.0 | 8.0 | 1.20±0.20 |
| 700-4554 | White | 3.0 | 1.0 | 0.60±0.10 |
| 700-4557 | White | 6.0 | 2.0 | 0.70±0.10 |
| 700-4551 | White | 9.0 | 3.0 | 0.80±0.15 |
| 700-4560 | White | 12.0 | 4.0 | 0.85±0.15 |
| 700-4567 | White | 18.0 | 6.0 | 1.00±0.15 |
| 700-4573 | White | 24.0 | 8.0 | 1.20±0.20 |
| 700-4582 | Green / Yellow | 3.0 | 1.0 | 0.60±0.10 |
| 700-4589 | Green / Yellow | 6.0 | 2.0 | 0.70±0.10 |
| 700-4595 | Green / Yellow | 9.0 | 3.0 | 0.80±0.15 |
| 700-4608 | Green / Yellow | 12.0 | 4.0 | 0.85±0.15 |
| 700-4611 | Green / Yellow | 18.0 | 6.0 | 1.00±0.15 |
| 700-4618 | Green / Yellow | 24.0 | 8.0 | 1.20±0.20 |

CROSS REFERENCE LIST

| RS Stock No. | Description |
|---------------------|-------------------------------------|
| 700-4453 | Heatshrink tube clear 3/1mm |
| 700-4456 | Heatshrink tube clear 6/2mm |
| 700-4450 | Heatshrink tube clear 9/3mm |
| 700-4469 | Heatshrink tube clear 12/4mm |
| 700-4462 | Heatshrink tube clear 18/6mm |
| 700-4466 | Heatshrink tube clear 24/8mm |
| 700-4475 | Heatshrink tube yellow 3/1mm |
| 700-4478 | Heatshrink tube yellow 6/2mm |
| 700-4472 | Heatshrink tube yellow 9/3mm |
| 700-4481 | Heatshrink tube yellow 12/4mm |
| 700-4484 | Heatshrink tube yellow 18/6mm |
| 700-4488 | Heatshrink tube yellow 24/8mm |
| 700-4497 | Heatshrink tube blue 3/1mm |
| 700-4490 | Heatshrink tube blue 6/2mm |
| 700-4494 | Heatshrink tube blue 9/3mm |
| 700-4504 | Heatshrink tube blue 12/4mm |
| 700-4507 | Heatshrink tube blue 18/6mm |
| 700-4501 | Heatshrink tube blue 24/8mm |
| 700-4510 | Heatshrink tube red 3/1mm |
| 700-4513 | Heatshrink tube red 6/2mm |
| 700-4517 | Heatshrink tube red 9/3mm |
| 700-4526 | Heatshrink tube red 12/4mm |
| 700-4529 | Heatshrink tube red 18/6mm |
| 700-4523 | Heatshrink tube red 24/8mm |
| 700-4532 | Heatshrink tube black 3/1mm |
| 700-4535 | Heatshrink tube black 6/2mm |
| 700-4539 | Heatshrink tube black 9/3mm |
| 700-4548 | Heatshrink tube black 12/4mm |
| 700-4541 | Heatshrink tube black 18/6mm |
| 700-4545 | Heatshrink tube black 24/8mm |
| 700-4554 | Heatshrink tube white 3/1mm |
| 700-4557 | Heatshrink tube white 6/2mm |
| 700-4551 | Heatshrink tube white 9/3mm |
| 700-4560 | Heatshrink tube white 12/4mm |
| 700-4567 | Heatshrink tube white 18/6mm |
| 700-4573 | Heatshrink tube white 24/8mm |
| 700-4582 | Heatshrink tube green/yellow 3/1mm |
| 700-4589 | Heatshrink tube green/yellow 6/2mm |
| 700-4595 | Heatshrink tube green/yellow 9/3mm |
| 700-4608 | Heatshrink tube green/yellow 12/4mm |
| 700-4611 | Heatshrink tube green/yellow 18/6mm |
| 700-4618 | Heatshrink tube green/yellow 24/8mm |