


AMP Mini CT

TE Internal #: 292206-3
PCB Mount Header, Right Angle, Wire-to-Board, 3 Position, 1.5 mm
[.059 in] Centerline, Fully Shrouded, Tin (Sn), Through Hole - Solder,
AMP Mini CT

[View on TE.com >](#)



Connectors > PCB Connectors > PCB Headers & Receptacles > MINI COMMON TERMINATION HEADERS



PCB Connector Type: **PCB Mount Header**
PCB Mount Orientation: **Right Angle**
Connector System: **Wire-to-Board**
Number of Positions: **3**
Number of Rows: **1**

[All MINI COMMON TERMINATION HEADERS \(39\)](#)

Features

Product Type Features

PCB Connector Type	PCB Mount Header
Connector System	Wire-to-Board
Header Type	Fully Shrouded
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board
Connector Product Type	Connector Assembly

Configuration Features

PCB Mount Orientation	Right Angle
Number of Positions	3
Number of Rows	1

Electrical Characteristics

Operating Voltage	50 VDC
-------------------	--------



Body Features

Primary Product Color	Natural
-----------------------	---------

Contact Features

Contact Mating Area Plating Material Thickness	1 μm[39.37 μin]
Mating Square Post Dimension	.5 mm[.02 in]
PCB Contact Termination Area Plating Material Thickness	1 – 2 μm[39.37 – 78.73 μin]
Contact Shape & Form	Square
Contact Layout	Staggered
Contact Mating Area Length	2.4 mm[.095 in]
Contact Base Material	Brass
PCB Contact Termination Area Plating Material	Tin
Contact Mating Area Plating Material Finish	Matte
Contact Mating Area Plating Material	Tin (Sn)
Contact Type	Pin
Contact Current Rating (Max)	2 A

Termination Features

Termination Post & Tail Length	3 mm[.118 in]
Square Termination Post & Tail Dimension	.5 mm[.02 in]
Termination Method to PCB	Through Hole - Solder

Mechanical Attachment

Panel Mount Feature	With
Mating Retention	With
Mating Alignment Type	Polarization
PCB Mount Retention Type	Kinked Legs
PCB Mount Retention	With
PCB Mount Alignment	With
Connector Mounting Type	Board Mount
Mating Alignment	With

Housing Features

Housing Material	Nylon(G.F)
Centerline (Pitch)	1.5 mm[.059 in]

Dimensions

--	--



Connector Width	4.9 mm[.192 in]
PCB Thickness (Recommended)	1.6 mm[.063 in]
Connector Height	8.45 mm[.332 in]
Connector Length	7 mm[.276 in]

Usage Conditions

Operating Temperature Range	-30 – 105 °C[-22 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Assembly Process Feature	Pick and Place Cover
Circuit Application	Signal

Industry Standards

Compatible With Agency/Standards Products	CSA, UL
Compatible With Approved Standards Products	CSA LR7189, UL E28476
UL Flammability Rating	UL 94V-0

Packaging Features

Packaging Quantity	2100
Packaging Method	Box, Tray

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Wave solder capable to 265°C


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products






will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 1-353293-3 MINI CT MT REC ASSY 13P GRAY	 TE Part # 2058943-2 Cable Assembly Mini CT 3 pos.	 TE Part # 353293-3 MINI CT MT REC ASSY 3P GRAY	 TE Part # 2-179694-3 2MM CT MT REC ASSY 3P GRAY
 TE Part # 1903108-1 MINI CT CABLE ASSY 3P REC GOLD PLT.	 TE Part # CAT-AM7053-C7671 Mini Common Termination Contacts	 TE Part # CAT-AM7053-H8172 Mini Common Termination (CT) Housings	 TE Part # 2-353293-3 1.5MM CT MT REC ASS'Y 3P BLACK
 TE Part # 5-353293-3 MINI CT MT REC ASSY 3P BLUE	 TE Part # 2405870-3 CT 3P 300MM CABLE ASSEMBLY 6-353908-3		

Also in the Series | AMP Mini CT

 Connector Contacts(4)	 Connector Hardware(10)	 PCB Headers & Receptacles(332)	 Wire-to-Board Connector Assemblies & Housings(172)
--	--	---	---



Wire-to-Board Headers & Receptacles
(332)

Customers Also Bought



TE Part #3-353293-2
1.5MM CT MT REC ASSY 12P BLACK



TE Part #1-292207-8
MINI CT SGL DIP V 18P NAT



TE Part #292230-5
1.5 MINI CT SGL V SMT W/BOSS 5



TE Part #292207-8
MINI CT SGL DIP V 8P NAT



TE Part #292207-9
MINI CT SGL DIP V 9P NAT



TE Part #1-292207-5
MINI CT SGL DIP V 15P NAT




TE Part #2-292208-2
MINI CT D/R DIP 22P V NAT



TE Part #3-292208-0
MINI CT D/R DIP 30P V NAT



TE Part #1-292207-1
MINI CT SGL DIP V 11P NAT



TE Part #8-292112-3
MT REC ASSY (#26,28)

Documents

- CAD Files
- 3D PDF
- 3D
- Customer View Model
- ENG_CVM_CVM_292206-3_E1.2d_dxf.zip
- English
- Customer View Model
- ENG_CVM_CVM_292206-3_E1.3d_igs.zip



English

Customer View Model

[ENG_CVM_CVM_292206-3_E1.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

[Application Specification](#)

English

Agency Approvals

[UL](#)

English