

## zce01

limit switch head ZCE - without lever spring return left and right actuation



### Main

Range of product	OsiSense XC
Series name	Standard format
Product or component type	Limit switch head
Device short name	ZCE
Head type	Rotary head
Product compatibility	XCKD XCKP XCKT XCMD
Associated lever	ZCY12 ZCY15 ZCY16 ZCY17 ZCY18 ZCY19 ZCY22 ZCY23 ZCY25 ZCY26 ZCY39 ZCY44 ZCY45 ZCY46 ZCY48 ZCY49 ZCY53 ZCY54 ZCY55 ZCY59 ZCY69 ZCY81 ZCY91
Associated body	ZCD21 ZCD21M12 ZCD25 ZCD26 ZCD27 ZCD28 ZCD29 ZCD29M12 ZCD31 ZCD35 ZCD37 ZCD39 ZCMD21C12 ZCMD21L08R12 ZCMD21L08U78 ZCMD21L1 ZCMD21L2 ZCMD21L5 ZCMD21M12 ZCMD25L1 ZCMD25L2 ZCMD25L5 ZCMD29C12 ZCMD29L1 ZCMD29L2 ZCMD29L5 ZCMD37L1 ZCMD37L2 ZCMD37L5 ZCMD39L1 ZCMD39L2

The information provided in this documentation contains general descriptions and/or technical characteristics of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

ZCMD39L5  
 ZCMD41L1  
 ZCMD41L2  
 ZCMD41L5  
 ZCMD61C12  
 ZCMD61M12  
 ZCMD69C12  
 ZCMD81L1  
 ZCMD81L2  
 ZCMD81L5  
 ZCP21  
 ZCP21M12  
 ZCP25  
 ZCP26  
 ZCP27  
 ZCP28  
 ZCP29  
 ZCP29M12  
 ZCP31  
 ZCP35  
 ZCP37  
 ZCP39  
 ZCT21G11  
 ZCT21N12  
 ZCT21P16  
 ZCT25G11  
 ZCT25N12  
 ZCT25P16  
 ZCT26G11  
 ZCT26N12  
 ZCT26P16  
 ZCT27G11  
 ZCT27N12  
 ZCT27P16  
 ZCT28G11  
 ZCT28N12  
 ZCT28P16

Movement of operating head	Rotary
Type of operator	Without operating lever spring return metal
Type of approach	Lateral approach 2 directions

### Complementary

Positive opening	With
------------------	------

### Environment

Ambient air temperature for operation	-25...70 °C
Ambient air temperature for storage	-40...70 °C
Environmental characteristic	Standard environment

### Offer Sustainability

Sustainable offer status	Green Premium product
RoHS	Compliant - since 0851 - Schneider Electric declaration of conformity
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations