

KSB630SE5

Tap off unit, Canalis KS 500A to 1000A, with fuse holder, 630A, blade size 3 fuses not supplied, 3L+PEN, IP55, RAL9001



Main

Range of product	Canalis
Range compatibility	Canalis KS busbar trunking
Product or component type	Tap-off unit
Busbar trunking compatibility	Canalis KS busbar trunkingplug-in
[Ie] rated operational current	630 A at 35 °C
Protection type	Fuse isolator: blade type fuse, size 3 conforming to NF or DIN
Provided equipment	Fuse to be ordered separately
Mounting mode	Plug-in with fixed polarity
Tap-off unit polarity	3L+PEN
Colour	White (RAL 9001)

Complementary

Device application	Medium power distribution
[Uimp] rated impulse withstand voltage	6.8 kV
[Ui] rated insulation voltage	500 V depending on protective device
Network frequency	50/60 Hz
Electrical connection	Copper cable lug - ISO40 480 mm ² flexible Copper cable lug - ISO40 480 mm ² rigid
Door/cover opening side	Right
Tap-off unit disconnection mode	By opening the door
Standards	IEC 61439-1 IEC 61439-6
Body material	Metal
Width	1144.5 mm
Depth	300 mm
Depth (door open)	1106.5 mm
Height	611 mm
Net weight	59 kg

Environment

Earthing system	TN-C
IP degree of protection	IP55 conforming to IEC 60529
IK degree of protection	IK08 conforming to IEC 62262

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
RoHS exemption information	Yes

China RoHS Regulation	 China RoHS Declaration
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	No need of specific recycling operations
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins