


Parker Product Datasheet



This polyurethane recoil tubing is perfect for installations requiring flexibility in confined spaces. Good resistance to shock and abrasion, together with a design integrating straight ends, allow for easy and safe operation of pneumatic equipment.

PART NUMBER: 1462U08 04
CONNECTION 1 THREAD SIZE (METRIC): na
TUBING MATERIAL: PU
LENGTH (M): 6
COLOR: BLUE
INSIDE DIAMETER: 5 mm
OUTSIDE DIAMETER: 8 mm

PRODUCT OVERVIEW

With its small coil diameter and good impact resistance, this polyurethane recoil tubing is perfect for installations requiring flexibility in confined spaces.

Good resistance to shock and abrasion, together with a design integrating straight ends, allow for easy and safe operation of pneumatic equipment.

Features/Benefits:

- Excellent Mechanical Properties
- Excellent coil memory
- Abrasion-resistant
- Perfect for rapid cycling applications
- Consistent tensile strength

- Optimum longevity
- Low pressure drop
- Lightweight with plastic protection spring
- Silicone-free

- Comprehensive Range

- Available in 2 materials: PU ester and PU ether
- With or without pre-assembled fittings
- Pre-assembled plastic or metal protection springs to prevent damage to equipment and tubing

Markets:

- Machine Tools
- Primary Metal Refining and Processing
- Miscellaneous Manufacturing
- Vehicle Assembly Facilities
- Transportation

Applications:

- Compressed Air and Lubricants Conveying
- Maintenance Workshop
- Industrial Cleaning
- Car Washing
- Power Hand Tools

Technologies:

- PU Tubing
- Polyurethane Tubing
- Recoil Tubing
- Industrial Tubing

Technical Characteristics:

- Fluids: Compressed air
- Materials: Polyurethane (52 Shore D)
- Pressure: 0 to 10 bar
- Temperature: -20°C to +70°C (assembled tubing)

Regulations:

Industrial

- NF E49-101
- DI: 2002/95/EC (RoHS), 2011/65/EC
- DI: 97/23/EC (PED)
- RG: 1907/2006 (REACH)

Product Types:

- Polyurethane (PU) Ester Recoil Tubing
- Recoil Polyurethane (PU) Ether Tubing
- Push-in Fitting with Protection Spring

TECH SPECIFICATIONS

MAXIMUM OPERATING PRESSURE	10 bar
WEIGHT	0.337 kg
SPECIFICATIONS MET	REACH (Industrial)
MAXIMUM OPERATING TEMPERATURE	70 °C
SPECIFICATIONS MET	RoHS (Industrial)
SPECIFICATIONS MET	NF E49-101 (Industrial)
SPECIFICATIONS MET	PED (Industrial)
MEDIA	Air (Compressed Air)
NUMBER OF TUBES	1
APPLICATION	Robotics
APPLICATION	Pneumatics
APPLICATION	Motion Technologies
APPLICATION	Tooling
MINIMUM OPERATING TEMPERATURE	-20 °C
APPLICATION	Industrial Machinery
DIVISION	Low Pressure Connectors Europe Division

APPLICATION

Workshops

DIVISION

Low Pressure Connectors Europe Division