



Chemical protection

BUTOFLEX 652

short wear

Ultimate specific chemical resistance



CHEMICAL PROTECTION
TYPE A

EN388



0010X

EN ISO 374-1



TYPE A
ABCILMNOS

EN ISO 374-5



EN 16350



CATEGORY 3



0334

DEXTERITY

EN ISO 21420:
5/5

SPECIFIC ADVANTAGES



Protection of electronic device from ElectroStatic Discharge (ESD)

- In compliance with the requirement of the norm EN 16350, standard for protective gloves - Electrostatic properties : $<1.0 \cdot 10^5$



Comfort

- Unrivalled flexibility and dexterity



Skin protection

- Ultimate specific chemical resistance, for very corrosive acids, ketones, esters and amine derivatives



Guaranteed quality

- Silicone free to prevent traces, defects on metal sheet and glass prior to painting

INDUSTRIES

- Mechanical industry
- Chemical industry
- Cosmetics and Pharmaceutical industry

APPLICATIONS

- Metal treatment and degreasing
- Formulating paints, varnishes, resins and inks
- Handling and repackaging chemicals
- Sampling chemicals
- Handling in laboratories



Chemical protection

BUTOFLEX 652

short wear

LEGENDS

EN388	MECHANICAL HAZARDS
	PERFORMANCE LEVELS (X = NOT TESTED)
0 0 1 0 X	
0-4 0-5 0-4 0-4 A-F P	
	Impact protection (optional)
	Cut resistance according to ISO 13997
	Puncture resistance
	Tear resistance
	Blade cut resistance
	Abrasion resistance

EN ISO 374-1	CHEMICAL RISKS
	A: Methanol
TYPE A	B: Acetone
	C: Acetonitrile
	I: Ethyl acetate
	L: Sulphuric acid 96%
	M: Nitric acid 65%
	N: Acetic acid 99%
	O: Ammonia 25%
	S: Hydrofluoric acid 40%

EN 16350	PROTECTION AGAINST STATIC ELECTRICITY

EN ISO 374-5	MICRO-ORGANISMS
	Protection against bacteria and fungi

PRODUCT DETAILS

Interior finish	Smooth
Exterior finish	Smooth
Material	Butyl
Cuff characteristic	Rolled Cuff
Colour.s	Black
Length (cm)	35
Thickness (mm)	.70
European sizes	7 8 9 10
Vertical resistance according to EN1149-2 (Value in palm area at 25% relative humidity)	7.61 E+05 Ω

LOGISTIC DETAILS

Packaging	1 pair/bag 6 pairs/carton
-----------	------------------------------

LEGISLATION

- This product is not classified hazardous according to the regulation (EC) n°1272/2008 of the European Parliament and of the Council.
- This product does not contain more than 0.1 % of substance of very high concern (SVHC) or any substance included in the annex XVII of the regulation n° 1907/2006 of the European Parliament and of the Council (REACH).
- UE type certificate or CE type examination certificate: 0075/014/162/08/24/1990
- Issued by the notified body nr: 0075 CTC - 4, rue Hermann Frenkel - 69367 Lyon Cedex 07- FRANCE
- Quality assurance certificat: 0334 - Asqual 14 rue des Reculettes -75013 Paris - France