

## Electronic housing - ME MAX 12,5 G 3-3 TBUS KMGY - 2279017

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (http://phoenixcontact.com/download)



Complete housing without vents, Cross connection: DIN rail bus connector, Color: light gray, Width: 12.5 mm, Constructional height: 114.5 mm, Number of positions cross connector: 5

#### Why buy this product

- Available in overall widths from 6.2 mm to 90 mm, modular extension is possible
- ☑ Inflammability class V0 according to UL 94
- ✓ Variety of connection technologies
- Can be mounted on the DIN rail
- Optional with bus connector for DIN rail mounting as well as power connection system





#### Key commercial data

Packing unit	10 pc
Minimum order quantity	10 pc
GTIN	4 046356 180597
Weight per Piece (excluding packing)	45.0 g
Custom tariff number	85472000
Country of origin	Germany
Note	Made to Order (non-returnable)

#### Technical data

#### General

Housing type	Complete housing
Housing material	Polyamide
Color	light gray

#### Ambient conditions

Ambient temperature (operation)	-40 °C (depending on power dissipation)



# Electronic housing - ME MAX 12,5 G 3-3 TBUS KMGY - 2279017

## Technical data

#### Dimensions

Constructional height	114.5 mm
Width	12.5 mm

#### Technical data

Inflammability class according to UL 94	V0
Power dissipation at 20°C in the horizontal mounting position	4.3 W 7.1 W

## Classifications

#### eCl@ss

eCl@ss 4.0	27180401
eCl@ss 4.1	27180401
eCl@ss 5.0	27180506
eCl@ss 5.1	27180506
eCl@ss 6.0	27180802
eCl@ss 7.0	27182702
eCl@ss 8.0	27182702

#### **ETIM**

ETIM 2.0	EC001031
ETIM 3.0	EC001031
ETIM 4.0	EC001031
ETIM 5.0	EC001031

#### **UNSPSC**

UNSPSC 6.01	31261501
UNSPSC 7.0901	31261501
UNSPSC 11	31261501
UNSPSC 12.01	31261501
UNSPSC 13.2	31261501

## Approvals

#### Approvals

Approvals

UL Recognized

Ex Approvals



# Electronic housing - ME MAX 12,5 G 3-3 TBUS KMGY - 2279017

# Approvals Approval submitted Approval details UL Recognized

Phoenix Contact 2015 @ - all rights reserved http://www.phoenixcontact.com