


Connectors in 3.81 mm pitch Series BC/SC 3.81

SC 3.81/././90



Male header with plugging direction in parallel to the circuit board.

- Available in closed (G) version and with screw flange (F)

Weidmüller's 3.81-mm-pitch (0.15 inch) plug-in connectors are compatible with the layouts of standard connectors. They support a flood-light display and offer space for labelling and coding.

Product data

IEC: 320 V / 17.5 A
UL: 300 V / 10 A

For additional articles and information, refer to catalog.weidmueller.com


Note:

- Additional colours on request
- Gold-plated contact surfaces on request
- Rated current related to rated cross-section and min. No. of poles.
- Rated data refer only to the component itself. Clearance and creepage distances to other components are to be designed in accordance with the relevant application standards.
- P on drg. = pitch

SC 3.81/././90G



Dimensioned drawing



Technical data

In compliance with IEC 60664-1 / IEC 61984

Clamping range, max.	mm ²		
Solid core H05(07) V-U	mm²		
Stranded H07 V-R			
Flexible H05(07) V-K	mm ²		
Flexible with ferrule	mm ²		
Ferrule with plastic collar	mm ²		
Stripping length	mm		
Screwdriver blade	mm		
According to norm			
Tightening torque range	Nm		
Rated current, max.	A	17.5	17.5
At ambient temperature		20°C	40°C
For conductor cross-section	mm ²		
Overvoltage category		III	III
Pollution severity		3	2
Rated voltage	V	160	160
Rated impulse voltage	kV	2.5	2.5
UL / CUL (Use Group)		B	C
Rated voltage	V	300	300
Rated current	A	10	10
AWG conductor	AWG		-
CSA (Use Group)		B	C
Rated voltage	V	300	300
Rated current	A	10	10
AWG conductor	AWG		-
General data			
Type of insulation material		PA GF	
Flammability class UL 94		V-0	
Contact base material		Copper alloy	
Material of contact surface		tinned	
Pin dimensions = d	mm	1.0, Octagonal	
Solder eyelet Ø = D	mm	1.2	
Solder eyelet Ø tolerance	mm	+ 0,1	

Accessories

Note: Refer to the Accessories chapter for additional accessories.

Coding	Order No.
SC-SMT 3.81 KO GR	1968900000

Ordering data

Solder pin length	3.2 mm	3.2 mm			
Colour	orange	black			
Pitch	3.81 mm				
Pol.	L1 (inch)	Qty.	Order No.	Order No.	
2	3.81	0.150	50	1942020000	1793130000
3	7.62	0.300	50	1942040000	1793140000
4	11.43	0.450	50	1942070000	1793150000
5	15.24	0.600	50	1942090000	1793160000
6	19.05	0.750	50	1942100000	1793170000
7	22.86	0.900	50	1942120000	1942350000
8	26.67	1.050	50	1942130000	1793180000
9	30.48	1.200	50	1942140000	1942360000
10	34.29	1.350	50	1942150000	1793190000
11	38.10	1.500	50	1942160000	1942370000
12	41.91	1.650	50	1942170000	1793200000
13	45.72	1.800	50	1942180000	1942380000
14	49.53	1.950	50	1942190000	1942390000
15	53.34	2.100	50	1942200000	1942400000
16	57.15	2.250	50	1942210000	1793210000
17	60.96	2.400	50	1942220000	1942410000
18	64.77	2.550	50	1942230000	1942420000
19	68.58	2.700	50	1942240000	1942430000
20	72.39	2.850	50	1942250000	1942440000