

SAC-5P-MS/ 3,0-920/FS SCO - Bus system cable



1410380

<https://www.phoenixcontact.com/gb/products/1410380>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Bus system cable, CANopen®, DeviceNet™, 5-position, PUR halogen-free, red lilac RAL 4001, shielded, Plug straight M12 SPEEDCON, coding: A, on Socket straight M12 SPEEDCON, coding: A, cable length: 3 m

Commercial data

Item number	1410380
Packing unit	1 pc
Minimum order quantity	10 pc
Note	Made to order (non-returnable)
Sales key	AF1CKD
Product key	AF1CKD
GTIN	4046356896672
Weight per piece (including packing)	209.2 g
Weight per piece (excluding packing)	205.1 g
Customs tariff number	85444290
Country of origin	PL

Technical data

Product properties

Product type	Data cable preassembled
Application	Bus system
Sensor type	CANopen®
Number of positions	5
No. of cable outlets	1
Shielded	yes
Coding	A

Insulation characteristics

Overvoltage category	II
Degree of pollution	3

Interfaces

Bus system	CANopen®/DeviceNet™
Signal type/category	CANopen®
	DeviceNet™

Signaling

Status display	no
Status display present	no

Electrical properties

Insulation resistance	≥ 100 MΩ
Nominal voltage U _N	48 V AC
	60 V DC
Nominal current I _N	4 A
Transmission medium	Copper

Material specifications

Flammability rating according to UL 94	HB
Seal material	NBR
Material of grip body	TPU, hardly inflammable, self-extinguishing
Contact material	CuSn
Contact surface material	Ni/Au
Contact carrier material	TPU GF
Material for screw connection	Zinc die-cast, nickel-plated

Connector

Connection 1

Type	Plug straight M12 SPEEDCON
Number of positions	5

SAC-5P-MS/ 3,0-920/FS SCO - Bus system cable



1410380

<https://www.phoenixcontact.com/gb/products/1410380>

Locking type	SPEEDCON
Coding type	A (Standard)

Connection 2

Type	Socket straight M12 SPEEDCON
Number of positions	5
Locking type	SPEEDCON
Coding type	A (Standard)

Cable/line

Cable length	3 m
--------------	-----

CANopen®/DeviceNet™, PUR, violet [920]

Dimensional drawing		
UL AWM Style	21198 (80°C/300 V)	
Number of positions	4	
Shielded	yes	
Cable type	CANopen®/DeviceNet™, PUR, violet [920]	
Conductor structure	2xAWG24/19+2xAWG22/19	
AWG signal line	24	
AWG power supply	22	
Conductor cross section	2x 0.25 mm² (Data cable)	
	2x 0.34 mm² (Power supply)	
	1x 0.34 mm² (Drain wire)	
Wire diameter incl. insulation	1.95 mm ±0.05 mm (Data cable)	
	1.4 mm ±0.05 mm (Power supply)	
External cable diameter	6.70 mm ±0.3 mm	
Outer sheath, material	PUR	
External sheath, color	red lilac RAL 4001	
Conductor material	Tin-plated Cu litz wires	
Material wire insulation	Foamed PE (Data cable)	
	PE (Power supply)	
Single wire, color	red-black, blue-white	
Twisted pairs	2 cores to the pair	
Overall twist	2 pairs around a drain wire in the center to the core	
Optical shield covering	80 %	
Insulation resistance	≥ 5 GΩ*km (Data cable)	
	≥ 5 GΩ*km (Power supply)	

SAC-5P-MS/ 3,0-920/FS SCO - Bus system cable



1410380

<https://www.phoenixcontact.com/gb/products/1410380>

Wave impedance	120 Ω $\pm$ 10 % (with 1 MHz)
Nominal voltage, cable	$\leq$ 300 V (Peak value, not for high-power applications)
Test voltage Core/Core	2000 V (50 Hz, 1 min.)
Test voltage Core/Shield	2000.00 V (50 Hz, 1 min.)
Minimum bending radius, fixed installation	4 x D
Minimum bending radius, flexible installation	8 x D
Dynamic load capacity (bending)	Max. bending cycles: 5000000, Bending radius: 70 mm, Bending radius: 15 x D, Traversing path: 4.5 m, Traversing rate: 3 m/s, Acceleration: 3 m/s ² , Ambient temperature: -20 °C ... 60 °C
Shield attenuation	$\leq$ 22.9 dB/km (with 1 MHz)
	$\leq$ 16.4 dB/km (At 500 kHz)
	$\leq$ 9.5 dB/km (At 125 kHz)
Halogen-free	in accordance with DIN VDE 0472 part 815
	according to IEC 60754-1
Flame resistance	UL 1581, Section 1060 and UL 2556, Section 9.3 (FT1)
	UL 1581, Section 1100 and UL 2556, Section 9.1 (HFT/FT2)
	IEC 60332-1-2
	in accordance with ISO 6722-1 5.22 (UN ECE-R 118.01)
Ambient temperature (operation)	-40 °C ... 80 °C (cable, fixed installation)
	-30 °C ... 70 °C (Cable, flexible installation)
	-20 °C ... 60 °C (for installation)
	-20 °C ... 60 °C (cable, drag chain applications)

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP65
	IP67
Ambient temperature (operation)	-25 °C ... 90 °C (Plug / socket)
	-40 °C ... 80 °C (cable, fixed installation)
	-20 °C ... 75 °C (Cable, flexible installation)

Drawings

Dimensional drawing



Plug, M12 x 1, straight, shielded

Dimensional drawing



M12 x 1 socket, straight, shielded

Schematic diagram




Pin assignment M12 male connector, 5-pos., A-coded, male side

Schematic diagram



Pin assignment M12 socket, 5-pos., A-coded, socket side view

Circuit diagram



SAC-5P-MS/ 3,0-920/FS SCO - Bus system cable



1410380

<https://www.phoenixcontact.com/gb/products/1410380>

Classifications

ECLASS

ECLASS-13.0	27060307
-------------	----------

ETIM

ETIM 9.0	EC001855
----------	----------

UNSPSC

UNSPSC 21.0	26121600
-------------	----------

SAC-5P-MS/ 3,0-920/FS SCO - Bus system cable



1410380

<https://www.phoenixcontact.com/gb/products/1410380>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk