

**BOSCH**

Invented for life

Product data sheet

Power tools for trade & industry

Rotary Hammer with SDS max

PRO GBH 12-52 D



Bosch's most heavy-duty SDS max rotary hammer

The most important data

Rated input power	1,700 W
Impact energy	19 J
Drilling dia. concrete, hammer drill bits	12 – 52 mm

Part Number 0 611 266 160

Technical data

Performance data

Impact rate at rated speed	1,025 – 2,100 bpm
Rated speed	105 – 215 rpm

Technical data

Tool holder	SDS max
Impact energy	19 J
Rated input power	1,700 W
Weight	11.5 kg
Packaging dimensions (width x length x height)	499 x 685 x 154 mm
Voltage, electrical	110 V

Drilling range

Drilling dia. concrete, hammer drill bits	12 – 52 mm
Opt. appl. range concrete, hammer drill bits	30 – 50 mm
Drilling dia. concrete, breakthrough drill bits	80 – 80 mm
Drilling diameter in concrete with core cutters	50 – 150 mm

Drilling range

Drilling dia. concrete, hammer drill bits	12 – 52 mm
Opt. appl. range concrete, hammer drill bits	30 – 50 mm
Drilling dia. concrete, breakthrough drill bits	80 – 80 mm

Drilling diameter in concrete with core cutters	50 – 150 mm
---	-------------

Drilling range

Drilling dia. concrete, hammer drill bits	12 – 52 mm
Opt. appl. range concrete, hammer drill bits	30 – 50 mm
Drilling dia. concrete, breakthrough drill bits	80 – 80 mm
Drilling diameter in concrete with core cutters	50 – 150 mm

Drilling range

Drilling dia. concrete, hammer drill bits	12 – 52 mm
Opt. appl. range concrete, hammer drill bits	30 – 50 mm
Drilling dia. concrete, breakthrough drill bits	80 – 80 mm
Drilling diameter in concrete with core cutters	50 – 150 mm

Noise/vibration information

Hammer drilling in concrete

Vibration emission value ah	16.4 m/s ²
Uncertainty K	1.5 m/s ²



Product data sheet

Power tools for trade & industry

Chiselling in concrete

Vibration emission value ah	15.4 m/s ²
Uncertainty K	1.5 m/s ²



Product data sheet

Power tools for trade & industry

Advantages:

- High-end motor for ultimate performance in SDS max tasks
- Powerful motor enables the delivery of 19 J of impact energy for heavy chiselling
- Highly durable due to extremely robust metal components



You can find more information about the deviations in the following link: <https://www.bosch-professional.com/gb/en/wac/>

