

8EI017HWDS0.XXXX-1

1 Order data

Order number	Short description	Figure
	Wall mounting	
8EI017HWDS0.XXXX-1	ACOPOS P3 servo drive, 3x200-480 VAC, 2x 17 A, SafeMOTION, 2 axes, wall mounting	
	Optional accessories	
	Display modules	
8EAD0000.000-1	Display module, LCD, 128 x 64, black/white, 1x USB 3.0	
	Front covers	
8EXA300.0010-00	ACOPOS P3 cover, B&R orange, double-width, suitable for servo drives 8EI017xxDxx.xxxx-x / 8EI022xxDxx.xxxx-x / 8EI024xxSxx.xxxx-x / 8EI034xxSxx.xxxx-x / 8EI044xxSxx.xxxx-x	
8EXA300.0020-00	ACOPOS P3 cover, B&R dark gray, double-width, suitable for servo drives 8EI017xxDxx.xxxx-x / 8EI022xxDxx.xxxx-x / 8EI024xxSxx.xxxx-x / 8EI034xxSxx.xxxx-x / 8EI044xxSxx.xxxx-x	
	Passive line filter	
8B0F0160H000.A00-1	Passive line filter, 16 A, 3x 480 VAC, 50/60 Hz, IP20	
8B0F0300H000.000-1	Passive line filter, 30 A, 3x 520 VAC, 50/60 Hz, IP20	
8B0F0550H000.000-1	Passive line filter, 55 A, 3x 520 VAC, 50/60 Hz, IP20	
	Plug-in modules	
8EAC0122.001-1	ACOPOS P3 plug-in module, resolver interface 10 kHz	
8EAC0122.003-1	ACOPOS P3 plug-in module, 3 resolver interfaces 10 kHz	
8EAC0130.000-1	ACOPOS P3 plug-in module, 8 digital I/O 24 V (4x 400 mA, 4x 100 mA) individually configurable as inputs or outputs, 2 digital I/O 24 V 2 A configurable in pairs as inputs or outputs, order terminal block 8TB0230.221A-00 separately!	
8EAC0150.001-1	ACOPOS P3 plug-in module, digital multi-encoder interface	
8EAC0150.003-1	ACOPOS P3 plug-in module, 3 digital multi-encoder interfaces	
8EAC0151.001-1	ACOPOS P3 plug-in module, incremental encoder interface	
8EAC0151.003-1	ACOPOS P3 plug-in module, 3 incremental encoder interfaces	
8EAC0152.001-1	ACOPOS P3 plug-in module, analog multi-encoder interface	
8EAC0152.003-1	ACOPOS P3 plug-in module, 3 analog multi-encoder interfaces	
	Shield component sets	
8SCSE01.0200-00	ACOPOS P3 shield component set: 1x ACOPOS P3 shield mounting plate, 2x 2x M3x6 screws	
8SCSE02.0100-00	ACOPOS P3 shield component set: 1x shield component set, type SK14	
8SCSE02.0200-00	ACOPOS P3 shield component set: 1x shield component set, type SK20	
	Terminals	
8TB2104.2210-00	Push-in terminal block 4-pin, 1-row, pitch: 5.08 mm, label 1: numbered consecutively	
8TB3102.222C-20	Push-in terminal block, 2-pin, single row, with locking mechanism, spacing: 7.62 mm, label 2: COM 24 V, C keying: 10	
8TB3202.222C-40	Push-in terminal block, 2-pin, 2-row, with locking mechanism, spacing: 7.62 mm, label 2: COM 24 V, C keying: 10	
8TB3308.222A-00	4+4-pin push-in terminal block 1-row / 2-row, pitch: 7.62 mm, label 2: T- B- T+ B+ PE W V U coding A: 0000	
8TB4103.222A-10	Push-in terminal block, 3-pin, 1-row, spacing: 10.16 mm, label 2: PE RB- RB+, A keying: 000	
8TB4104.222L-10	Push-in terminal block, 4-pin, 1-row, spacing: 10.16 mm, label 2: PE L3 L2 L1, L keying: 1010	
8TB4104.227F-10	Push-in terminal block, 4-pin, 1-row, spacing: 10.16 mm, label 4: DC-, DC-, DC+, DC+ F keying: 0101	
8TB4204.202L-10	4-pin push-in screw terminal block, 2-row, pitch: 10.16 mm, label 2: PE L3 L2 L1, coding L: 1010	

Table 1: 8EI017HWDS0.XXXX-1 - Order data

2 Technical data

Order number	8EI017HWDS0.XXXX-1
General information	
Slots for plug-in modules	1
Certifications	
CE	Yes
UL	cULus E225616
EAC	Power conversion equipment
KC	Yes
	In preparation
Mains connection	
Network configurations	TN-S, TN-C-S with grounded neutral
Mains input voltage	3x 200 VAC to 480 VAC $\pm 10\%$
Frequency	50 / 60 Hz $\pm 4\%$
Installed load	Max. 26.4 kVA
Inrush current	100 A
Switch-on interval	In preparation
Integrated line filter per EN 61800-3, category C3	No ¹⁾
Terminal connection cross section	
Flexible and fine-stranded wires	
With wire end sleeves	0.75 to 16 mm ²
Approbation data	
UL/C-UL-US	20 to 4 AWG
CSA	20 to 4 AWG
Power dissipation at device nominal power without braking resistor	In preparation
Max. line length	3 m ²⁾
DC bus connection	
Continuous power ³⁾	14 kW ⁴⁾
Reduction of continuous power depending on mains input voltage	
Mains input voltage <3x 400 VAC	14 kW * (Mains input voltage [V] / 400 V)
DC bus capacitance	1680 μ F
Terminal connection cross sections	
Flexible and fine-stranded wires	
With wire end sleeves	0.75 to 16 mm ²
Approbation data	
UL/C-UL-US	20 to 4 AWG
CSA	20 to 4 AWG
Max. line length	3 m ⁵⁾
24 VDC power supply	
Input voltage	24 VDC $\pm 25\%$
Input capacitance	5500 μ F
Current consumption	2.4 A + Current for motor holding brake ⁶⁾⁷⁾
Terminal connection cross sections	
Flexible and fine-stranded wires	
With wire end sleeves	0.25 to 4 mm ²
Approbation data	
UL/C-UL-US	24 to 8 AWG
CSA	24 to 8 AWG
Max. line length	30 m
Motor connection	
Quantity	2
Continuous power per motor connection ⁸⁾	7 / 7 kW ⁴⁾
Continuous current per motor connection ⁸⁾	17 / 17 A _{eff}
Accuracy of the safe current ⁹⁾	
Safety function SLT ¹⁰⁾	
SIL 2 / PL d / Cat. 3 ¹¹⁾	Hardware upgrade 1.10.2.x: 3.030 A
SIL 2 / PL d / Cat. 2 ¹¹⁾	Hardware upgrade 1.10.3.0 or later: 2.611 A
Safety function SBT ¹⁰⁾	1.404 A
SIL 2 / PL d / Cat. 3 ¹¹⁾	Hardware upgrade 1.10.2.x: 2.308 A
SIL 2 / PL d / Cat. 2 ¹¹⁾	Hardware upgrade 1.10.3.0 or later: 1.868 A
	0.900 A

Table 2: 8EI017HWDS0.XXXX-1 - Technical data

Order number	8EI017HWDS0.XXXX-1
Reduction of continuous current depending on ambient temperature	
Mains input voltage: 400 VAC	
Switching frequency 5 kHz	No reduction
Switching frequency 10 kHz	0.195 A/K (starting at 16°C) ¹²⁾
Switching frequency 20 kHz	0.145 A/K (starting at -59°C) ¹²⁾
Mains input voltage: 480 VAC	
Switching frequency 5 kHz	0.345 A/K (starting at 44°C) ¹²⁾
Switching frequency 10 kHz	0.210 A/K (starting at -5°C) ¹²⁾
Switching frequency 20 kHz	0.145 A/K (starting at -87°C) ¹²⁾
Reduction of continuous current depending on installation elevation	
Starting at 500 m above sea level	1.7 A _{eff} per 1000 m
Peak current per motor connection	42.5 / 42.5 A _{eff}
Peak power output	17.5 / 17.5 kW
Nominal switching frequency	5 kHz
Possible switching frequencies ¹³⁾	5 / 10 / 20 kHz
Insulation stress of the connected motor per IEC TS 60034-25:2004	Limit value curve A
Protective measures	
Overload protection	Yes
Short circuit and ground fault protection	Yes
Max. output frequency	598 Hz ¹⁴⁾
Variant	
U, V, W, PE	Connector
Shield connection	Yes
Terminal connection cross section	
Flexible and fine-stranded wires	
With wire end sleeves	1.5 to 6 mm ²
Approbation data	
UL/C-UL-US	24 to 8 AWG
CSA	24 to 8 AWG
Max. motor cable length depending on switching frequency	
Switching frequency 5 kHz	75 m ¹⁵⁾
Switching frequency 10 kHz	75 m ¹⁵⁾
Switching frequency 20 kHz	30 m ¹⁵⁾
Motor holding brake connection	
Quantity	2
Output voltage ¹⁶⁾	Depends on the input voltage on connector X2
Continuous current	4 A
Max. internal resistance	0.25 Ω
Extinction potential	In preparation
Max. extinction energy per switching operation	In preparation
Max. switching frequency	In preparation
Protective measures	
Overload and short-circuit protection	Yes
Open circuit monitoring	Yes
Undervoltage monitoring	Yes
Response threshold for open circuit monitoring	Max. 70 mA
Response threshold for undervoltage monitoring	Approx. 23 V
Max. breaking current SBC	80 mA
Max. line length	In preparation
Braking resistor ¹⁷⁾	
Peak power output	45 kW
Continuous power	4 kW
Minimum braking resistance (ext.)	13 Ω
Terminal connection cross section	
Flexible and fine-stranded wires	
With wire end sleeves	0.75 to 16 mm ²
Approbation data	
UL/C-UL-US	20 to 4 AWG
CSA	20 to 4 AWG
Protective measures	
Overload protection	No
Short circuit and ground fault protection	Short-circuit protection: Yes Ground fault protection: No
Max. line length	3 m
Fieldbus	
Type	POWERLINK V2 controlled node (CN)
Variant	2x RJ45, shielded, 2-port hub
Line length	Max. 100 m between 2 stations (segment length)
Transfer rate	100 Mbit/s

Table 2: 8EI017HWDS0.XXXX-1 - Technical data

Order number	8EI017HWDS0.XXXX-1
Encoder interfaces	
Quantity	2
Type	Digital multi-encoder interface, configurable ¹⁸⁾
Connections	8-pin female Mini I/O connector
Status indicators	None ¹⁹⁾
Electrical isolation	
Encoder - ACOPOS P3	No
Max. encoder cable length	75 m Depends on the cross section of the power supply wires in the encoder cable ²⁰⁾
Encoder power supply	
Output voltage	Configurable Typ. 11.45 V ± 0.1 V / 5.2 V ± 0.1 V ²¹⁾²²⁾
Load capacity	Max. 300 mA
Sense lines	2, compensation of max. 2x 0.7 V
Protective measures	
Short-circuit proof	Yes
Overload-proof	Yes
Synchronous serial interface	
Signal transmission	RS485 ²³⁾
Data transfer rate	Depends on the configured encoder type
Differential voltage ²⁴⁾	
Minimum	2.0 V
Maximum	6.0 V
Max. power consumption per encoder interface	$P_{\text{ENCODER}} [\text{W}] = U_{24\text{V}} [\text{V}] * (I_{\text{ENCODER}} [\text{A}] * 0.7) + 0.5 \text{ W}$ ²⁵⁾
Trigger inputs	
Quantity	2
Circuit	Sink
Electrical isolation	
Input - ACOPOS P3	Yes
Input - Input	Yes
Input voltage	
Nominal	24 VDC
Maximum	30 VDC
Switching threshold	
Low	<5 V
High	>15 V
Input current at nominal voltage	7 mA
Switching delay	
Rising edge	<51 μs
Falling edge	<52 μs
Modulation compared to ground potential	Max. $\pm 38 \text{ V}$
Terminal connection cross section	
Flexible and fine-stranded wires	
With wire end sleeves	0.25 to 2.5 mm ²
Approbation data	
UL/C-UL-US	26 to 12 AWG
CSA	26 to 12 AWG
Max. line length	100 m
Support	
Motion system	
mapp Motion	5.03.0 and higher
ACP10/ARNC0	5.03.0 and higher
Operating conditions	
Permissible mounting orientations	
Hanging vertically	Yes
Standing horizontally	Yes
Installation elevation above sea level	
Nominal	0 to 500 m
Maximum	4000 m
Pollution degree per EN 61800-5-1	2 (non-conductive pollution)
Overvoltage category per EN 61800-5-1	III
Degree of protection per EN 60529	IP20 ²⁶⁾
Ambient conditions	
Temperature	
Operation	
Minimum	-25°C ²⁷⁾
Nominal	5 to 40°C
Maximum	55°C
Storage	-25 to 55°C
Transport	-25 to 70°C

Table 2: 8EI017HWDS0.XXXX-1 - Technical data

Order number	8EI017HWDS0.XXXX-1
Relative humidity	
Operation	5 to 85%, non-condensing
Storage	5 to 95%
Transport	95% at 40°C
Mechanical properties	
Dimensions	
Width	133 mm
Height	374 mm
Depth	
Wall mounting	258.5 mm (with 8EXA front cover: 261 mm)
Weight	8 kg

Table 2: 8EI017HWDS0.XXXX-1 - Technical data

- 1) A line filter must be connected.
CE compliance can only be ensured by connecting a B&R line filter (8x0F...).
In extreme cases, using line filters from 3rd-party manufacturers can result in irreparable damage to the ACOPOS P3 8EI servo drive.
- 2) Maximum line length between line filter and mains connection on the module.
- 3) Valid for mains input voltage $\geq 3 \times 400$ VAC.
The sum of the continuous power values on all motor connections and the power of the DC bus connector is not permitted to exceed this value.
- 4) The continuous power is reduced as a percentage of the continuous current if the continuous current is subject to derating.
- 5) This value applies to unshielded wiring inside a control cabinet.
Maximum length of the DC bus wiring inside a control cabinet.
- 6) Current consumption depends on the respective configuration of the ACOPOS P3 8EI servo drive.
The inrush current of the 24 VDC power supply is not limited by the module.
- 7) At nominal 24 VDC supply voltage and 20 kHz switching frequency. Without plug-in card.
- 8) Valid under the following conditions: 560 VDC DC bus voltage, 5 kHz switching frequency, 40°C ambient temperature, installation elevation <500 m above sea level, no derating due to cooling type.
- 9) The accuracy of the safe current is relevant for safety functions SLT and SBT, which are based on the safe current measurement. Safety functions SBT, SLT and SSO are available starting with hardware upgrade 1.10.2.0 and only for 8EI servo drives with 8ZELxxxx revision D0 or later. See the device information on the left side cover of the servo drive.
- 10) This safety function is certified for ACOPOS P3 per category 3 as well as category 2 of EN ISO 13849. Depending on the desired category, the corresponding accuracy of the safe current and corresponding safety characteristics must be used.
- 11) These values apply up to the continuous current specified in the technical data (taking into account the respective derating specifications).
- 12) The module cannot supply the full continuous current at this switching frequency. This unusual value for the ambient temperature, at which derating of the continuous current must be taken into account, ensures that the derating of the continuous current can be determined in the same manner as at other switching frequencies.
- 13) B&R recommends operating the module at its nominal switching frequency. Operating the module at a higher switching frequency for application-specific reasons reduces the continuous current and increases CPU utilization.
- 14) The module's electrical output frequency (SCTRL_SPEED_ACT * MOTOR_POLEPAIRS) is monitored to protect against dual use in accordance with Regulation (EC) 428/2009 | 3A225. If the electrical output frequency of the module exceeds the limit value of 598 Hz uninterrupted for more than 0.5 s, then the current movement is aborted and error 6060 is output ("Power unit: Limit speed exceeded").
- 15) The sum of the cable lengths of all motor cables connected to this module is not permitted to exceed this value.
- 16) During configuration, it is necessary to check if the minimum voltage can be maintained on the holding brake with the specified input voltage and wiring. For the operating voltage range of the holding brake, see the user documentation for the motor being used.
- 17) This values apply to an external braking resistor. This module is not equipped with an internal braking resistor.
- 18) The encoder type is not predefined from the factory. The encoder type necessary in each case must be configured in Automation Studio.
- 19) The direction of rotation of the encoder can be displayed on the 8EAD0000.000-1 display module.
- 20) Maximum encoder cable length l_{max} can be calculated as follows (the maximum permissible encoder cable length of 75 m is not permitted to exceeded):

$$l_{max} = f / I_G * A * 1/(2 * \rho)$$

f ... (Output voltage of encoder interface [V] - Min. permissible supply voltage of connected encoder [V]) * 1.1

I_G ... Max. current consumption of the connected encoder [A].

A ... Cross section of the power supply wires [mm²]

ρ ... Specific resistance [Ω mm²/m] (e.g. for copper: $\rho = 0.0178$)

- 21) The output voltage is not predefined from the factory (with the exception of encoder types EnDat 2.2 and HIPERFACE DSL). It must be configured in Automation Studio based on the encoder type. If no output voltage is configured, then the encoder will not be supplied by digital multi-encoder interface X4x. Power to the encoder can then be supplied externally.
- 22) Output voltage 5.2 V is only available under the following conditions:
 - 8EI servo drive with 8ZECxxx revision D0 and higher - see the device information on the left side cover of the 8EI servo drive
 - ACOPOS operating system 3.15.0 and higher (for 8ElxxxxxD... 2-axis modules and 8ElxxxxxT... 3-axis modules)
 - ACOPOS operating system 3.17.0 and higher (for 8ElxxxxxS... 1-axis modules)
- 23) Except encoder type HIPERFACE DSL.
- 24) Values valid for clock output and data input. Except encoder type HIPERFACE DSL.
- 25) $I_{ENCODER}$... Current consumption of the encoder
 U_{24V} ... Input voltage on the +24 VDC input of the module
- 26) The specified degree of protection is only met if either the slot cover is installed on the module or an 8EAC plug-in module is installed and suitable terminals are connected to all connectors and all fans are installed.
- 27) Only permitted for modules with 8ZEL... Revision E0 and higher. See the device information on the left side cover of the module. During storage or transport, sudden temperature changes may cause condensation or icing in the module. The module is only permitted to be commissioned if it is free of condensation or icing at the time of commissioning.

3 Status indicators

3.1 SafeMOTION 2-axis modules



Figure 1: 8EI SafeMOTION servo drives - Status indicators

3.2 POWERLINK - LED status indicators

Label	Color	Description	
PLK	Green	Blinking green (1x)	The client detects a valid POWERLINK frame on the network.
		Blinking green (2x)	Cyclic operation on the network, but the client itself is not yet in cyclic operation.
		Blinking green (3x)	Cyclic operation of the client is in preparation.
		Solid green	The client is in cyclic operation.
		Flickering green	The client is not in cyclic operation and also does not detect any other stations on the network in cyclic operation.
	Red	Solid red	The POWERLINK node number of the module is 0.
		Blinking red/green	The client is in an error state (drops out of cyclic operation).
	Orange	Solid orange	Module booting

Table 3: POWERLINK - LED status indicators

3.3 Ax1/Ax2/Ax3 - LED status indicators

Label	Color	Function	Description	
Ax1 Ax2 Ax3	Green	Ready	Solid green	The module is ready for operation and the power stage can be enabled (operating system present and booted, no pending permanent or temporary errors).
			Blinking green	The module is not ready for operation. Examples: - No signal on one or both enable inputs - DC bus voltage outside the tolerance range - Overtemperature on the motor (temperature sensor) - Motor feedback not connected or defective - Motor temperature sensor not connected or defective - Overtemperature on the module (IGBT junction, heat sink, etc.) - Disturbance on network
	Red	Error	Solid red	There is a permanent error on the module. Examples: - Permanent overcurrent - Invalid data in EPROM
			Blinking red	Burning ACOPOS P3 operating system
	Orange	Run	Solid orange	The module's power stage is enabled.
	---	---	LED off	No voltage being supplied to module

Table 4: Ax1/Ax2/Ax3 - LED status indicators

3.4 LED state during startup

The following intervals are used for the LED status indicators:

Width of box: 50 ms

Repeats after: 3,000 ms




Table 5: LED state during startup

3.5 R/E and SE - LED status indicators

LED	Color		Description
R/E	Green	Red	
	Off	Off	Module not supplied with power, no communication
	Single flash		Mode "Unlink"
	Double flash		Updating firmware
	Blinking		Mode PREOPERATIONAL
	On		Mode RUN
	On	Single flash, inverse	Safety-related firmware invalid
		Triple flash, inverse	Updating safety-related firmware
		On	Communication error
	Off	On	Error
SE	Red	Off	Mode RUN
		On	Non-acknowledgeable error state, FAIL SAFE state

The two "SE" indicators are two separate LEDs that show the states of safety processor 1 and safety processor 2. This is only distinguishable when the front cover is open, however.

Table 6: R/E and SE - LED status indicators

4 Installation

4.1 SafeMOTION double-width modules - Dimension diagram




Figure 2: SafeMOTION double-width modules - Dimension diagram

- 1) Without front cover: 258.5 mm
- 2) Hole for M5 screws.

4.2 Installation dimensions




Figure 3: ACOPOS P3 8EI servo drives - Installation dimensions

- 1) For sufficient air circulation, a clearance of at least 80 mm must be provided above and below the module.
 In order to connect display module 8EAD0000.000-1 to the module without problems, at least 100 mm clearance is necessary above the module.
 In order to ensure easy wiring (taking all minimum bend radii into account), at least 200 mm clearance is necessary below the module.

Caution!

Cooling air exiting the 8EI servo drive can have a temperature up to 90°C. Any components installed near the air outlet must be designed to withstand these high temperatures!

5 Wiring

5.1 Pinout overview




Figure 4: Mains input voltage - 3x 200 to 480 VAC

- 1) A temperature sensor does not need to be connected when using 8ECHxxx hybrid motor cables since the motor temperature is transferred digitally.
- 2) The COM connection on connector X2 must be grounded to achieve a defined relationship between the signal ground and ground potential!
- 3) Only 8EAD0000.000-1 display modules are permitted to be connected to connector X9!

5.2 Connector X1 - Pinout



X1	Description	Function
	L1	Mains connection L1
	L2	Mains connection L2
	L3	Mains connection L3
	PE	Protective ground conductor
Tightening torque for the terminal screws [Nm]: 1.7 to 18 (2-row connectors only)		

Table 7: Connector X1 - Pinout

Information:

Strain relief is required for the cable when using the 2-row connector.

Danger!

During operation, the contacts of connector X1 carry a high voltage if connector X11 is connected. Touching one of these contacts can result in a life-threatening electric shock. This could result in death or severe injury.

For this reason, terminal block 8TB3106.222B-20, 8TB3106.223C-20, 8TB3206.222B-40, 8TB3206.223C-40, 8TB4104.222L-10 or 8TB4204.202L-10 must always be connected to connector X1 during operation.

5.2.1 Mains connection

3x 200 - 480 VAC




Figure 5: Mains connection 3x 200 - 480 VAC

5.3 Connector X2 - Pinout

X2	Name	Function
	COM	0 V power supply
	24 V	+24 V power supply

Table 8: Connector X2 - Pinout

5.4 Connectors X3A, X3B - Pinout


X3A, X3B	Pin	Name	Function
	1	RXD	Receive signal
	2	RXD\	Receive signal inverted
	3	TXD	Transmit signal
	4	Shield	Shield
	5	Shield	Shield
	6	TXD\	Transmit signal inverted
	7	Shield	Shield
	8	Shield	Shield

Table 9: X3A, X3B connectors - Pinout

5.5 SafeMOTION connector X4x - Pinout


X4x	Pin	Description	Function depending on configured encoder type			
			EnDat SafeMOTION	EnDat 2.2	SSI	BiSS
	1	U+	Encoder power supply +			
	2	T	Clock output			
	3	---	---			
	4	T\	Clock output inverted			
	5	---	---			
	6	D	Data			
	7	COM	Encoder power supply 0 V			
	8	D\	Data inverted			

Table 10: Connector X4x - Pinout

1) Only if the encoder supply voltage (5 V) is configured accordingly.

5.6 Connector X5x - Pinout


X5x	Name	Function
	B+	Brake +
	B-	Brake -
	T+	Temperature sensor + ¹⁾
	T-	Temperature sensor - ¹⁾
	PE	Protective ground conductor
	U	Motor connection U
	V	Motor connection V
	W	Motor connection W

Table 11: Connector X5x - Pinout

1) A temperature sensor does not need to be connected when using a hybrid motor cable solution since the motor temperature is transferred digitally.

Danger!

The connections for the motor temperature sensors and the motor holding brake are safely isolated circuits. As a result, only devices or components that have at least safe isolation per IEC 60364-4-41 or EN 61800-5-1 are permitted to be connected to these connections.

Information:

B&R recommends wiring the ACOPOS P3 X5x motor connectors in the following order:

1. X51
2. X52
3. X53

5.7 Connector X6 - Pinout


X6	Description	Function
	PE	Protective ground conductor
	RB-	Braking resistor -
	RB+	Braking resistor +

Table 12: Connector X6 - Pinout

Danger!

During operation, the contacts of connector X6 carry dangerous voltages greater than 60 VDC. Touching one of these contacts can result in a life-threatening electric shock. This could result in death or severe injury.

For this reason, terminal block 8TB3103.222A-20 or 8TB4103.222A-10 must always be connected to connector X6 during operation.

5.8 Connector X8 - Pinout


X8	Pin	Name	Function
	1	Trigger 1	Trigger 1
	2	COM (1)	Trigger 1 0 V
	3	Trigger 2	Trigger 2
	4	COM (2)	Trigger 2 0 V

Table 13: Connector X8 - Pinout

5.9 Connector X10 - Pinout

In preparation

5.10 Connector X11 - Pinout


X11	Description	Function
	DC+	DC bus connection DC+
	DC+	DC bus connection DC+
	DC-	DC bus connection DC-
	DC-	DC bus connection DC-

Table 14: Connector X11 - Pinout

Danger!

During operation, the contacts of connector X11 carry dangerous voltages greater than 60 VDC. Touching one of these contacts can result in a life-threatening electric shock. This could result in death or severe injury.

For this reason, terminal block 8TB4104.227F-10 must always be connected to connector X11 during operation.

Warning!

Only DC bus circuits of 8EI servo drives with the same supply voltage range are permitted to be connected.