



### Main

Range	Merten
Product or component type	Presence detector
Device presentation	Complete product
Colour tint	Polar white (RAL 9010)

### Complementary

Device application	Lighting
Technology type	Electronic
Device mounting	Surface
Material	Thermoplastic
Surface finish	Glossy
[Ue] rated operational voltage	230 V
Network type	AC
Network frequency	50/60 Hz
Rated current	16 A
Protection type	Creep zone protection
Detection angle	220°
Light intensity adjustment	3...1000 lux
Time delay range	1 s...8 min
Mounting height	2.5 m
IP degree of protection	IP55

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins