



## JxxXxxXyyDzzz


Optical UPC zipcord duplex LSZH patchcords



P/N: JSCSC2DOS2  
SC/SC duplex yellow patch cord OS2  
Duplex clip included ( Other connectors available)



Fiber cable construction



## DESCRIPTION / APPLICATIONS

MMC optical patchcords are ideal for all singlemode and multimode applications. These patchcords are a part of the complete optical link and suit all type of networks, like Telecom, LAN (local Area Network), Wan ( Wide Area Network) and MAN (Metropolitan Area Network).

## GENERAL CHARACTERISTICS

- Optically and mechanically compatible with all the equivalent connectors.
- Optical patch cords with 4 connectors with ceramic ferrule (ZrO<sub>2</sub>) and composite body (SC, LC) or metal (ST, FC)
- Duplex optical patch cords
- Duplex LSZH sheath with aramid yarns strength members (Kevlar-type)
- Individual test report and unit packaging
- Available in different lengths

## STANDARDS

- IEC 60874-14, IEC 61754-2, -4, -4-7, -4-8, -13, -20, -20-7, -20-8,
- IEC 793, IEC 794-1-E1, IEC 794-1-E3,
- ITU-T G.652D,
- UL 1666/901 (WHEN UL CABLE IS USED AND TIA/EIA 455)
- ISO/IEC 11801 2ND ED. AMS 1.0, AMD 2.0
- JIS C5973 F04, ICEA-596
- BELLCORE/TELCORDIA GR-326, GR-409-CORE
- TIA/EIA 604-3, TIA/EIA 568, EN 50173
- ROHS COMPLIANCE ON ALL COMPONENTS AND FINAL PRODUCT,
- WITH NO HAZARDOUS SUBSTANCES AS DETAILED IN ROHS 2002/95/EC

## PATCH CORDS GENERAL CHARACTERISTICS

Temperature range	- 20°C to +60°C(OM3,OM4, OM5,OS2) - 5°C to +60°C
Mating cycles	> 500 cycles
Colour of sheath	Yellow (OS2)   Aqua (OM3)   Erika Violet (OM4)
Fiber version	3mm (OM3, OM4,OM4A,OS2)   3mm (ST & SC)
Colour of boots	Black & Red (ST & SC) White(LC)(OM3, OM4,OM4A)   Green & Black (OS2APC)   Blue & Black (OS2)
Return Loss	> 20dB (OM3,OM4)   > 40dB (OS2)
Insertion Loss (Attenuation)	< 0.3 dB(OM3,OM4,OS2)   < 0.25dB (OM4A)

## CONNECTORS TECHNICAL CHARACTERISTICS

Types	SC, LC (other on request)
Material of ferrule	ZrO <sub>2</sub> (Zirconia / Ceramic)
Connector surface	Convex
Fiber's connection	Epoxy
Material of body	Metal (ST, FC) or composite (SC, LC, MU)
Ferrule drilling	125/126µm (OS2)   127/128µm (OM3,OM4)

## OPTICAL CABLE MECHANICAL PROPERTIES

Weight	15 kg/km
Temperature range	-20°C to +60°C (-5°C to +70°C OM4)
Bending radius	40 mm
Tensile strength	250N (long term) – 450N (short term)
Crush resistance	1000N/dm (OM3,OM4,OS2)   2000N/dm (OM4)

## OPTICAL CABLE PERFORMANCES

Parameters		OM3	OM4	OS2
Core diameter	μm	50	50	9
Cladding diameter	μm	125	125	125
Typ. Attenuation @ 850nm	dB/km	≤ 2.7	≤ 2.7	≤ 0.35
Typ. Attenuation @ 1300nm	dB/km	≤ 0.8	≤ 0.8	≤ 0.22
Bandwidth @ 850nm	MHz * km	> 1500	> 3500	
Bandwidth @ 1300nm	MHz * km	> 500	> 500	
EMB* @ 850nm	MHz * km	> 2000	> 4700	
Chromatic dispersion @1285-13300nm	Ps/(nm*km)			≤ 0.35
Chromatic dispersion @ 1550nm	Ps/(nm*km)			≤ 0.22

## ORDERING INFORMATION

Part Numbers structure	JxxX xxX yyy Dzzz
Replace xx by the connectors left/right	Standard UPC connectors are : SC, LC (others on request)
Replace X by A for APC	Standard APC 8° connectors are: SC, LC, FC
Replace yyy by the length in meters	From 1 up to 100 meters
Replace zzz the type of fiber	OM3 , OM4 ,OS2
Standard lengths (other lengths on request)	1m / 2m / 3m / 5m / 10m / 15m / 20m / 25m / 30m / 50m / 100m