



Product designation
Product type designation
Motor type

Soft Starter
ADXL
Asynchronous
three phase

Electrical features

Supplies voltage

Type of system			Three phase
Rated supply voltage	V		208...600VAC
auxiliary supply voltage (Us)			100...240VAC
Rated frequency	Hz		50/60
Rated starter current Ie	A		162
Rated motor power in-line			
IEC ratings (T≤40°C)			
	230VAC	kW	45
	400VAC	kW	90
	500VAC	KW	110
UL ratings (T≤40°C)			
	220-240VAC	HP	60
	380-415VAC	HP	75
	440-480VAC	HP	125
	550-600VAC	HP	150
Number of controlled phases		Nr.	2
Built-in bypass			Yes
Cooling System			Forced
Rated insulation voltage Ui		V	600

Programming interface

Display	Backlit icon LCD display
Programming with NFC technology	Yes
Optical port	Yes

Startup and stop settings

Startup method	Torque ramp with current limit, Voltage ramp with current limit, Constant torque with current limit
Stop method	Torque ramp, voltage ramp, free-wheel stop

Protections

Auxiliary supply protection	Voltage too low
-----------------------------	-----------------

Power supply Protection	No power, phase loss, phase sequence, frequency out of limits, minimum and maximum voltage
Motor protection	Overload at starting (trip class 2, 10A, 10, 15, 20, 25, 30, 35 and 40), overload during running (trip class 2, 10A, 10, 15, 20, 25 and 30), locked rotor, current asymmetry, minimum torque (dry run), overtemperature, starting too long
Starter protection	Overcurrent, overtemperature, bypass failure, phase shorted, temperature sensor fault, cooling fan fault, maintenance request

Functions	
Built-in bypass	Yes
Built-in display and keypad	Yes
Languages	6
View measurements	Yes
Torque control	Yes
Adjustable current limit	Yes
Dynamic braking	Yes
Kick Start function	Yes
Motor overload electronic protection	Yes
Motor protection PTC input	Yes
Protection against phase loss	Yes
Protection against phase inversion	Yes
Protection against locked rotor	Yes
Protection against thyristor overtemperature	Yes
Protection against low load	Yes
Programmable alarm	Yes
Digital inputs	3
Analog inputs	0
Digital outputs	3
Analog output	0
Optical port for programming	Yes
Event log	Yes
Motor hour counter	Yes
Startup counter	Yes

Clock calendar	Yes
Remote external keypad	No

Input and Output

Digital inputs			
	Number of digital input	Nr.	3
	Digital input type		2 input with dry contact + 1 input with dry contact or PTC (configurable) Programmable (motor start, motor stop, freewheel stop, motor preheating, commands lock, alarms inhibition, thermal status reset, keyboard lock, motor selection, user alarm, command)
	Digital input functions		

Digital outputs			
	Number of digital output	Nr.	3
	Digital output arrangement		2 x 1 NO (SPST) + 1 C/O (SPDT) Ratings: 2 x 1NO contacts: 3A 250VAC - 3A 30VDC 1 x C/O contact: NO contact 5A 250VAC - 5A 30VDC; NC contact 3A 250VAC - 3A 30VDC Programmable (line contactor, run, global alarm, limits, remote variable, alarm Axx, user alarm Axx, OFF)
	Digital output functions		

Ambient conditions


Temperature			
	Operating temperature		
		min	°C -20
		max	°C +60°C (with current derating >40°C of 0.5%/°C)
	Storage temperature		
		min	°C -30
		max	°C +80

Max altitude	m	1000 without derating (over 1000mt with current derating of 0.5%/100m)
Relative humidity	%	<80%
Pollution degree		2
Installation category		III

Housing

Mounting		Screw-fixing
IP degree of protection		IP00
Dimensions (W x H x D)	mm	212 x 301 x 216
Weight	Kg	7.8

Dimensions



Certifications and compliance

Compliance

CSA C22.2 n° 14
IEC/EN 60947-1
IEC/EN 60947-4-2
UL508

Certificates

cULus
EAC
RCM

ETIM classification

ETIM 8.0

EC000640 - Soft
starter