

TECHNICAL DATA

Fluke 301A



Key features

- The body weighs only 132g and is 16mm thick, which is light and portable and can be fitted into a pocket
- The slim and thin jaw of only 10mm can easily clamp onto tightly packed wires
- 400A AC range, 0.01A high resolution
- Tests voltage, resistance and continuity
- Tests current frequency and voltage frequency
- Tests capacitance and diodes

Product overview: Fluke 301A

Fluke 301A

The Fluke 301A Clamp Meter has a lightweight and compact body, which allows you to carry it around in your pocket. The slim and thin jaw can easily clamp onto tightly packed wires. The Fluke 301A tests current, voltage, resistance, continuity, frequency (voltage and current), capacitance, and diode, etc.. You can handle more testing needs with it.

Specifications: Fluke 301A

Specifications

Accuracy is specified for 1 year after calibration, with operating temperatures from 18 °C to 28 °C and relative humidity from 0 % to 75 %. Accuracy specifications take the form of:
 $\pm([\% \text{ of Reading}] + [\text{Number of Least Significant Digits}])$.

Models		301A/301A+		301B		301C		
AC Current (45 to 400 Hz)	Range	40.00 A	400.0 A	60.00 A	600.0 A	60.00 A	600.0 A	1000 A
	Resolution	0.01 A	0.1 A	0.01 A	0.1 A	0.01 A	0.1 A	1 A
	Accuracy	2 % + 10	2 % + 5	2 % + 10	2 % + 5	2 % + 10	2 % + 5	2 % + 5
AC Voltage (45 to 400 Hz)	Range	600.0 V		600.0 V		600.0 V		
	Resolution	0.1 V		0.1 V		0.1V		
	Accuracy	1.5% + 5		1.5% + 5		1.5% + 5		
DC Voltage	Range	600.0 V		600.0 V		600.0 V		
	Resolution	0.1 V		0.1 V		0.1 V		
	Accuracy	1% + 5		1% + 5		1% + 5		
Resistance	Range	600.0 Ω 6.000 kΩ 60.00 kΩ		600.0 Ω 6.000 kΩ 60.00 kΩ		600.0 Ω 6.000 kΩ 60.00 kΩ		
	Accuracy	1% + 5		1% + 5		1% + 5		
Voltage Frequency	Range	9.999 Hz 99.99 Hz 999.9 Hz 9.999 kHz 99.99 kHz		9.999 Hz 99.99 Hz 999.9 Hz 9.999 kHz 99.99 kHz		9.999 Hz 99.99 Hz 999.9 Hz 9.999 kHz 99.99 kHz		
	Accuracy	0.1% + 3		0.1% + 3		0.1% + 3		
Current Frequency	Range	45.0 to 400.0 Hz		45.0 to 400.0 Hz		45.0 to 400.0 Hz		
	Accuracy	0.1% + 3		0.1% + 3		0.1% + 3		
Capacitance	Range	9.999 uF	99.99 uF 999.9 uF	9.999 uF	99.99 uF 999.9 uF	9.999 uF	99.99 uF 999.9 uF	
	Accuracy	2 % + 5	5% + 5	2 % + 5	5% + 5	2 % + 5	5% + 5	
Diode	Range	3.000 V		3.000 V		3.000 V		
	Accuracy	10%		10%		10%		
T-rms Value		-		-		☒		
Continuity		☒		☒		☒		
Hold		☒		☒		☒		
Backlight		-		☒		☒		
Safety rating		CAT III 300V		CAT III 300V		CAT III 300V		
Weight		132 g		132 g		132 g		
Size		190 mm x 52 mm x 16 mm		190 mm x 52 mm x 16 mm		190 mm x 52 mm x 16 mm		
Jaw Opening		34 mm		34 mm		34 mm		
Clamp Arm Size		10 mm X 10 mm		10 mm X 10 mm		10 mm X 10 mm		
Battery		(2) AAA Batteries		(2) AAA Batteries		(2) AAA Batteries		
Warranty		1 year		1 year		1 year		

General Specifications

Maximum Voltage between any Terminal and Earth Ground	300 V
Maximum Differential Voltage between V/ Ω and COM Terminals	600 V
Display (LCD)	6000 counts, updates 3 times per second
Battery Type	2 AAA, IEC LR03
Battery Life	500 hours minimum
Auto Power Off Time	20 minutes
Temperature	Operating: -10 °C to 50 °C
	Storage: -30 °C to 60 °C
Relative Humidity	Operating Humidity: Non condensing (<10°C); ≤ 90 % RH at 10 °C to 30 °C; ≤ 75 % RH at 30 °C to 40 °C; ≤ 45 % RH at 40 °C to 50 °C;
Altitude	Operating: 2000 m; Storage: 12000 m
Temperature Coefficient	0.1 x (specified accuracy) /°C (<18 °C or >28 °C)
Dimensions (H x W x L)	190 mm x 52 mm x 16 mm
Weight	132 g
Jaw Opening	34 mm
Ingress Protection Rating	IP30
Safety	IEC 61010--1, IEC61010-2-032 CAT III 300 V, Pollution Degree 2
Electromagnetic Environment	IEC 61326--1: Portable

Fluke. *Keeping your world up and running.®*

Fluke Corporation
PO Box 9090, Everett, WA 98206 U.S.A.

For more information call:
In the U.S.A. (800) 443-5853
In Europe/M-East/Africa
+31 (0)40 267 5100
In Canada (800)-36-FLUKE
From other countries +1 (425) 446-5500

BUT. FLUKE SOUTH EAST ASIA PTE LTD
Menera Satu Sentra Kelapa Gading #06-05
Jl. Bulevar Kelapa Gading Kav. LA# No. 1
Summarecon Kelapa Gading
Jakarta Utara 14240
Indonesia
Tel: +62 21 2938 5922
Email: info.asean@fluke.com
www.fluke.com/id-en
©2023 Fluke Corporation. Specifications subject to
change without notice.
07/2023

**Modification of this document is not permitted
without written permission from Fluke Corporation.**