

XS5L81PA140

inductive sensor XS5 8x43x8 - brass -
Sn1.5mm - 12..24VDC - cable 2m



Main

Range of product	OsiSense XS
Series name	General purpose
Sensor type	Inductive proximity sensor
Product specific application	-
Sensor name	XS5
Sensor design	Form 8 x 43 x 8
Size	8 mm
Body type	Fixed
Enclosure material	Nickel plated brass
Type of output signal	Discrete
Wiring technique	3-wire
[Sn] nominal sensing distance	1.5 mm
Discrete output function	1 NO
Discrete output type	PNP
Electrical connection	Cable
Cable length	2 m
[Us] rated supply voltage	12...24 V DC
Switching capacity in mA	<= 200 mA
IP degree of protection	IP67

Complementary

Detection face	Lateral top
Detector flush mounting acceptance	Flush mountable
Material	Metal
Front material	PPS
Output circuit type	DC
Cable composition	3 x 0.11 mm ²
Wire insulation material	PvR
Switching frequency	<= 2500 Hz
Marking	CE
Depth	8 mm
Height	8 mm
Width	43 mm
Net weight	0.1 kg

Environment





Product certifications	UL
Ambient air temperature for operation	-25...70 °C

Packing Units

Package 1 Weight	0.046 kg
------------------	----------

The information provided in this documentation contains general descriptions and/or technical characteristics of the products of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Offer Sustainability

Sustainable offer status	Green Premium product
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	 End Of Life Information

Contractual warranty

Warranty	18 months
----------	-----------