



873 PRESTEX SELF-CLOSING BASIN TAP



BASIN PILLAR TAP WITH UNDERBASIN CARTRIDGE AND FLOW REGULATOR SITUATED UNDER THE HANDLE FOR ON SITE ADJUSTMENT.

TECHNICAL INFORMATION



Materials	Body: Brass Cartridge: Brass/dezincification resistant alloys
Cartridge Type	Self-closing, non-concussive, servo assisted diaphragm type using water pressure to assist opening and closing
Time Delay	Maximum 2 seconds
Max. Working Temperature	70°C
Outlet Type	Plastic flow straightener
Connections	1/2" BSP male parallel thread suitable for tap connector or 15 mm Cu compression joint connection
Surface Finish	Chrome Plate

RECOMMENDED OPERATING PRESSURES

Minimum – 0.2 bar (2 metres) static. Maximum – 7 bar

Flow Rates litres/minutes	DYNAMIC PRESSURES	0.1 bar	1 bar	5 bar
	MINIMUM FLOW SETTING	3.0	9.5	21.2
	MAXIMUM FLOW SETTING	6.0	19.0	42.4

876 PRESTEX SELF-CLOSING BASIN TAP



BASIN PILLAR TAP WITH FLOW REGULATOR SITUATED UNDER THE HANDLE FOR ON SITE ADJUSTMENT.

TECHNICAL INFORMATION



Materials	Body: Brass Cartridge: Brass/dezincification resistant alloys
Cartridge Type	Self-closing, non-concussive, servo assisted diaphragm type using water pressure to assist opening and closing
Time Delay	Maximum 2 seconds
Max. Working Temperature	70°C
Outlet Type	Open (unrestricted)
Connections	1/2" BSP male parallel thread suitable for tap connector or 15mm Cu compression joint connection
Surface Finish	Chrome Plate

RECOMMENDED OPERATING PRESSURES

Minimum – 0.2 bar (2 metres) static. Maximum – 7 bar

Flow Rates litres/minutes	DYNAMIC PRESSURES	0.1 bar	1 bar	5 bar
	MINIMUM FLOW SETTING	4.0	12.6	28.3
	MAXIMUM FLOW SETTING	8.3	26.2	58.7

877-2 PRESTEX SELF-CLOSING BASIN TAP



BASIN PILLAR TAP WITH SPRAY AND OPTIONAL FLOW STRAIGHTENER.

TECHNICAL INFORMATION

Materials	Handle: Brass Body: Brass Cartridge: Plastic
Time Delay	Non adjustable ~ 15 seconds in accordance with BS EN 816 at 3 bar
Max. Working Temperature	60°C
Outlet Type	Flow straightener spray plate with flow restrictor interchangeable spray
Connections	1/2" BSP male parallel thread suitable for tap connector or 15mm Cu compression joint connection
Surface Finish	Chrome Plate

RECOMMENDED OPERATING PRESSURES

Minimum – 0.3 bar (3 metres) static. Maximum – 7 bar

Flow Rates litres/minutes	DYNAMIC PRESSURES	0.5 bar	1 bar	2.5 bar
	SPRAY	2.7	3.9	4.5
	FLOW STRAIGHTENER	12	17.4	23.4