



LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
FT	0						
			P2	REVISED PER ECO-11-004820	11MAR11	RK	HMR



- WILL ACCEPT (20) MULTIMATE AND 2 TYPE XII PIN CONTACTS.
- CAVITY IDENTIFICATION ON FRONT AND REAR FACE.

△ NUMBER 4 FASTENERS RECOMMENDED FOR MOUNTING.

△ HOUSING: NYLON, BLACK.
PERIPHERAL SEAL: ELASTOMER, GRAY.

△ APPLIES TO 206613-6 ONLY.

△ PERMANENT WHITE MARKED OR WHITE INK STAMPED CAVITY IDENTIFICATION.

△ HOUSING: NYLON, RED.
PERIPHERAL SEAL: ELASTOMER, GRAY.

△ WHITE DOT NEAR POSITION 1 ON WIRE ENTRY FACE.

PRELIMINARY PRELIMINARY	△△	-	YES	A	1-206613-2
	△	-	YES	A	206613-9
	△△	-	YES	A	206613-7
	△	4	NO	A	206613-6
	△	-	YES	A	206613-5
	△	-	NO	B	206613-3
NOTES	△	-	NO	A	206613-1
		THREADED INSERTS	PERIPHERAL SEAL	SEE DETAIL	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN M. BINNER	05/26/94	 TE Connectivity	
		CHK R. STONE	6-23-94		
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME	
		0 PLC ± -		PRODUCT SPEC	
		1 PLC ± -		108-10024	
		2 PLC ± 0.13 [.005]		APPLICATION SPEC	
		3 PLC ± -			
		4 PLC ± -			
ANGLES		± -		SIZE	
FINISH		-		CAGE CODE	
MATERIAL		-4△△		DRAWING NO	
				A1 00779	
		CUSTOMER DRAWING		C 206613	
		WEIGHT		RESTRICTED TO	
		-		-	
				SCALE	
				2:1	
				SHEET	
				1 OF 1	
				REV	
				P2	